



jalas® 3325

ASTM F2413-18 M/I/C/SD 35/PR ASTM F3445-21 SR EN ISO 20345:2022 S7, HRO, CI

Learn more

A robust, waterproof safety boot with highest protection levels built for warmth in cold environments. The winter-lined grain leather upper and high cut provides feet with both outstanding safety and support. The oil and heat-resistant nitrilee outer sole provides excellent grip, while JALAS® aluminium toe cap protection, steel puncture protection and double impact protection zones in in PORON® XRD® keeps feet in comfort.

CHARACTERISTICS

- Highest level of protection
- Excellent grip
- Perfect fit
- Extra comfortable
- Extremely warm
- Excellent shock absorption

FUNCTIONS

- Waterproof Drylock-membrane
- Heat-resistant outsole
- Oil-resistant outsole
- Anti-static properties
- Bellows tongue
- Padded boot shaft
- Pull loops
- Snow lock
- Zipper
- Waterproof
- Double shock absorption zones
- Conforms with IEC 61340-5-1 (ESD)

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Toe injuries, Nail penetration, Antistatic, Contact with cold

PRIMARY ENVIRONMENTS OF USE

Outdoors, Environments with risk for outsole penetration, Wet environments, Harsh environments

SPECIFICATION

TYPE Safety footwear, Boots/Ankle boots
CATEGORY Cat. II
NAIL PROTECTION MATERIAL Steel
FITTING Regular
UPPER MATERIAL Full-grain leather
TOECAP MATERIAL Aluminium
LINING MATERIAL ThermoCloud - thermal insulation, Polyester, Drylock membrane
INSOLE JALAS 8245 FX2 ThermAL
INNERSOLE MATERIAL Textile, Aluminium foil, Soft EVA, Polyester-based conductive thread, Merino wool, Double shock absorption zones in PORON® XRD®
MIDSOLE MATERIAL PU midsole
OUTSOLE MATERIAL Nitrile rubber outsole
FASTENING Laces, Zipper
SHOELACES LENGTH 180 cm
COLOUR Black
NET WEIGHT, (SIZE 42) 1.65 kg

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

ASTM F2413-18
M/I/C/SD 35/PR

ASTM F3445-21
SR

EN ISO 20345:2022
S7, HRO, CI

FEATURES

- Anti-static properties
- Ergothan Shock Absorption System
- ESD
- Aluminium toecap
- Oil-resistant outsole
- Nail protection in steel
- Heat-resistant outsole
- Waterproof
- Winter model
- Zipper

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
36	3	4	5	3325-36	6408487500695
37	4	5	6	3325-37	6408487500701
38	5	5.5	6.5	3325-38	6408487500718
39	6	6.5	7.5	3325-39	6408487500725
40	6.5	7.5	8.5	3325-40	6408487500732
41	7	8	9	3325-41	6408487500749
42	8	9	10	3325-42	6408487500756
43	9	9.5	11	3325-43	6408487500763
44	10	10.5	11.5	3325-44	6408487500770
45	10.5	11	12.5	3325-45	6408487500787
46	11	12	13	3325-46	6408487500794
47	12	13	14	3325-47	6408487500800

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.