ABB BALDOR RELIANCE

Customer information packet

ECTM3770T-G-AO

7.5 AIR OVERHP, 1770RPM, 3PH, 60HZ, 215T, 073
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 9:29:07 AM

Specifications

Enclosure	TEAO
Frame	215T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	7.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA EEV
	NEMA PREMIUM
	NEMA_PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	9.500 A @ 460.0 V
	20.200 A @ 208.0 V
	19.000 A @ 230.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None

Part Detail

Revision	C
Type	AC
Mech. spec.	07D709
Base	
Status	PRD/A
Elec. spec.	07WGT510
Layout	07LYD709
Eff. date	09-08-2023
CD Diagram	CD0005
Poles	04
Leads	9#14
Proprietary	False
Created date	04-05-2022

Heater Indicator	Heater Included, 115 V
High Voltage Full Load Amps	9.5 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	J
Lifting Lugs	Vertical Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0738M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	19.62 IN
Power Factor	81
Product Family	Chemical Processing (Not DC)
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	Standard
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2178									
CAT.NO.	ECTM3770T-G-AO								
SPEC.	07D709T510G1								
HP	7.5 AIR OVER								
VOLTS	230/460								
AMP	19/9.5								
RPM	1770								
FRAME	215T	**HZ**	60			**PH**	3		
SER.F.	1.15	**CODE**	J	**DES**	A	**CL**	F		
NEMA-NOM-EFF	91.7	**PF**	81						
RATING	40C AMB-CONT								
CC									
DE	6307	**ODE**	6206						
ENCL	TEAO	**SN**							
	INV DUT 20:1 VT								

AC Induction Motor Performance Data
Record # 86625
Preliminary Data Sheet

Winding: 07WGT510-R002	**Type:** 0738M	**Enclosure:** TEAO

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			7.5	**Full Load Torque**	22.3 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			19/9.5	**Breakdown Torque**	69.1 LB-FT
R.P.M.			1770	**Pull-up Torque**	28.7 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	39.1 LB-FT
NEMA Design Code	A	**KVA Code**	J	**Starting Current**	67.4 A
Service Factor (S.F.)			1.15	**No-load Current**	4.07 A
NEMA Nom. Eff.	91.7	**Power Factor**	81	**Line-line Res. @ 25ºC**	1.55 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	48°C
S.F. Amps			21.4/10.7	**Temp. Rise @ S.F. Load**	62°C
				Locked-rotor Power Factor	41.2
				Rotor inertia	0.934 lb-ft²

Load Characteristics 460 V, 60 Hz, 7.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	44	66	76	81	84	85	83
Efficiency	88	91.7	92.2	91.7	90.7	89.3	90.9
Speed	1792	1785	1777	1769	1759	1749	1761
Line amperes	4.61	5.85	7.48	9.43	11.6	13.9	10.7


ABB Motors and Mechanical Inc.


WINDING # 07WGT510

7.5 HP 3 PH 60 HZ 1770 RPM 460 V 0738M

Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=69.1 PU=28.7 LR=39.1 LRA=67.4





CUSTOMER ONLY NOTE: FOR VERTICAL SHAFT UP LIFTING, REMOVE EYEBOLT FROM TOP OF MOTOR AND SCREW INTO END OF SHAFT

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION


REV. DESC: NEW FOR CCT STOCK DEVELOPMENT			
REV: -	VERSION: 00	REVISED: 04:14:44 04/18/2022	TDR: 000001187869
MODEL NO. 07LYD709			REF: -
BY: ENSTEK0			B


BALDOR

HOR 213-5T TEAO CP COOLING TOWER,LIFT,SLD BRGS,SEAL PU,AEGIS

07LYD709

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS