ABB BALDOR RELIANCE

Customer information packet

EM4103T-12

25HP, 1775RPM, 3PH, 60HZ, 284T, 1054M, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 4:15:08 PM

Specifications

Enclosure	TEFC
Frame	284T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	25.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	CURUSEEV
	NEMA PREMIUM
	NEMA PREMIUM (OLD LOGO)
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	62.000 A @ 230.0 V
	64.000 A @ 208.0 V
	31.000 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.6 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part Detail

Revision	K
Type	AC
Mech. spec.	10L62
Base	
Status	PRD/A
Elec. spec.	10WGZ696
Layout	10LYL062
Eff. date	06-27-2024
CD Diagram	CD0104
Poles	04
Leads	12#10
Proprietary	False
Created date	10-23-2017

Heater Indicator	No Heater
High Voltage Full Load Amps	31.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	12 @ 10 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1054M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	27.63 IN
Power Factor	81
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1775 rpm
Speed Code	Single Speed
Starting Method	Wye Start - Delta Run
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2	None

Nameplate

NP3443L											
CAT.NO.	EM4103T-12			**CUST. P/N**						**ENCL**	TEFC
SPEC.	10L062Z696	**CC**	010A	**FRAME**	284T		**SER.NO.**				
HP	25	**CLASS**	F	**HZ**	60						
R.P.M.	1775	**PH**	3	**DES**	A						
VOLTS	230/460	**CODE**	J	**ODE BRG**	6309	**DE BRG**	6311				
AMPS	62/31										
RATING	40C AMB-CONT	**NEMA NOM. EFF.**	93.6	**GREASE**	POLYREX EM						
P.F.	81	**SER.F.**	1.15	**VPWM INVERTER READY**							
HTR-VOLTS		**HTR-AMPS**		**HTR-WATTS**							

AC Induction Motor Performance Data
Record # 67498
Typical performance - not guaranteed values

Winding: 10WGZ696-R001	**Type:** 1054M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: Run Connection**	
Rated Output (HP)			25	**Full Load Torque**	74.02 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			62/31	**Breakdown Torque**	262 LB-FT
R.P.M.			1775	**Pull-up Torque**	118 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	142 LB-FT
NEMA Design Code	A	**KVA Code**	J	**Starting Current**	223 A
Service Factor (S.F.)			1.15	**No-load Current**	13.6 A
NEMA Nom. Eff.	93.6	**Power Factor**	81	**Line-line Res. @ 25ºC**	0.2345 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	51°C
S.F. Amps				**Temp. Rise @ S.F. Load**	61°C
				Locked-rotor Power Factor	30.6

Load Characteristics 460 V, 60 Hz, 25 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	43	65	76	81	84	85	83
Efficiency	88.3	92.8	93.9	94	93.7	93.1	93.8
Speed	1794.1	1789.3	1783.5	1777.8	1770.8	1763.8	1774
Line amperes	15.3	19.3	24.6	30.6	37.2	44.5	34.6


ABB Motors and Mechanical Inc.


WINDING # 10WGZ696

25 HP 3 PH 60 HZ 1775 RPM 460 V 1054M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=262 PU=118 LR=142 LRA=223




10LYL062
(1030-1062) = 27.63
12.75
4.75
4.63
.50 KEY
3.25 LONG
Ø 1.875
1.874
SLINGER
8 HOLES
Ø .53
9.50
.92
9.50
4.75
11.00
12.84
AUTO DRAIN
(EA. END)
15.72
13.18
7.80
GREASER &
RELIEF
(EA. END)
2.70
14.44
7.00 +.00 -.06
LEAD HOLE
Ø 2.00
5.50
5.50
10.57
6.38
12.75
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LOAD DRAWING TO SOLIDWORKS
REV: J
VERSION: 05
REVISED: 07:41:47 06/06/2022
TDR: 000001191141
MODEL NO. 10LYL062
REF: -
BY: ENALEM0
B
BALDOR
HORZ TEFC 284-6T, HI-EFF
10LYL062

CD0104





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0104

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00008\377	REVISED: 09:02:55 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 12 LEADS, Y START/D RUN

SH 1 of 1