SCHAEFER®

30CFO-HE

30CFO-HE



Product Description

Schaefer OSHA compliant high-efficiency circulation fans meet all OSHA safety regulation while delivering maximum airflow. These permanent magnet, electronically commutated motors provide maximum energy savings. They can be mounted on a ceiling, wall, pedestal or cart, which makes them the ideal cooling solution for any commercial, industrial or agricultural facility.

Features

Matched direct drive motors and blades for highest achievable levels of airflow, rated up to 12,000 cfm

Powder coated steel guards for corrosion resistant and durability

Energy efficient designed for additional cost savings, draws as little as 1.6 amps

Variable speed functionality via 0-10VDC for easy control option and direct connection to building management systems

Permanent magnet motor means higher energy efficiency, lower noise and less heat generation

Two year warranty

Made in the USA

Specifications

Blade Color	Metallic
Brand	Schaefer
Cfm/watt (@0.10")	TBD
Drive	Direct
Phase	1
Speeds	2
Vfd Compatible	No
Cfm/watt (free Air)	20.8
Cord	Included - Wired
Diameter (inches)	30
Frequency (hz)	60
Guard Color	White
Nameplate Amps	5.2/2.8

Number Of Wings	3
Cfm/watt (@0.05")	TBD
Power (hp)	1/2
Product Dimensions (l X W X H Inches)	33.5 x 33.5x13.5
Product Net Weight (lbs)	45
Performance Test #	248
Switch	On product
Voltage	115
Maximum Rpm	1075
Blade Material	Aluminum
Cfm (high)	9420
Cfm Calculation Standard	ANSI/AMCA Standard 230-99
Product Color	White

Product Shipping Dimensions (in)	34 x 34 x 14
Speed Control Compatible?	No
Able To Ship Small Parcel	Yes
Cfm (low)	7000
Cfm Range (free Air)	5001 - 10000
Cord Length (feet)	10
Fixed Or Portable	Fixed
Guard Material	Powder Coated Steel
Mount Type Recommended	WMTA30-B, VS30FMT
Oscillating	No
Country Of Origin	US
Guard Spacing (inches)	1/2 OSHA

SIGN UP!