DATA SHEET

Premium Efficiency Motor: **PEWWE2-12-184T** **60 Hz**

WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net

Document Generated: 8-Oct-2024
Document ID:

Customer:

MOTOR INFORMATION

HP	2
RPM	1200
Phase	3
Frequency	60 Hz
Voltage	230/460 V
Frame Size	184T
Enclosure	TEFC
Degree of Protection	IP55
Service Factor	1.25
Poles	6
Full Load Speed	1175
Insulation Class	F
Temp Rise	80°C
NEMA Code Letter	L
Duty Cycle	S1 / Continuous
Slip	2.08%
NEMA Design	B
Moment of Inertia	0.383 lb.ft.^2
Locked Rotor Time (Hot)	14 seconds
Sound Pressure Level	62 dB(A)
Number of Starts	2 Cold/ 1 Hot
Max Ambient Temperature	40°C
Max Elevation	1000 m.a.s.l (3300 f.a.s.l)
Mounting	F1
Rotation	Bi-Directional
Area of Classification	Class 1 Division 2 Groups A,B,C,D T3C(160°C)
Inverter Rating	10:1 CT / 20:1 VT PWM Type
Standard	NEMA MG-1
Approvals	CSA-US, CE

ADDITIONAL DATA

F2 Suitable	Yes
Shaft Material	1045 Carbon Steel
Connection Diagram	230 / 460 V - 9 Lead Y
Approximate Weight	91.5 lbs.

EFFICIENCY/POWER FACTOR

LOAD	EFF	P. F.
100%	88.5 %	0.71
75%	88.3 %	0.63
50%	86.4 %	0.51

TORQUE

FULL LOAD	LRT	BDT
8.94 lb.ft.	200 %	320 %

AMPERAGE INFORMATION

	230V	460V
Full Load Amps	5.96A	2.98A
Locked Rotor Amps	50A	25A
No Load Current	3.7A	1.85A
Usable at 208V	6.59A	

BEARING INFORMATION


DE Bearing	6206ZZ C3
ODE Bearing	6206ZZ C3
Grease Type	-
DE Regreasing Interval	- Hours
ODE Regreasing Interval	- Hours

This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization

MOTOR DRAWING

Premium Efficiency Motor: **PEWWE2-12-184T**

WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net



DIMENSION - INCHES

MOUNTING					A	B	C	D	G	J	P	O	T	AB
E	2F1	2F	H	BA										
3.75	4.5	5.5	0.41	2.75	8.898	6.852	15.827	4.5	0.591	1.969	9.606	9.5	1.417	7.876

SHAFT & KEY				
S	ES	R	N-W	U
0.25	1.78	0.986	2.75	1.125

TERMINAL BOX				
AA	XB	XC	XD	XF
1	2.26	5.124	4.567	5.509

This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization

PERFORMANCE CURVES


Premium Efficiency Motor: **PEWWE2-12-184T**


WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net

Document Generated:	8-Oct-2024
Document ID:	

Customer:

Motor Type	PEWWE						
Output Rating (HP)	2		FL Speed	1175			
Full Load Torque	8.94	lb.ft	LRT (%FLT)	200	460 volt FLA	2.98	A
Rotor Wk^2	0.383	lb-ft^2	BDT (%FLT)	320	230 volt FLA	5.96	A





This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization.


NAMEPLATE / WIRING

Premium Efficiency Motor: **PEWWE2-12-184T**

WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net

Document Generated: 8-Oct-2024 Document ID:	Customer:

SAMPLE NAMEPLATE DATA



Model	PEWWE2-12-184T						
HP	2	S.F.	1.25	IP	IP55	Encl	TEFC
Frame	184T	P.F.	0.71	Code	L	Type	
Voltage	230/460 V	Hz	60 Hz	Ins Cl	F	Ambient	40°C
Amps	5.96/2.98	RPM	1175	Design	B	DE Brng	6206ZZ C3
Nom.Eff.	FL	88.5%	3/4	88.3%		ODE Brng	6206ZZ C3
Class 1 Division 2 Groups A,B,C,D T3C(160℃)						Grease type:	-

50Hz				
2 HP	200/400 V	7.6/3.8 A	970 rpm	79.8%

This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization