



jalas® GRAN PREMIO 1828 JUPITER

ASTM F2413-18 M/I/C/SD 35/PR EN ISO 20345:2011 S3, SRC, CI, HRO, HI

Learn more

A tough, comfortable mid-cut safety boot with highest (S3) protection for the toughest outdoor conditions. A PU-coated split leather upper protects feet and is both water-repellent and anti-static. The oil and heat-resistant nitrilee outer sole has excellent grip and wide last means extra room. The JALAS® aluminium toe cap, steel puncture protection and double impact protection zones in PORON® XRD® mean safety where it's needed.

CHARACTERISTICS

- Highest level of protection
- Excellent grip
- Perfect fit
- Extra comfortable
- Excellent shock absorption

FUNCTIONS

- ProNose toe reinforcement
- Wide fit
- Heat-resistant outsole
- Oil-resistant outsole
- Anti-static properties
- Bellows tongue
- Padded boot shaft
- Ventilating insole
- Ankle support
- Pull loops
- Water repellent
- Double shock absorption zones
- Conforms with IEC 61340-5-1 (ESD)

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Toe injuries, Nail penetration, Antistatic

PRIMARY ENVIRONMENTS OF USE

Outdoors, Environments with risk for outsole penetration, Harsh environments

SPECIFICATION

TYPE Safety footwear, Boots/Ankle boots
CATEGORY Cat. II
NAIL PROTECTION MATERIAL Steel
FITTING Wide
COLLECTION Gran Premio
UPPER MATERIAL PU-coated leather
PRONOSE MATERIAL PU
TOECAP MATERIAL Aluminium
LINING MATERIAL Polyester, polyamide
INSOLE JALAS 8103 FX2 Pro-X
INNERSOLE MATERIAL Textile, Soft EVA, Polyester-based conductive thread, Double shock absorption zones in PORON® XRD®
MIDSOLE MATERIAL PU midsole
OUTSOLE MATERIAL Nitrile rubber outsole
FASTENING Laces
SHOELACES LENGTH 120 cm
COLOUR Black
NET WEIGHT, (SIZE 42) 1.44 kg

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

ASTM F2413-18
M/I/C/SD 35/PR

EN ISO 20345:2011
S3, SRC, CI, HRO, HI

FEATURES

- Anti-static properties
- Ergothan Shock Absorption System
- ESD
- Aluminium toecap
- Oil-resistant outsole
- ProNose toe reinforcement
- Nail protection in steel
- Wide fit
- Heat-resistant outsole
- Water repellent

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
35	2	3.5	4	1828-35	6408487502163
36	3	4	5	1828-36	6408487502170
37	4	5	6	1828-37	6408487440458
38	5	5.5	6.5	1828-38	6408487440465
39	6	6.5	7.5	1828-39	6408487440472
40	6.5	7.5	8.5	1828-40	6408487440489
41	7	8	9	1828-41	6408487440496
42	8	9	10	1828-42	6408487440502
43	9	9.5	11	1828-43	6408487440519
44	10	10.5	11.5	1828-44	6408487440526
45	10.5	11	12.5	1828-45	6408487440533
46	11	12	13	1828-46	6408487440540
47	12	13	14	1828-47	6408487440557
48	13	13.5	14.5	1828-48	6408487440564
49	14	14.5	15.5	1828-49	6408487502194
50	15	15.5	16.5	1828-50	6408487502187

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.