



Fuse terminal thermoplast Screw terminal on both sides 10 mm Sz. 1.5

| Model   |                      |
|---|----------------------|
| product brand name                                    | ALPHA                |
| type of light source / as defect indicator            | without              |
| design of the fuse link                               | others               |
| design of fuse holder                                 | without              |
| General technical data                                |                      |
| insulation material                                   | thermoplastic        |
| terminal contact spacing                              | 10 mm                |
| Supply voltage  |                      |
| operating voltage / rated value                       | 250 V                |
| type of voltage / for supply of the defect indicator  | others               |
| Protection class                                      |                      |
| combustibility class acc. to UL 94                    | Other                |
| Main circuit  |                      |
| operational current / rated value                     | 6.3 A                |
| Appearance  |                      |
| color   | miscellaneous        |
| Product details                                       |                      |
| product component / required / end cover plate        | No                   |
| Number  |                      |
| number of terminal levels                             | 1                    |
| Connections   |                      |
| connectable conductor cross-section / solid           |                      |
| • minimum   | 1 mm <sup>2</sup>    |
| • maximum   | 1 mm <sup>2</sup>    |
| connectable conductor cross-section / stranded        |                      |
| • maximum   | 1.5 mm <sup>2</sup>  |
| connectable conductor cross-section / finely stranded |                      |
| • with core end processing / minimum                  | 0.75 mm <sup>2</sup> |
| • with core end processing / maximum                  | 1.5 mm <sup>2</sup>  |
| type of electrical connection                         |                      |
| • 1   | screw-type terminal  |
| • 2   | screw-type terminal  |
| position / of the terminal                            | lateral              |
| Mechanical Design                                     |                      |
| height / with lowest-profile installation             | 42 mm                |

|                                   |                                  |                          |                          |
|-----------------------------------|----------------------------------|--------------------------|--------------------------|
| length                            | 57 mm                            |                          |                          |
| fastening method                  | DIN rail 35 mm                   |                          |                          |
| material / of the insulating body | Thermoplast                      |                          |                          |
| <b>General Product Approval</b>   | <b>Declaration of Conformity</b> | <b>Test Certificates</b> | <b>Marine / Shipping</b> |



[Miscellaneous](#)



other

[Environmental Confirmations](#)

#### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8WA1011-1SF12>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/8WA1011-1SF12>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8WA1011-1SF12](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8WA1011-1SF12)

**Tender specifications**

<http://www.siemens.com/specifications>

