

## AYP2, Compression Pin Adapter, 2 AWG, AL9CU

By Burndy  
Catalog # [AYP2](#)

2 AWG, Aluminum Termination, Straight Pin, .23" Pin Dia, .68" Pin Length



### Features

- All-aluminum electro-tin plated design eliminates possible bi-metallic corrosion
- Provides the shortest connector length design possible permitting easy installation in equipment with limited working space
- Solid electro-tin plated aluminum plug
- Proper electrical connection made easily and eliminates the "how tight is tight" issue
- Solid plug has equivalent cross-sectional area as current carrying equivalent copper wire permitting use of larger aluminum wire to connect equipment
- Offset plug design available in sizes 2/0 through 750 kcmil providing flexibility and maximizing the use of limited space while eliminating interference between conductors and equipment
- Electro-tin plating resists corrosion
- Factory pre-filled with PENETROX oxide inhibiting compound with conductive metallic particles to penetrate aluminum oxide between strands and forms an air-tight connection
- EPDM rubber covers supplied with each connector and rated for 600V eliminating taping
- Only 5 die sets are required to install the complete line from #6 to 750 kcmil reducing inventory requirements
- Supplied in plastic convenience pack so cover and connector are kept together and free of foreign material until opened
- Connectors are clearly marked with catalog number, wire size, along with a color-coded die index providing clear, easy to use information

### Application

Wire Termination

### Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Certification - CSA Approved Yes

### Conductor

Conductor - Material	ALUMINUM / COPPER
Wire Size	2 AWG
Conductor - AL Str Size	2 AWG
Conductor - AL Str Size Range	2 AWG
Conductor - Copper Str Size	2 AWG
Conductor - Copper Flex I Size Range	2 AWG
Conductor - Copper DLO Size Range	2 AWG
Conductor - Copper Str Compact Size	2 AWG
Conductor - Copper DLO Size Conductor Size	4 AWG 2 AWG
Conductor - Copper Solid Size	2 AWG
Conductor - Copper Solid Size Range	2 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	2 AWG
Conductor - Copper Flex I Size	2 AWG

### Configuration

Physical Attribute - Number of Crimps Required	1
Connector Type	INLINE PIN

### Current

Voltage Rating	35 kV
Voltage - Maximum	35000 V

### Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - P inch	0.68 in
Dimension - L Length Overall mm	47 mm
Width	0.6 in
Dimension - A Outside	0.60 in
Diameter inch	
Dimension - Strip Length inch	1-1/16 in

Length	1.85 in
Equivalent Pin Size	4 AWG
Dimension - B Length fraction	1 in
Dimension - B Length inch	1.00 in
Dimension - B Outside	0.23 in
Diameter inch	
Height	0.6 in
Dimension - Length Overall inch	1.85 in
Dimensions	1.85 in x 0.6 in x 0.6 in

### General

Insulation Type	EPDM Rubber
Trade Name	HYPLUG™
Die Index	296
Insulation	Y
Terminal Type	Pin
Plated	Y
Color Code	Tan
Pin Type	Solid

Sub Brand	HYPLUG
UPC	781810737545
Type	Aluminum Pin Adapters
Material	Aluminum
Plating Type	Tin
Finish Type	Tin-Plated
UPC 12 Digit	781810737545
UPC 14 Digit GTIN	00781810737545

### Logistics

Minimum Pack Quantity	1
Pallet Quantity	7400
Carton Quantity	25

### Operational

Temperature Rating	194
--------------------	-----

### Product Assets

[Catalog \[English\]](#)



A Hubbell brand