

## IEC Sizes L, M and N

| Description                                                                       |                    | IEC Size L<br>Part Number | IEC Size M<br>Part Number | IEC Size N<br>Part Number |
|-----------------------------------------------------------------------------------|--------------------|---------------------------|---------------------------|---------------------------|
| <b>Contact Kits</b>                                                               |                    |                           |                           |                           |
| Two-pole                                                                          |                    | 6-43-3                    | 6-43                      | 6-43-5                    |
| Three-pole                                                                        |                    | 6-43-4                    | 6-43-2                    | 6-43-6                    |
| Four-pole                                                                         |                    | —                         | —                         | —                         |
| Five-pole                                                                         |                    | —                         | —                         | —                         |
| <b>Magnet Coils</b>                                                               | <b>Coil Suffix</b> |                           |                           |                           |
| 120V, 60 Hz or 110V, 50 Hz                                                        | A                  | 9-2756-1                  | 9-2756-1                  | 9-2756-1                  |
| 240V, 60 Hz or 220V, 50 Hz                                                        | B                  | 9-2756-2                  | 9-2756-2                  | 9-2756-2                  |
| 480V, 60 Hz or 440V, 50 Hz                                                        | C                  | 9-2756-3                  | 9-2756-3                  | 9-2756-3                  |
| 600V, 60 Hz or 550V, 50 Hz                                                        | D                  | 9-2756-4                  | 9-2756-4                  | 9-2756-4                  |
| 208V, 60 Hz                                                                       | E                  | 9-2756-5                  | 9-2756-5                  | 9-2756-5                  |
| 277V, 60 Hz                                                                       | H                  | 9-2756-9                  | 9-2756-9                  | 9-2756-9                  |
| 240V, 50 Hz                                                                       | K                  | 9-2756-13                 | 9-2756-13                 | 9-2756-13                 |
| 380–415V, 50 Hz                                                                   | L                  | —                         | —                         | —                         |
| 380V, 50 Hz                                                                       | L                  | 9-2756-12                 | 9-2756-12                 | 9-2756-12                 |
| 415V, 50 Hz                                                                       | M                  | 9-2756-8                  | 9-2756-8                  | 9-2756-8                  |
| 550V, 50 Hz                                                                       | N                  | 9-2756-14                 | 9-2756-14                 | 9-2756-14                 |
| 24V, 60 Hz–24V, 50 Hz                                                             | T                  | —                         | —                         | —                         |
| 24V, 60 Hz                                                                        | T                  | 9-2756-6                  | 9-2756-6                  | 9-2756-6                  |
| 24V, 50 Hz                                                                        | U                  | 9-2756-11                 | 9-2756-11                 | 9-2756-11                 |
| 32V, 50 Hz                                                                        | V                  | 9-2756-10                 | 9-2756-10                 | 9-2756-10                 |
| 48V, 60 Hz                                                                        | W                  | 9-2756-15                 | 9-2756-15                 | 9-2756-15                 |
| 48V, 50 Hz                                                                        | Y                  | 9-2756-7                  | 9-2756-7                  | 9-2756-7                  |
| <b>Overload Relays</b>                                                            |                    |                           |                           |                           |
| For replacement on existing starters<br>three-pole—ambient compensated bimetallic |                    | 10-6530                   | 10-6530-2                 | 10-6530-3                 |
| <b>Current Transformer</b>                                                        |                    |                           |                           |                           |
| Transformer                                                                       |                    | —                         | —                         | —                         |
| <b>Magnet Frame Armature</b>                                                      |                    |                           |                           |                           |
| Lower magnet frame                                                                |                    | 17-8955-2                 | 17-8955-2                 | 17-8955-2                 |
| Upper magnet frame                                                                |                    | 48-1902                   | 48-1902                   | 48-1902                   |