



# SAFETY DATA SHEET

## 1. Identification

<b>Important information</b>	*** This Safety Data Sheet is only authorised for use by HP for HP Original products. Any unauthorised use of this Safety Data Sheet is strictly prohibited and may result in legal action being taken by HP. ***
<b>Product identifier</b>	W1143A
<b>Other means of identification</b>	None.
<b>Recommended use</b>	Not available.
<b>Recommended restrictions</b>	None known.
<b>Manufacturer/Importer/Supplier/Distributor information</b>	HP Inc. 1501 Page Mill Road Palo Alto, CA 94304-1112 United States
<b>Telephone</b>	650-857-1501
<b>HP Inc. health effects line (Toll-free within the US) (Direct)</b>	1-800-457-4209 1-760-710-0048
<b>HP Inc. Customer Care Line (Toll-free within the US) (Direct)</b>	1-800-474-6836 1-208-323-2551
<b>Email:</b>	sustainability@hp.com

## 2. Hazard(s) identification

<b>Physical hazards</b>	Not classified.
<b>Health hazards</b>	Not classified.
<b>Environmental hazards</b>	Not classified.
<b>OSHA defined hazards</b>	Not classified.
<b>Label elements</b>	
<b>Hazard symbol</b>	None.
<b>Signal word</b>	None.
<b>Hazard statement</b>	Not available.
<b>Precautionary statement</b>	
<b>Prevention</b>	Not available.
<b>Response</b>	Not available.
<b>Storage</b>	Not available.
<b>Disposal</b>	Not available.
<b>Hazard(s) not otherwise classified (HNOC)</b>	Carbon black is classified by the IARC as a Group 2B carcinogen (the substance is possibly carcinogenic to humans). Carbon black in this preparation, due to its bound form, does not present this carcinogenic risk. None of the other ingredients in this preparation are classified as carcinogens according to ACGIH, EU, IARC, MAK, NTP or OSHA.
<b>Supplemental information</b>	This product is not classified as hazardous according to OSHA CFR 1910.1200 (HazCom 2012).

## 3. Composition/information on ingredients

### Mixtures

Chemical name	Common name and synonyms	CAS number	%
Polyester resin	Polyester resin	Proprietary	<95

Material name: W1143A

14936 Version #: 13 Revision date: 20-May-2025 Issue date: 28-Nov-2019

SDS US

1 / 8

Chemical name	Common name and synonyms	CAS number	%
Black Pigment		Proprietary	<5
Silica		Proprietary	<5
Wax	Wax	Proprietary	<5
<b>Composition comments</b>	This product has been evaluated using criteria specified in 29 CFR 1910.1200 (Hazard Communication Standard).		
	*Proprietary		

#### 4. First-aid measures

<b>Inhalation</b>	Move person to fresh air immediately. If irritation persists, consult a physician.
<b>Skin contact</b>	Wash affected areas thoroughly with mild soap and water. Get medical attention if irritation develops or persists.
<b>Eye contact</b>	Do not rub eyes. Immediately flush with large amounts of clean, warm water (low pressure) for at least 15 minutes or until particles are removed. If irritation persists, consult a physician.
<b>Ingestion</b>	Rinse mouth with water. Drink one to two glasses of water. DO NOT induce vomiting. Get medical attention immediately.
<b>Most important symptoms/effects, acute and delayed</b>	Difficulty in breathing. Coughing.
<b>Indication of immediate medical attention and special treatment needed</b>	Treat symptomatically.
<b>General information</b>	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

#### 5. Fire-fighting measures

<b>Suitable extinguishing media</b>	Dry chemical, foam, carbon dioxide, water fog.
<b>Unsuitable extinguishing media</b>	Do not use water jet as an extinguisher, as this will spread the fire.
<b>Specific hazards arising from the chemical</b>	During fire, gases hazardous to health may be formed.
<b>Special protective equipment and precautions for firefighters</b>	Firefighters should wear full protective clothing including self contained breathing apparatus.
<b>Fire fighting equipment/instructions</b>	Move containers from fire area if you can do so without risk.
<b>Specific methods</b>	Use standard firefighting procedures and consider the hazards of other involved materials.
<b>General fire hazards</b>	No unusual fire or explosion hazards noted.

#### 6. Accidental release measures

<b>Personal precautions, protective equipment and emergency procedures</b>	Keep unnecessary personnel away. Wear appropriate protective equipment and clothing during clean-up. Use a NIOSH/MSHA approved respirator if there is a risk of exposure to dust/fume at levels exceeding the exposure limits. See Section 8 of the SDS for Personal Protective Equipment.
<b>Methods and materials for containment and cleaning up</b>	Avoid the generation of dusts during clean-up. Use explosion proof electric equipment. Collect dust using a vacuum cleaner equipped with HEPA filter. The product is immiscible with water and will spread on the water surface. Stop the flow of material, if this is without risk. Sweep up or vacuum up spillage and collect in suitable container for disposal.
<b>Environmental precautions</b>	Avoid discharge into drains, water courses or onto the ground.

#### 7. Handling and storage

<b>Precautions for safe handling</b>	Minimize dust generation and accumulation. Use local exhaust ventilation. Avoid prolonged exposure. Practice good housekeeping.
<b>Conditions for safe storage, including any incompatibilities</b>	Store in tightly closed original container. Store in a well-ventilated place. Store away from incompatible materials (see Section 10 of the SDS).

## 8. Exposure controls/personal protection

### Occupational exposure limits

#### US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value
Black Pigment	PEL	3.5 mg/m3

#### US. OSHA Table Z-3 (29 CFR 1910.1000)

Components	Type	Value	Form
Black Pigment	TWA	5 mg/m3	Respirable fraction.
		15 mg/m3	Total dust.
		50 mppcf	Total dust.
		15 mppcf	Respirable fraction.

#### US. ACGIH Threshold Limit Values

Components	Type	Value	Form
Black Pigment	TWA	3 mg/m3	Inhalable fraction.

#### US. NIOSH. Immediately Dangerous to Life or Health (IDLH) Values, as amended

Components	Type	Value
Black Pigment	IDLH	1750 mg/m3

#### US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
Black Pigment	TWA	0.1 mg/m3

### Biological limit values

No biological exposure limits noted for the ingredient(s).

### Exposure guidelines

USA OSHA (TWA/PEL): 15 mg/m3 (Total Dust) 5 mg/m3 (Respirable Fraction)

ACGIH (TWA/TLV): 10 mg/m3 (Inhalable Particulate) 3 mg/m3 (Respirable Particulate)

### Appropriate engineering controls

Good general ventilation should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. If engineering measures are not sufficient to maintain concentrations of dust particulates below the Occupational Exposure Limit (OEL), suitable respiratory protection must be worn. If material is ground, cut, or used in any operation which may generate dusts, use appropriate local exhaust ventilation to keep exposures below the recommended exposure limits.

### Individual protection measures, such as personal protective equipment

**Eye/face protection** Wear safety glasses with side shields (or goggles).

#### Skin protection

**Hand protection** Rubber gloves are recommended. Wash hands after handling.

**Other** Protection suit must be worn.

**Respiratory protection** No personal respiratory protective equipment required under normal conditions of use. Use a NIOSH/MSHA approved respirator if there is a risk of exposure to dust/fume at levels exceeding the exposure limits.

**Thermal hazards** Wear appropriate thermal protective clothing, when necessary.

### General hygiene considerations

Keep away from food, drink and animal feeding stuffs. Wash hands before breaks and immediately after handling the product.

## 9. Physical and chemical properties

### Appearance

**Physical state** Not available.

**Form** Solid. Fine powder

**Color** Black.

**Odor** Odorless

**Odor threshold** Not available.

**pH** Not available.

<b>Melting point/freezing point</b>	Not available.
<b>Initial boiling point and boiling range</b>	Not available.
<b>Flash point</b>	Not available.
<b>Evaporation rate</b>	Not available.
<b>Flammability (solid, gas)</b>	Not available.
<b>Upper/lower flammability or explosive limits</b>	
<b>Explosive limit - lower (%)</b>	Not available.
<b>Explosive limit - upper (%)</b>	Not available.
<b>Vapor density</b>	Not available.
<b>Vapor density</b>	Not available.
<b>Solubility(ies)</b>	
<b>Solubility (water)</b>	Insoluble in water.
<b>Solubility (other)</b>	Partially soluble in toluene, chloroform and tetrahydrofuran
<b>Partition coefficient (n-octanol/water)</b>	Not available.
<b>Auto-ignition temperature</b>	Not available.
<b>Decomposition temperature</b>	>392 °F (>200 °C)
<b>Viscosity</b>	Not available.
<b>Other information</b>	Not available.
<b>Oxidizing properties</b>	No information available.
<b>9.2. Other information</b>	
<b>Density</b>	1.20 g/ml

---

## 10. Stability and reactivity

<b>Reactivity</b>	The product is stable and non-reactive under normal conditions of use, storage and transport.
<b>Chemical stability</b>	Stable under normal storage conditions.
<b>Possibility of hazardous reactions</b>	No dangerous reaction known under conditions of normal use.
<b>Conditions to avoid</b>	Avoid temperatures exceeding the decomposition temperature. Contact with incompatible materials.
<b>Incompatible materials</b>	This product may react with strong oxidizing agents.
<b>Hazardous decomposition products</b>	Carbon monoxide and carbon dioxide.

---

## 11. Toxicological information

### Information on likely routes of exposure

<b>Inhalation</b>	Dust may irritate respiratory system. Prolonged inhalation may be harmful.
<b>Skin contact</b>	Dust or powder may irritate the skin.
<b>Eye contact</b>	Dust may irritate the eyes.
<b>Ingestion</b>	Expected to be a low ingestion hazard.

**Symptoms related to the physical, chemical and toxicological characteristics** Not available.

### Information on toxicological effects

**Acute toxicity** Based on available data, the classification criteria are not met.  
LD50/oral/rat >5000 mg/kg.

<b>Components</b>	<b>Species</b>	<b>Test Results</b>
Black Pigment		
<u><b>Acute</b></u>		
<b>Oral</b>		
LD50	Rat	> 10000 mg/kg

<b>Skin corrosion/irritation</b>	Based on available data, the classification criteria are not met. Not a known irritant. (OECD 404).
<b>Serious eye damage/eye irritation</b>	Based on available data, the classification criteria are not met. Not a known irritant. (OECD 405).
<b>Respiratory or skin sensitization</b>	
<b>Respiratory sensitization</b>	Not a respiratory sensitizer.
<b>Skin sensitization</b>	This product is not expected to cause skin sensitization.
<b>Germ cell mutagenicity</b>	Based on available data, the classification criteria are not met. Negative Ames Test (Test strains: Salmonella typhimurium).
<b>Carcinogenicity</b>	Based on available data, the classification criteria are not met.  Carbon black is classified as a carcinogen by the IARC (possibly carcinogenic to humans, Group 2B) and by the State of California under Proposition 65. In their evaluations of carbon black, both organizations indicate that exposure to carbon black, per se, does not occur when it remains bound within a product matrix, specifically, rubber, ink, or paint.  None of the other ingredients in this preparation are classified as carcinogens according to ACGIH, EU, IARC, MAK, NTP or OSHA.
<b>IARC Monographs. Overall Evaluation of Carcinogenicity</b>	
Black Pigment (CAS Proprietary)	2B Possibly carcinogenic to humans.
<b>OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)</b>	
Not listed.	
<b>US. National Toxicology Program (NTP) Report on Carcinogens</b>	
Black Pigment (CAS Proprietary)	Known To Be Human Carcinogen.
<b>Reproductive toxicity</b>	This product is not expected to cause reproductive or developmental effects.
<b>Specific target organ toxicity - single exposure</b>	Based on available data, the classification criteria are not met.
<b>Specific target organ toxicity - repeated exposure</b>	Based on available data, the classification criteria are not met.
<b>Aspiration hazard</b>	Based on available data, the classification criteria are not met.
<b>Further information</b>	Complete toxicity data are not available for this specific formulation Refer to Section 2 for potential health effects and Section 4 for first aid measures.  In a study in rats (H.Muhle) by chronic inhalation exposure to a typical toner, a mild to moderate degree of lung fibrosis was observed in 92% of the rats in the concentration(16mg/m3) exposure group, and a minimal to mild degree of fibrosis was noted in 22% of the animals in the middle (4mg/m3) exposure group. But no pulmonary changes was reported in the lowest (1mg/m3) exposure group, the most relevant level to potential human exposures.

---

## 12. Ecological information

<b>Ecotoxicity</b>	The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.
<b>Persistence and degradability</b>	No data is available on the degradability of any ingredients in the mixture.
<b>Bioaccumulative potential</b>	Not available.
<b>Mobility in soil</b>	Not available.
<b>Other adverse effects</b>	Not available.

---

## 13. Disposal considerations

<b>Disposal instructions</b>	Dispose of in compliance with federal, state, and local regulations. Do not shred toner cartridge, unless dust-explosion prevention measures are taken. Do not put toner container into fire; heated toner may cause severe burns. Do not incinerate. Do not allow this material to drain into sewers/water supplies.  HP's Planet Partners (trademark) supplies recycling program enables simple, convenient recycling of HP original inkjet and LaserJet supplies. For more information and to determine if this service is available in your location, please visit <a href="http://www.hp.com/recycle">http://www.hp.com/recycle</a> .
------------------------------	--

---

## 14. Transport information

<b>DOT</b>	
<b>UN number</b>	Not available.

**UN proper shipping name** Not Regulated  
**Transport hazard class(es)**  
**Class** Not available.  
**Subsidiary risk** -  
**Packing group** Not available.  
**Environmental hazards**  
**Marine pollutant** No  
**Special precautions for user** Not available.

#### IATA

**UN number** Not available.  
**UN proper shipping name** Not Regulated  
**Transport hazard class(es)**  
**Class** Not available.  
**Subsidiary risk** -  
**Packing group** Not available.  
**Environmental hazards** No  
**Special precautions for user** Not available.

#### IMDG

**UN number** Not available.  
**UN proper shipping name** No Regulated  
**Transport hazard class(es)**  
**Class** Not available.  
**Subsidiary risk** -  
**Packing group** Not available.  
**Transport hazard class(es)**  
**Marine pollutant** No  
**EmS** Not available.  
**Special precautions for user** Not available.

#### ADR

**UN number** Not available.  
**UN proper shipping name** Not Regulated  
**Transport hazard class(es)**  
**Class** Not available.  
**Subsidiary risk** -  
**Hazard No. (ADR)** Not available.  
**Tunnel restriction code** Not available.  
**Packing group** Not available.  
**Environmental hazards** No  
**Special precautions for user** Not available.

**Further information** Not a dangerous good under DOT, IATA, ADR, IMDG, or RID.

---

## 15. Regulatory information

**US federal regulations** US EPA TSCA Inventory: All chemical substances in this product comply with all rules or orders under TSCA.

### Toxic Substances Control Act (TSCA)

#### TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

### CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

### SARA 304 Emergency release notification

Not regulated.

### OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Not listed.

### Superfund Amendments and Reauthorization Act of 1986 (SARA)

#### SARA 302 Extremely hazardous substance

Not listed.

**SARA 311/312 Hazardous chemical** No

**Other federal regulations**

**Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List**

No intentionally added HAP substances.

**Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)**

Not regulated.

**Safe Drinking Water Act (SDWA)** Not regulated.

**US state regulations**

**California Proposition 65**

**California Proposition 65 - CRT: Listed date/Carcinogenic substance**

Black Pigment (CAS Proprietary)

Listed: February 21, 2003

**Regulatory information**

HP complies with chemical regulatory requirements in chemical substance notification laws, where applicable. All chemical substances are notified or exempt from notification or listed in the inventory as existing substances in the following countries: US (TSCA), Canada (DSL/NDSL), Australia (AICIS), Japan (ISHL, ENCS), Philippines (PICCS), New Zealand (NZIoC) and China (IECSC). For guidance on importation and/or additional requirements for registration schemes such as EAEU, EU, South Korea, Turkey, UK, India and Taiwan, please contact the Sustainability and Compliance Center (sustainability@hp.com).

---

**16. Other information, including date of preparation or last revision**

**Issue date** 28-Nov-2019

**Revision date** 20-May-2025

**Version #** 13

**Other information** This SDS was prepared in accordance with USA OSHA Hazard Communications regulation (29 CFR 1910.1200).

**Disclaimer**

This Safety Data Sheet document is provided without charge to customers of HP. Data is the most current known to HP at the time of preparation of this document and is believed to be accurate. It should not be construed as guaranteeing specific properties of the products as described or suitability for a particular application. This document was prepared to the requirements of the jurisdiction specified in Section 1 above and may not meet regulatory requirements in other countries.

This safety data sheet is meant to convey information about HP inks (toners) provided in HP Original ink (toner) supplies. If our Safety Data Sheet has been provided to you with a refilled, remanufactured, compatible or other non-HP Original supply please be aware that the information contained herein was not meant to convey information about such products and there could be considerable differences from information in this document and the safety information for the product you purchased. Please contact the seller of the refilled, remanufactured or compatible supplies for applicable information, including information on personal protective equipment, exposure risks and safe handling guidance. HP does not accept refilled, remanufactured or compatible supplies in our recycling programs.

## Explanation of abbreviations

<b>ACGIH</b>	American Conference of Governmental Industrial Hygienists
<b>Acute Tox.</b>	Acute toxicity
<b>Aquatic Acute</b>	Short-term (acute) aquatic hazard
<b>Aquatic Chronic</b>	Long-term (chronic) aquatic hazard
<b>Asp. Tox.</b>	Aspiration hazard
<b>Carc.</b>	Carcinogenicity
<b>CAS</b>	Chemical Abstracts Service
<b>CERCLA</b>	Comprehensive Environmental Response Compensation and Liability Act
<b>CFR</b>	Code of Federal Regulations
<b>COC</b>	Cleveland Open Cup
<b>DOT</b>	Department of Transportation
<b>EPCRA</b>	Emergency Planning and Community Right-to-Know Act (aka SARA)
<b>Eye Dam.</b>	Serious eye damage
<b>Eye Irrit.</b>	Eye Irritation
<b>Flam. Liq.</b>	Flammable liquids
<b>Flam. Sol.</b>	Flammable solids
<b>Lact.</b>	Effects on or via lactation
<b>Muta.</b>	Germ cell mutagenicity
<b>IARC</b>	International Agency for Research on Cancer
<b>NIOSH</b>	National Institute for Occupational Safety and Health
<b>NTP</b>	National Toxicology Program
<b>OSHA</b>	Occupational Safety and Health Administration
<b>Ox. Liq.</b>	Oxidising liquids
<b>Ozone</b>	Hazardous to the ozone layer
<b>PEL</b>	Permissible Exposure Limit
<b>Press. Gas</b>	Gases under pressure
<b>RCRA</b>	Resource Conservation and Recovery Act
<b>REC</b>	Recommended
<b>REL</b>	Recommended Exposure Limit
<b>Repr.</b>	Reproductive toxicity
<b>Resp. Sens.</b>	Respiratory sensitization
<b>SARA</b>	Superfund Amendments and Reauthorization Act of 1986
<b>Skin Corr.</b>	Skin corrosion
<b>Skin Irrit.</b>	Skin irritation
<b>Skin Sens.</b>	Skin sensitization
<b>STEL</b>	Short-Term Exposure Limit
<b>STOT RE</b>	Specific target organ toxicity - repeated exposure
<b>STOT SE</b>	Specific target organ toxicity - single exposure
<b>TCLP</b>	Toxicity Characteristics Leaching Procedure
<b>TLV</b>	Threshold Limit Value
<b>TSCA</b>	Toxic Substances Control Act