ABB BALDOR RELIANCE

Customer information packet

CEM3708T

5HP, 1165RPM, 3PH, 60HZ, 215TC, 3746M, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 6:17:01 PM

Specifications

Enclosure	TEFC
Frame	215TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CURUSEEV
	NEMA PREMIUM
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	15.600 A @ 208.0 V
	15.600 A @ 230.0 V
	7.800 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	7.8 a

Part Detail

Revision	-
Type	AC
Mech. spec.	37G814
Base	
Status	PRD/A
Elec. spec.	37WGZ714
Layout	37LYG814
Eff. date	11-24-2025
CD Diagram	CD0005
Poles	06
Leads	9#14
Proprietary	False
Created date	11-05-2025

Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	K
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3746M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	20.50 IN
Power Factor	67
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1165 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3441LUA												
CAT.NO.	CEM3708T											
SPEC	37G814Z714											
HP	5											
VOLTS	230/460											
AMPS	15.6/7.8											
RPM	1165											
FRAME	215TC		**HZ**	60			**PH**	3				
SF	1.15	**CODE**	K	**DES**	A	**CLASS**	F					
NEMA NOM. EFF	89.5	**PF**	67									
RATING	40C AMB-CONT											
CC	010A											
ENCL	TEFC	**SER**										
DE	6307		**ODE**	6206								
VPWM INVERTER READY		SFA 17.3/8.64										
CT6-60H(10:1)VT3-60H(20:1												

AC Induction Motor Performance Data
Record # 113577
Preliminary Data Sheet

Winding: 37WGZ714-R001	**Type:** 3746M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			5	**Full Load Torque**	22.45 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			15.6/7.8	**Breakdown Torque**	86.4 LB-FT
R.P.M.			1165	**Pull-up Torque**	57.4 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	62.6 LB-FT
NEMA Design Code	A	**KVA Code**	K	**Starting Current**	59.4 A
Service Factor (S.F.)			1.15	**No-load Current**	4.66 A
NEMA Nom. Eff.	89.5	**Power Factor**	67	**Line-line Res. @ 25ºC**	1.59 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	61°C
S.F. Amps			17.3/8.64	**Temp. Rise @ S.F. Load**	74°C
				Locked-rotor Power Factor	22.7
				Rotor inertia	1.14 lb-ft²

Load Characteristics 460 V, 60 Hz, 5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	29	47	59	67	71	74	69
Efficiency	83	88.6	89.7	89.5	88.5	87.2	88.9
Speed	1192	1184	1176	1166	1156	1144	1160
Line amperes	4.92	5.65	6.58	7.8	9.21	10.83	8.65


ABB Motors and Mechanical Inc.


WINDING # 37WGZ714

5 HP 3 PH 60 HZ 1165 RPM 460 V 3746M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=86.4 PU=57.4 LR=62.6 LRA=59.4




37LYG814
(717-735) = 18.63
(736-744) = 19.75
(745-750) = 20.50
(751-756) = 21.25
5.01
.26
3.12
GREASE FITTING
(EA. END)
Ø 10.28
NAMEPLATE
.31 KEY
2.38 LONG
Ø 8.500
8.497
Ø9.06
Ø 1.3750
1.3745
6 HOLES
Ø.43
5.50
.50
7.00
4.24
8.00
Ø9.56
8.00
2.26
45°
45°
10.03
5.25
5.19
LEAD
HOLE
Ø1.38
4 HOLES
.50-13 TAP
ON
Ø7.25 B.C.
4.25
4.25
6.76
4.75
9.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERSION OF ACAD TO SWD INOPC PKG 19
REV: E
VERSION: 02
REVISED: 10:36:23 10/11/2022
TDR: 000001197758
MODEL NO. 37LYG814
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
STD HORZ 213-5TC TEFC 37M W/EPACT SHOVE
37LYG814

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS