



SAFETY DATA SHEET

1. Identification

Important information	*** This Safety Data Sheet is only authorised for use by HP for HP Original products. Any unauthorised use of this Safety Data Sheet is strictly prohibited and may result in legal action being taken by HP. ***
Product identifier	HP Color LaserJet W2140Z-ZC Black Print Cartridge
Other means of identification	None.
Recommended use	This product is a toner preparation that is used in HP Color LaserJet Enterprise 5700 5800 6700 6800,HP Color LaserJet Enterprise X654,HP Color LaserJet Enterprise MFP X677,HP Color LaserJet Managed MFP E686,HP Color LaserJet Enterprise X55745,HP Color LaserJet Enterprise MFP X57945 series printers.
Recommended restrictions	None known.
Manufacturer/Importer/Supplier/Distributor information	HP Inc. 1501 Page Mill Road Palo Alto, CA 94304-1112 United States
Telephone	650-857-1501
HP Inc. health effects line (Toll-free within the US)	1-800-457-4209
(Direct)	1-760-710-0048
HP Inc. Customer Care Line	
(Toll-free within the US)	1-800-474-6836
(Direct)	1-208-323-2551
Email:	sustainability@hp.com

2. Hazard(s) identification

Physical hazards	Not classified.
Health hazards	Not classified.
Environmental hazards	Not classified.
OSHA defined hazards	Not classified.
Label elements	
Hazard symbol	None.
Signal word	None.
Hazard statement	Not available.
Precautionary statement	
Prevention	Not available.
Response	Not available.
Storage	Not available.
Disposal	Not available.
Hazard(s) not otherwise classified (HNOC)	None of the other ingredients in this preparation are classified as carcinogens according to ACGIH, EU, IARC, MAK, NTP or OSHA.
Supplemental information	This product is not classified as hazardous according to OSHA CFR 1910.1200 (HazCom 2012).

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
Styrene acrylate copolymer		CBI	<80
Wax	Wax	CBI	<15
Carbon Black		1333-86-4	<10

4. First-aid measures

Inhalation	Move person to fresh air immediately. If irritation persists, consult a physician.
Skin contact	Wash affected areas thoroughly with mild soap and water. Get medical attention if irritation develops or persists.
Eye contact	Flush thoroughly with water. If irritation occurs, get medical assistance.
Ingestion	Rinse mouth with water. Drink one to two glasses of water. If symptoms occur, consult a physician.
Most important symptoms/effects, acute and delayed	Not available.

5. Fire-fighting measures

Suitable extinguishing media	CO2, water, or dry chemical
Unsuitable extinguishing media	None known.
Specific hazards arising from the chemical	Like most organic material in powder form, toner can form explosive dust-air mixtures when finely dispersed in air.
Special protective equipment and precautions for firefighters	Not available.
Fire fighting equipment/instructions	If fire occurs in the printer, treat as an electrical fire.
Specific methods	None established.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Avoid contact with skin and eyes.
Methods and materials for containment and cleaning up	Slowly vacuum or sweep the material into a bag or other sealed container. Clean remainder with a damp cloth or vacuum cleaner. If a vacuum is used, the motor must be rated as dust explosion-proof. Fine powder can form explosive dust-air mixtures.
Environmental precautions	Keep out of waterways

7. Handling and storage

Precautions for safe handling	Avoid breathing dust or vapor. Avoid inhalation of dust and contact with skin and eyes. Use with adequate ventilation.
Conditions for safe storage, including any incompatibilities	Keep out of the reach of children. Keep tightly closed and dry. Store at room temperature. Store away from strong oxidizers.

8. Exposure controls/personal protection

Occupational exposure limits

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value
Carbon black (CAS 1333-86-4)	PEL	3.5 mg/m3

US. ACGIH Threshold Limit Values

Components	Type	Value	Form
Carbon black (CAS 1333-86-4)	TWA	3 mg/m3	Inhalable fraction.

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
Carbon black (CAS 1333-86-4)	TWA	0.1 mg/m3

Biological limit values	No biological exposure limits noted for the ingredient(s).
--------------------------------	--

Exposure guidelines	Carbon Black : OSHA (TWA/PEL): 3.5 mg/m ³ , ACGIH TLV (TWA) : 3 mg/m ³ , inhalable particulate matter
Appropriate engineering controls	None established.
Individual protection measures, such as personal protective equipment	
Eye/face protection	Not available.
Skin protection	
Hand protection	Not available.
Other	Not available.
Respiratory protection	Not available.
Thermal hazards	Not available.

9. Physical and chemical properties

Appearance	Fine powder
Physical state	Solid.
Form	solid
Color	Black.
Odor	Slight plastic odor
Odor threshold	Not available.
pH	Not applicable
Melting point/freezing point	Not available.
Initial boiling point and boiling range	Not applicable
Flash point	Not applicable
Evaporation rate	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Explosive limit - lower (%)	Not flammable
Explosive limit - upper (%)	Not available.
Vapor pressure	Not applicable
Relative vapor density	Not available.
Solubility(ies)	
Solubility (water)	Negligible in water. Partially soluble in toluene and xylene.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	No data available
Decomposition temperature	>392 °F (>200 °C)
Viscosity	Not applicable
Other information	
Density	Not available.
Oxidizing properties	No information available.
Percent volatile	Negligible
Softening point	176 - 266 °F (80 - 130 °C)
Specific gravity	1 - 1.2
VOC	Not applicable

10. Stability and reactivity

Reactivity	Not available.
Chemical stability	Stable under normal storage conditions.
Possibility of hazardous reactions	None.
Conditions to avoid	None.
Incompatible materials	Acids, Bases, Oxidizing agents, Reducing agents.

Hazardous decomposition products Carbon monoxide and carbon dioxide.

11. Toxicological information

Information on likely routes of exposure

Inhalation Not available.

Skin contact Not available.

Eye contact Not available.

Ingestion Not available.

Symptoms related to the physical, chemical and toxicological characteristics Not available.

Information on toxicological effects

Acute toxicity LD50 > 2000 mg/kg (Ingestion)

Components	Species	Test Results
------------	---------	--------------

Carbon Black (CAS 1333-86-4)

Acute

Oral

LD50	Rat	> 10000 mg/kg
------	-----	---------------

Skin corrosion/irritation Non-irritant

Serious eye damage/eye irritation Transient slight conjunctival irritation only

Respiratory or skin sensitization

Respiratory sensitization Non - Sensitizing

Skin sensitization Based on available data, the classification criteria are not met.

Germ cell mutagenicity Negative, does not indicate mutagenic potential (Ames Test: Salmonella typhimurium)

Carcinogenicity The IARC evaluated carbon black as a Group 2B carcinogen, for which there is inadequate human evidence, but sufficient animal evidence. The latter is based upon the development of lung tumors in rats receiving chronic inhalation exposure to powdered carbon black at levels that induce particle overload of the lung. However, there is a two-year inhalation study of a toner containing carbon black which demonstrated no association between toner exposure and tumor development in rats.

IARC Monographs. Overall Evaluation of Carcinogenicity

Carbon Black (CAS 1333-86-4) 2B Possibly carcinogenic to humans.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Not listed.

US. National Toxicology Program (NTP) Report on Carcinogens

Not listed.

Reproductive toxicity Not available.

Specific target organ toxicity - single exposure Not available.

Specific target organ toxicity - repeated exposure Reported pulmonary response upon chronic inhalation exposure in rats to a toner enriched in respirable-sized particles compared to commercial toner. No pulmonary change was found at 1 mg/m³ which is most relevant to potential human exposure. A minimal to mild degree of fibrosis was noted in 22% of the animals at 4 mg/m³, and a mild to moderate degree of fibrosis was observed in 92% of the animals at 16 mg/m³. These findings are attributed to "lung overloading", a generic response to excessive amounts of any dust retained in the lung for a prolonged interval.

Aspiration hazard Not available.

Further information No information available.

12. Ecological information

Ecotoxicity ErL50: >100 mg/l, Algae, 72.00 Hours

Product	Species		Test Results
W2140Z-ZC			
Aquatic			
Algae	ErL50	Algae	> 100 mg/l, 72 Hours
Crustacea	EL50	Crustacea	> 100 mg/l, 48 Hours
Fish	LL50	Fish	> 100 mg/l, 96 Hours
Persistence and degradability	Not available.		
Bioaccumulative potential	Not available.		
Mobility in soil	Not available.		
Other adverse effects	Not available.		

13. Disposal considerations

Disposal instructions	Do not shred toner cartridge, unless dust-explosion prevention measures are taken. Finely dispersed particles may form explosive mixtures in air. Dispose of in compliance with federal, state, and local regulations.
	HP's Planet Partners (trademark) supplies recycling program enables simple, convenient recycling of HP original inkjet and LaserJet supplies. For more information and to determine if this service is available in your location, please visit http://www.hp.com/recycle .

14. Transport information

DOT

UN number	Not regulated as dangerous goods.
UN proper shipping name	Not Regulated
Transport hazard class(es)	
Class	Not assigned.
Subsidiary risk	-
Packing group	Not assigned.
Environmental hazards	
Marine pollutant	No
Special precautions for user	Not assigned.

IATA

UN number	Not regulated as dangerous goods.
UN proper shipping name	Not Regulated
Transport hazard class(es)	
Class	Not assigned
Subsidiary risk	-
Packing group	Not assigned
Environmental hazards	No
Special precautions for user	Not assigned

IMDG

UN number	Not regulated as dangerous goods.
UN proper shipping name	Not Regulated
Transport hazard class(es)	
Class	Not assigned.
Subsidiary risk	-
Packing group	Not assigned.
Transport hazard class(es)	
Marine pollutant	No
EmS	Not assigned.
Special precautions for user	Not assigned.

ADR

UN number	Not regulated as dangerous goods.
UN proper shipping name	Not Regulated
Transport hazard class(es)	
Class	Not assigned
Subsidiary risk	-
Hazard No. (ADR)	Not assigned
Tunnel restriction code	Not assigned

Packing group Not assigned
Environmental hazards No
Soecial precautions for user Not assigned

Further information Not a dangerous good under DOT, IATA, ADR, IMDG, or RID.

15. Regulatory information

US federal regulations US EPA TSCA Inventory: All chemical substances in this product comply with all rules or orders under TSCA.

Toxic Substances Control Act (TSCA)

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Not listed.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical No

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

No intentionally added HAP substances.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA) Not regulated.

US state regulations

US. California. Candidate Chemicals List. Safer Consumer Products Regulations (Cal. Code Regs, tit. 22, 69502.3, subd. (a))

Carbon Black (CAS 1333-86-4)

California Proposition 65

California Proposition 65 - CRT: Listed date/Carcinogenic substance

Carbon Black (CAS 1333-86-4)

Listed: February 21, 2003

Regulatory information All chemical substances in this HP product have been notified or are exempt from notification under chemical substances notification laws in the following countries: US (TSCA), EU (EINECS/ELINCS), Switzerland, Canada (DSL/NDSL), Australia, Japan, Philippines, South Korea, New Zealand, and China.

Clean Air Act (CAA) No intentionally added HAP substances.

16. Other information, including date of preparation or last revision

Issue date 03-Apr-2023

Revision date 10-Sep-2023

Version # 02

Other information This SDS was prepared in accordance with USA OSHA Hazard Communications regulation (29 CFR 1910.1200).

Disclaimer

This Safety Data Sheet document is provided without charge to customers of HP. Data is the most current known to HP at the time of preparation of this document and is believed to be accurate. It should not be construed as guaranteeing specific properties of the products as described or suitability for a particular application. This document was prepared to the requirements of the jurisdiction specified in Section 1 above and may not meet regulatory requirements in other countries.

This safety data sheet is meant to convey information about HP inks (toners) provided in HP Original ink (toner) supplies. If our Safety Data Sheet has been provided to you with a refilled, remanufactured, compatible or other non-HP Original supply please be aware that the information contained herein was not meant to convey information about such products and there could be considerable differences from information in this document and the safety information for the product you purchased. Please contact the seller of the refilled, remanufactured or compatible supplies for applicable information, including information on personal protective equipment, exposure risks and safe handling guidance. HP does not accept refilled, remanufactured or compatible supplies in our recycling programs.

Explanation of abbreviations

ACGIH	American Conference of Governmental Industrial Hygienists
Acute Tox.	Acute toxicity
Aquatic Acute	Short-term (acute) aquatic hazard
Aquatic Chronic	Long-term (chronic) aquatic hazard
Asp. Tox.	Aspiration hazard
Carc.	Carcinogenicity
CAS	Chemical Abstracts Service
CERCLA	Comprehensive Environmental Response Compensation and Liability Act
CFR	Code of Federal Regulations
COC	Cleveland Open Cup
DOT	Department of Transportation
EPCRA	Emergency Planning and Community Right-to-Know Act (aka SARA)
Eye Dam.	Serious eye damage
Eye Irrit.	Eye Irritation
Flam. Liq.	Flammable liquids
Flam. Sol.	Flammable solids
Lact.	Effects on or via lactation
Muta.	Germ cell mutagenicity
IARC	International Agency for Research on Cancer
NIOSH	National Institute for Occupational Safety and Health
NTP	National Toxicology Program
OSHA	Occupational Safety and Health Administration
Ox. Liq.	Oxidising liquids
Ozone	Hazardous to the ozone layer
PEL	Permissible Exposure Limit
Press. Gas	Gases under pressure
RCRA	Resource Conservation and Recovery Act
REC	Recommended
REL	Recommended Exposure Limit
Repr.	Reproductive toxicity
Resp. Sens.	Respiratory sensitization
SARA	Superfund Amendments and Reauthorization Act of 1986
Skin Corr.	Skin corrosion
Skin Irrit.	Skin irritation
Skin Sens.	Skin sensitization
STEL	Short-Term Exposure Limit
STOT RE	Specific target organ toxicity - repeated exposure
STOT SE	Specific target organ toxicity - single exposure
TCLP	Toxicity Characteristics Leaching Procedure
TLV	Threshold Limit Value
TSCA	Toxic Substances Control Act