DATA SHEET

Premium Efficiency Motor: **ODP150-18-444T,** **60 Hz**

WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net

Document Generated: 31-Mar-2025
Document ID:

Customer:

MOTOR INFORMATION

HP	150
RPM	1800
Phase	3
Frequency	60
Voltage	230/460
Frame Size	444/5T
Enclosure	ODP
Degree of Protection	IP23
Service Factor	1.15
Poles	4
Full Load Speed	1783
Insulation Class	F
Temp Rise	80˚C
NEMA Code Letter	G
Duty Cycle	S1 / Continuous
Slip	0.96%
NEMA Design	B
Moment of Inertia	39.487 lb.ft.^2
Locked Rotor Time (Hot)	12 seconds
Sound Pressure Level	90 dB(A)
Number of Starts	2 Cold / 1 Hot
Max Ambient Temperature	40˚C
Max Elevation	1000 m.a.s.l (3300 f.a.s.l)
Mounting	F1
Rotation	Bi-Directional
Area of Classification	Safe Area
Inverter Rating	10:1 CT / 20:1 VT
Standard	NEMA MG 1
Approvals	UL, CE

ADDITIONAL DATA

F2 Suitable	Yes
Shaft Material	AISI 1045
Connection Diagram	12 Lead Delta
Approximate Weight	1547 lbs.

EFFICIENCY/POWER FACTOR

LOAD	EFF	P. F.
100%	95.8 %	0.87
75%	96.1 %	0.84
50%	95.8 %	0.74

TORQUE

FULL LOAD	LRT	BDT
434.8 lb.ft.	194 %	316 %

AMPERAGE INFORMATION

	230V	460V
Full Load Amps	330.8A	165.4A
Locked Rotor Amps	2346A	1173A
No Load Current	103.4A	51.7A
Usable at 208V	183.56A	

BEARING INFORMATION


DE Bearing	6320
ODE Bearing	6316
Grease Type	Mobil Polyrex EM
DE Regreasing Interval	2400 Hours
ODE Regreasing Interval	3600 Hours
Grease Quantity	51g/33g

This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization

MOTOR DRAWING

Premium Efficiency Motor: **ODP150-18-444T**

WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net



DIMENSION - INCHES

MOUNTING					A	B	C	D	G	P	O	T	AB
E	2F1	2F2	H	BA									
9	14.5	16.5	0.81	7.5	22.3	22.9	39.45	11	1.37	23.42	22.7	3	20.6

SHAFT & KEY				
S	ES	R	N-W	U
0.875	6.91	2.88	8.5	3.375

T-BOX	GND
AA	LUG
3	M12*P1.75

This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization

PERFORMANCE CURVES


Premium Efficiency Motor: **ODP150-18-444T**


WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net

Document Generated:	31-Mar-2025
Document ID:	

Customer:

Motor Type	ODP					
Output Rating (HP)	150		FL Speed	1783		
Full Load Torque	434.8	lb.ft	LRT (%FLT)	194	460 volt FLA	165.4
Rotor Wk^2	0.958	lb-ft^2	BDT (%FLT)	316	230 volt FLA	330.8





This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization.

NAMEPLATE / WIRING

Premium Efficiency Motor: **ODP150-18-444T**

WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net

Document Generated:	31-Mar-2025
Document ID:	

Customer:

SAMPLE NAMEPLATE DATA

WORLDWIDE CC306B


OPEN DRIP PROOF
3 PHASE MOTOR


NEMA Premium ENERGY c UL us E309286 CE

Model :		Encl :		SN :		
HP :	Poles :	FR:	Ins :	IP23	Max Amb 40℃	Duty:Cont

Hz :	CODE :	Hz :	Design :
Volts :	P.F :	Volts :	DE BRG :
Amps :	Eff :	Amps :	ODE BRG :
RPM :	S.F :	RPM :	WT :
		S.F :	Date :

WorldWide Electric Corporation





Model:	ODP150-18-444T			**Encl:**	ODP				
HP:	150	**Poles:**	4	**Frame**	444/5T	**Ins Cl:**	F	**IP**	IP23
Hz:	60	**Code:**	G	**Hz:**	50	**Design:**	B		
Volts:	230/460	**P.F.:**	0.87	**Volts:**	190/380	**DE Brg:**	6320		
Amps:	330.8/165.4	**Eff:**	95.8%	**Amps:**	397/198.5	**ODE Brg:**	6316		
RPM:	1783	**S.F.:**	1.15	**RPM:**	1460	**WT:**	1547 lbs.		
				S.F.:	1.0				

This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization