ABB BALDOR RELIANCE

Customer information packet

VPECP4114T

52M 2P TEFC VER 326VP CP 32-6 DRIPCOVER
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 2:22:21 PM

Specifications

Enclosure	TEFC
Frame	326VP
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	50.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	CSA
	CSA EEV
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	56.000 A @ 460.0 V
	122.000 A @ 208.0 V
	112.000 A @ 230.0 V
Design Code	A
Drip Cover	Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None

Part Detail

Revision	G
Type	AC
Mech. spec.	12K58
Base	
Status	PRD/A
Elec. spec.	12WGY291
Layout	12LYK058
Eff. date	12-09-2025
CD Diagram	CD0180
Poles	02
Leads	9#8
Proprietary	False
Created date	05-29-2018

Haz Area Temp Code	T3
Heater Indicator	No Heater
High Voltage Full Load Amps	56.0 a
Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	H
Lifting Lugs	Vertical Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	5400 rpm
Motor Lead Quantity/Wire Size	9 @ 8 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1252M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	34.71 IN
Power Factor	90
Product Family	Super-E Chemical Processing
Pulley End Bearing Type	Thrust
Pulley Shaft Indicator	P-Base Groove & Key
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3540 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3241

CAT.NO.	VPECP4114T		**P/N**				**ENCLOSURE**	TEFC					
SPEC.	12K058Y291G2	**CC**	010A	**FRAME**	326VP		**S/N**						
HP	50		**CLASS**	F	**HZ**	60	**DES**	A					
RPM	3540		**RPM MAX**	5400	**PH**	3	**KVA-CODE**	H					
VOLT	230/460			**MOTOR WEIGHT**	587								
AMP	112/56		**SER.F.**	1.15	**PF**	90	**ODE BRG**	6311	**DE BRG**	7311			
RATING	40C AMB-CONT			**NEMA-NOM-EFF**	93		**GREASE**	POLYREX EM					
					INV.TYPE	PWM							
TEMP CODE	T3		**INVERTER-TEMP-CODE**	200									
TEMP =	200	**C HP FR**	60		**C HP TO**	90							
CT HZ FROM	6		**CT HZ TO**	60									
HTR-VOLTS		**HTR-AMPS**		**HTR-WATTS**			**MAX. SPACE HEATER TEMP.**				**VT HZ FROM**	3	**VT HZ TO** 60

AC Induction Motor Performance Data
Record # 70997
Typical performance - not guaranteed values

Winding: 12WGY291-R044	**Type:** 1252M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			50	**Full Load Torque**	74.4 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			112/56	**Breakdown Torque**	292 LB-FT
R.P.M.			3540	**Pull-up Torque**	112 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	139 LB-FT
NEMA Design Code	A	**KVA Code**	H	**Starting Current**	408 A
Service Factor (S.F.)			1.15	**No-load Current**	14.9 A
NEMA Nom. Eff.	93	**Power Factor**	90	**Line-line Res. @ 25ºC**	0.11257 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	77°C
S.F. Amps				**Temp. Rise @ S.F. Load**	95°C
				Locked-rotor Power Factor	20.9
				Rotor inertia	4.07 lb-ft²

Load Characteristics 460 V, 60 Hz, 50 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	66	82	88	90	91	90	91
Efficiency	91.1	93.8	94.2	93.9	93.2	92.3	93.5
Speed	3584.1	3571.8	3558.2	3544.1	3528.2	3511.2	3535
Line amperes	20.4	30.8	42.9	55.8	69.5	84.6	64


ABB Motors and Mechanical Inc.


WINDING # 12WGY291

50 HP 3 PH 60 HZ 3540 RPM 460 V 1252M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=292 PU=112 LR=139 LRA=408





12LYK058
(1232-1272) = 34.71
16.55
4.02
4.50
4.44
1.01
.25
GREASE FITTING (EA END)
.38 KEY 3.75 LONG
.750
.745
.377
.375
Ø16.49
1.250
1.245
1.625
1.624
13.505
13.500
LABEL LB1182
.50-13 TAP GND LOC.
GREASE RELIEF (EA. END)
17.43
13.76
8.50
45°
45°
DRAIN HOLE
19.70
LEAD HOLE 2.00 NPT
11.33
4 HOLES Ø.69 ON Ø14.75 B.C.
EXTERNAL OPP DRIVE END SLINGER
EXTERNAL DRIVE END SLINGER
OPPOSITE DRIVE END
DRIVE END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT DRW FROM AUTOCAD TO SWD
REV: H
VERSION: 07
REVISED: 03:43:20 11/10/2023
TDR: 000001220227
MODEL NO. 12LYK058
REF: -
BY: USALMAZ
B
BALDOR
VERT TEFC 324-6VP CP 2 PL, 311 THRUST PAC
12LYK058

CD0180







NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1