



SAFETY DATA SHEET

1. Identification

Important information	*** This Safety Data Sheet is only authorised for use by HP for HP Original products. Any unauthorised use of this Safety Data Sheet is strictly prohibited and may result in legal action being taken by HP. ***
Product identifier	4K0T2Series
Other means of identification	None.
Recommended use	Inkjet printing
Recommended restrictions	None known.
Manufacturer/Importer/Supplier/Distributor information	HP Inc. 1501 Page Mill Road Palo Alto, CA 94304-1112 United States
Telephone	650-857-1501
HP Inc. health effects line (Toll-free within the US)	1-800-457-4209
(Direct)	1-760-710-0048
HP Inc. Customer Care Line	
(Toll-free within the US)	1-800-474-6836
(Direct)	1-208-323-2551
Email:	sustainability@hp.com

2. Hazard(s) identification

Physical hazards	Not classified.
Health hazards	Not classified.
Environmental hazards	Not classified.
OSHA defined hazards	Not classified.
Label elements	
Hazard symbol	None.
Signal word	None.
Hazard statement	Not available.
Precautionary statement	
Prevention	Not available.
Response	Not available.
Storage	Not available.
Disposal	Not available.
Hazard(s) not otherwise classified (HNOC)	Potential routes of overexposure to this product are skin and eye contact. Inhalation of vapor and ingestion are not expected to be significant routes of exposure for this product under normal use conditions. Complete toxicity data are not available for this specific formulation.
Supplemental information	None.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
Water		7732-18-5	65-85

Chemical name	Common name and synonyms	CAS number	%
Cyclo Amide*		Proprietary*	<10
Pigment Yellow*		Proprietary*	<5
2,4,7,9-Tetramethyl-5-decyne-4,7-diol, ethoxylated		9014-85-1	<1

Composition comments This ink supply contains an aqueous ink formulation. This product has been evaluated using criteria specified in 29 CFR 1910.1200 (Hazard Communication Standard).
*Proprietary

4. First-aid measures

Inhalation Move to fresh air. If symptoms persist, get medical attention.

Skin contact Wash affected areas thoroughly with mild soap and water. Get medical attention if irritation develops or persists.

Eye contact Do not rub eyes. Immediately flush with large amounts of clean, warm water (low pressure) for at least 15 minutes or until particles are removed. If irritation persists get medical attention.

Ingestion If ingestion of a large amount does occur, seek medical attention.

Most important symptoms/effects, acute and delayed Not available.

5. Fire-fighting measures

Suitable extinguishing media Dry chemical, CO2, water spray or regular foam.

Unsuitable extinguishing media None known.

Specific hazards arising from the chemical Not applicable.

Special protective equipment and precautions for firefighters Not available.

Specific methods None established.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures Wear appropriate personal protective equipment.

Methods and materials for containment and cleaning up Dike the spilled material, where this is possible. Absorb with inert absorbent such as dry clay, sand or diatomaceous earth, commercial sorbents, or recover using pumps.

Environmental precautions Do not let product enter drains. Do not flush into surface water or sanitary sewer system.

7. Handling and storage

Precautions for safe handling Avoid contact with skin, eyes and clothing.

Conditions for safe storage, including any incompatibilities Keep out of the reach of children. Keep away from excessive heat or cold.

8. Exposure controls/personal protection

Biological limit values No biological exposure limits noted for the ingredient(s).

Exposure guidelines Exposure limits have not been established for this product.

Appropriate engineering controls Use in a well ventilated area.

Individual protection measures, such as personal protective equipment

Eye/face protection Not available.

Skin protection

Hand protection Not available.

Other Not available.

Respiratory protection Not available.

Thermal hazards Not available.

General hygiene considerations Handle in accordance with good industrial hygiene and safety practice.

9. Physical and chemical properties

Appearance

Physical state	Liquid.
Form	Not available.
Color	Yellow

Odor Not available.

Odor threshold Not available.

pH 9 - 10

Melting point/freezing point Not available.

Initial boiling point and boiling range Not available.

Flash point >230.0 °F (>110.0 °C) Pensky-Martens Closed Cup US EPA Method 1020

Evaporation rate Not available.

Flammability (solid, gas) Not available.

Upper/lower flammability or explosive limits

Explosive limit - lower (%) Not available.

Explosive limit - upper (%) Not available.

Vapor pressure Not available.

Relative vapor density Not available.

Solubility(ies)

Solubility (water) Not available.

Partition coefficient (n-octanol/water) Not available.

Auto-ignition temperature Not available.

Decomposition temperature Not available.

Viscosity Not available.

Other information For other VOC regulatory data/information see Section 15.

Density 1.04 g/cm³

Oxidizing properties Not determined

VOC <7 g/L

10. Stability and reactivity

Reactivity Not available.

Chemical stability Stable under recommended storage conditions.

Possibility of hazardous reactions Will not occur.

Conditions to avoid Not available.

Incompatible materials Incompatible with strong bases and oxidizing agents.

Hazardous decomposition products Upon decomposition, this product may yield gaseous nitrogen oxides, carbon monoxide, carbon dioxide and/or low molecular weight hydrocarbons.

11. Toxicological information

Information on likely routes of exposure

Inhalation Under normal conditions of intended use, this material is not expected to be an inhalation hazard.

Skin contact Contact with skin may result in mild irritation.

Eye contact Contact with eyes may result in mild irritation.

Ingestion Health injuries are not known or expected under normal use.

Symptoms related to the physical, chemical and toxicological characteristics Not available.

Information on toxicological effects

Acute toxicity Based on available data, the classification criteria are not met.

Components	Species	Test Results
2,4,7,9-Tetramethyl-5-decyne-4,7-diol, ethoxylated (CAS 9014-85-1)		
Acute		
Inhalation		
LC50	Rat	20 mg/l, 1 h Dusts, mists and fumes. The data are derived from the evaluations or test results achieved with similar products (conclusion by analogy).
Oral		
LD50	Rat	6300 mg/kg
Skin corrosion/irritation	Based on available data, the classification criteria are not met.	
Irritation Corrosion - Skin		
2,4,7,9-Tetramethyl-5-decyne-4,7-diol, ethoxylated	Not irritating, The data are derived from the evaluations or test results achieved with similar products (conclusion by analogy). Test Duration: 24 h	
Serious eye damage/eye irritation	Based on available data, the classification criteria are not met.	
Eye		
2,4,7,9-Tetramethyl-5-decyne-4,7-diol, ethoxylated	Risk of serious damage to eyes, The data are derived from the evaluations or test results achieved with similar products (conclusion by analogy). Species: Rabbit	
Respiratory or skin sensitization		
Respiratory sensitization	Based on available data, the classification criteria are not met.	
Skin sensitization	Based on available data, the classification criteria are not met.	
Sensitization		
2,4,7,9-Tetramethyl-5-decyne-4,7-diol, ethoxylated	May cause sensitization by skin contact.	
Germ cell mutagenicity	Based on available data, the classification criteria are not met.	
Carcinogenicity		
2,4,7,9-Tetramethyl-5-decyne-4,7-diol, ethoxylated	Ames (OECD 471), Chromosomal aberration (OECD 473), gene mutation (OECD 476), negative. The data are derived from the evaluations or test results achieved with similar products (conclusion by analogy).	
IARC Monographs. Overall Evaluation of Carcinogenicity		
Not listed.		
OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)		
Not listed.		
US. National Toxicology Program (NTP) Report on Carcinogens		
Not listed.		
Reproductive toxicity	Based on available data, the classification criteria are not met.	
Specific target organ toxicity - single exposure	Based on available data, the classification criteria are not met.	
Specific target organ toxicity - repeated exposure	Based on available data, the classification criteria are not met.	
Aspiration hazard	Based on available data, the classification criteria are not met.	
Further information	Complete toxicity data are not available for this specific formulation Refer to Section 2 for potential health effects and Section 4 for first aid measures.	

12. Ecological information

Aquatic toxicity Not expected to be harmful to aquatic organisms.

Ecotoxicity

Product	Species	Test Results
4K0T2Series		
Aquatic		
<i>Acute</i>		
Fish	LC50	Fathead minnow (<i>Pimephales promelas</i>) > 750 mg/l, 96 hours

Components	Species	Test Results
2,4,7,9-Tetramethyl-5-decyne-4,7-diol, ethoxylated (CAS 9014-85-1)		
<i>Acute</i>		
	LC50	Scophthalmus maximus (turbot) 52 mg/l, 96 h
Aquatic		
<i>Acute</i>		
Crustacea	EC50	Daphnia magna 88 mg/l, 48 h The data are derived from the evaluations or test results achieved with similar products (conclusion by analogy). (OECD 202)
	LC50	Acartia tonsa 166 mg/l, 48 h
Fish	LC50	<i>Pimephales promelas</i> 36 mg/l, 96 h The data are derived from the evaluations or test results achieved with similar products (conclusion by analogy). (OECD 203)

Persistence and degradability Not available.

Bioaccumulative potential Not available.

Mobility in soil Not available.

Other adverse effects Not available.

13. Disposal considerations

Disposal instructions Do not allow this material to drain into sewers/water supplies. Dispose of waste material according to Local, State, Federal, and Provincial Environmental Regulations.

HP's Planet Partners (trademark) supplies recycling program enables simple, convenient recycling of HP original inkjet and LaserJet supplies. For more information and to determine if this service is available in your location, please visit <http://www.hp.com/recycle>.

14. Transport information**DOT**

UN number Not regulated as dangerous goods.
UN proper shipping name Not Regulated
Transport hazard class(es)
Class Not assigned.
Subsidiary risk -
Packing group Not assigned.
Environmental hazards
Marine pollutant No
Special precautions for user Not assigned.

IATA

UN number Not regulated as dangerous goods.
UN proper shipping name Not Regulated
Transport hazard class(es)
Class Not assigned
Subsidiary risk -
Packing group Not assigned
Environmental hazards No
Special precautions for user Not assigned

IMDG

UN number Not regulated as dangerous goods.
UN proper shipping name Not Regulated

Transport hazard class(es)
Class Not assigned.
Subsidiary risk -
Packing group Not assigned.
Transport hazard class(es)
Marine pollutant No
EmS Not assigned.
Special precautions for user Not assigned.

ADR

UN number Not regulated as dangerous goods.
UN proper shipping name Not Regulated
Transport hazard class(es)
Class Not assigned
Subsidiary risk -
Hazard No. (ADR) Not assigned
Tunnel restriction code Not assigned
Packing group Not assigned
Environmental hazards No
Soecial precautions for user Not assigned

Further information Not a dangerous good under DOT, IATA, ADR, IMDG, or RID.

Transport in bulk according to Annex II of MARPOL73/78 and the IBC code: Not applicable.

15. Regulatory information

US federal regulations US TSCA 12(b): Does not contain listed chemicals.

Toxic Substances Control Act (TSCA)

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Not listed.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical No

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

No intentionally added HAP substances.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA) Not regulated.

Other information

VOC content (less water, less exempt compounds) = <39 g/L (U.S. requirement, not for emissions)
VOC data based on formulation (Organic compounds minus solids)

Regulatory information

HP complies with chemical regulatory requirements in chemical substance notification laws, where applicable. All chemical substances are notified or exempt from notification or listed in the inventory as existing substances in the following countries: US (TSCA), Canada (DSL/NDSL), Australia (AICIS), Japan (ISHL, ENCS), Philippines (PICCS), New Zealand (NZIoC) and China (IECSC). For guidance on importation and/or additional requirements for registration schemes such as EAEU, EU, South Korea, Turkey, UK, India and Taiwan, please contact the Sustainability and Compliance Center (sustainability@hp.com).

Clean Air Act (CAA) No intentionally added HAP substances.

16. Other information, including date of preparation or last revision

Issue date	14-Nov-2023
Version #	01
Other information	This SDS was prepared in accordance with USA OSHA Hazard Communications regulation (29 CFR 1910.1200).
Disclaimer	<p>This Safety Data Sheet document is provided without charge to customers of HP. Data is the most current known to HP at the time of preparation of this document and is believed to be accurate. It should not be construed as guaranteeing specific properties of the products as described or suitability for a particular application. This document was prepared to the requirements of the jurisdiction specified in Section 1 above and may not meet regulatory requirements in other countries.</p> <p>This safety data sheet is meant to convey information about HP inks (toners) provided in HP Original ink (toner) supplies. If our Safety Data Sheet has been provided to you with a refilled, remanufactured, compatible or other non-HP Original supply please be aware that the information contained herein was not meant to convey information about such products and there could be considerable differences from information in this document and the safety information for the product you purchased. Please contact the seller of the refilled, remanufactured or compatible supplies for applicable information, including information on personal protective equipment, exposure risks and safe handling guidance. HP does not accept refilled, remanufactured or compatible supplies in our recycling programs.</p>
Revision information	1. Product and Company Identification: Alternate Trade Names

Explanation of abbreviations

ACGIH	American Conference of Governmental Industrial Hygienists
Acute Tox.	Acute toxicity
Aquatic Acute	Short-term (acute) aquatic hazard
Aquatic Chronic	Long-term (chronic) aquatic hazard
Asp. Tox.	Aspiration hazard
Carc.	Carcinogenicity
CAS	Chemical Abstracts Service
CERCLA	Comprehensive Environmental Response Compensation and Liability Act
CFR	Code of Federal Regulations
COC	Cleveland Open Cup
DOT	Department of Transportation
EPCRA	Emergency Planning and Community Right-to-Know Act (aka SARA)
Eye Dam.	Serious eye damage
Eye Irrit.	Eye Irritation
Flam. Liq.	Flammable liquids
Flam. Sol.	Flammable solids
Lact.	Effects on or via lactation
Muta.	Germ cell mutagenicity
IARC	International Agency for Research on Cancer
NIOSH	National Institute for Occupational Safety and Health
NTP	National Toxicology Program
OSHA	Occupational Safety and Health Administration
Ox. Liq.	Oxidising liquids
Ozone	Hazardous to the ozone layer
PEL	Permissible Exposure Limit
Press. Gas	Gases under pressure
RCRA	Resource Conservation and Recovery Act
REC	Recommended
REL	Recommended Exposure Limit
Repr.	Reproductive toxicity
Resp. Sens.	Respiratory sensitization
SARA	Superfund Amendments and Reauthorization Act of 1986
Skin Corr.	Skin corrosion
Skin Irrit.	Skin irritation
Skin Sens.	Skin sensitization
STEL	Short-Term Exposure Limit
STOT RE	Specific target organ toxicity - repeated exposure
STOT SE	Specific target organ toxicity - single exposure
TCLP	Toxicity Characteristics Leaching Procedure
TLV	Threshold Limit Value
TSCA	Toxic Substances Control Act
VOC	Volatile Organic Compounds