



SAFETY DATA SHEET

1. Identification

Product identifier F9J64Series
Other means of identification Not available.
Recommended use Inkjet printing
Recommended restrictions None known.
Company identification HP
1501 Page Mill Road
Palo Alto, CA 94304-1112
United States
Telephone 650-857-5020

HP health effects line
(Toll-free within the US) 1-800-457-4209
(Direct) 1-760-710-0048
HP Customer Care Line
(Toll-free within the US) 1-800-474-6836
(Direct) 1-208-323-2551
Email: hpcustomer.inquiries@hp.com

2. Hazard(s) identification

Physical hazards Not classified.
Health hazards Not classified.
Environmental hazards Not classified.
OSHA defined hazards Not classified.

Label elements

Hazard symbol None.
Signal word None.
Hazard statement Not available.
Precautionary statement
Prevention Not available.
Response Not available.
Storage Not available.
Disposal Not available.

Hazard(s) not otherwise classified (HNOC) Potential routes of overexposure to this product are skin and eye contact. Inhalation of vapor and ingestion are not expected to be significant routes of exposure for this product under normal use conditions. Complete toxicity data are not available for this specific formulation. Carbon black is classified by the IARC as a Group 2B carcinogen (the substance is possibly carcinogenic to humans). Carbon black in this preparation, due to its bound form, does not present this carcinogenic risk. None of the other ingredients in this preparation are classified as carcinogens according to ACGIH, EU, IARC, MAK, NTP or OSHA.

Supplemental information This product is not classified as hazardous according to OSHA CFR 1910.1200 (HazCom 2012).

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
Water		7732-18-5	70-80
2-pyrrolidone		616-45-5	< 15
Modified carbon black 11		Proprietary	<5
Glycerol		56-81-5	<2.5

Composition comments This ink supply contains an aqueous ink formulation.
This product has been evaluated using criteria specified in 29 CFR 1910.1200 (Hazard Communication Standard).

4. First-aid measures

Inhalation Move to fresh air. If symptoms persist, get medical attention.
Skin contact Wash affected areas thoroughly with mild soap and water. If irritation persists get medical attention.
Eye contact Do not rub eyes. Immediately flush with large amounts of clean, warm water (low pressure) for at least 15 minutes or until particles are removed. If irritation persists get medical attention.
Ingestion If ingestion of a large amount does occur, seek medical attention.
Most important symptoms/effects, acute and delayed Not available.

5. Fire-fighting measures

Suitable extinguishing media CO2, water, dry chemical, or foam
Unsuitable extinguishing media None known.
Specific hazards arising from the chemical Not applicable.
Special protective equipment and precautions for firefighters Not available.
Specific methods None established.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures Wear appropriate personal protective equipment.
Methods and materials for containment and cleaning up Dike the spilled material, where this is possible. Absorb with inert absorbent such as dry clay, sand or diatomaceous earth, commercial sorbents, or recover using pumps.
Environmental precautions Do not let product enter drains. Do not flush into surface water or sanitary sewer system.

7. Handling and storage

Precautions for safe handling Avoid contact with skin, eyes and clothing.
Conditions for safe storage, including any incompatibilities Keep out of the reach of children. Keep away from excessive heat or cold.

8. Exposure controls/personal protection

Occupational exposure limits

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value	Form
Glycerol (CAS 56-81-5)	PEL	5 mg/m3 15 mg/m3	Respirable fraction. Total dust.

Biological limit values No biological exposure limits noted for the ingredient(s).
Exposure guidelines Exposure limits have not been established for this product.
Appropriate engineering controls Use in a well ventilated area.
Individual protection measures, such as personal protective equipment
Eye/face protection Not available.
Skin protection
Hand protection Not available.
Other Not available.
Respiratory protection Not available.
Thermal hazards Not available.

9. Physical and chemical properties

Appearance

Physical state Not available.

Color Black.

Odor Not available.

Odor threshold Not available.

pH 9.2

Melting point/freezing point Not available.

Initial boiling point and boiling range Not determined

Flash point > 200.0 °F (> 93.3 °C) Pensky-Martens Closed Cup

Evaporation rate Not determined

Flammability (solid, gas) Not available.

Upper/lower flammability or explosive limits

Flammability limit - lower (%) Not determined

Flammability limit - upper (%) Not available.

Explosive limit - lower (%) Not available.

Explosive limit - upper (%) Not available.

Vapor pressure Not determined

Solubility(ies)

Solubility (water) Soluble in water

Partition coefficient (n-octanol/water) Not available.

Auto-ignition temperature Not determined

Decomposition temperature Not available.

Viscosity Not available.

Other information

Specific gravity 1 - 1.1

Other information For other VOC regulatory data/information see Section 15.

VOC (Weight %) < 240 g/l

10. Stability and reactivity

Reactivity Not available.

Chemical stability Stable under recommended storage conditions.

Possibility of hazardous reactions Will not occur.

Conditions to avoid Not available.

Incompatible materials Incompatible with strong bases and oxidizing agents.

Hazardous decomposition products Upon decomposition, this product may yield gaseous nitrogen oxides, carbon monoxide, carbon dioxide and/or low molecular weight hydrocarbons. hydrogen fluoride, fluorinated hydrocarbons

11. Toxicological information

Symptoms related to the physical, chemical and toxicological characteristics Not available.

Information on toxicological effects

Acute toxicity Based on available data, the classification criteria are not met.

Skin corrosion/irritation	Based on available data, the classification criteria are not met.
Serious eye damage/eye irritation	Based on available data, the classification criteria are not met.
Respiratory or skin sensitization	
Respiratory sensitization	Based on available data, the classification criteria are not met.
Skin sensitization	Based on available data, the classification criteria are not met.
Germ cell mutagenicity	Based on available data, the classification criteria are not met.
Carcinogenicity	Based on available data, the classification criteria are not met.

Carbon black is classified as a carcinogen by the IARC (possibly carcinogenic to humans, Group 2B) and by the State of California under Proposition 65. In their evaluations of carbon black, both organizations indicate that exposure to carbon black, per se, does not occur when it remains bound within a product matrix, specifically, rubber, ink, or paint. Carbon black is present only in a bound form in this preparation.

Reproductive toxicity	Based on available data, the classification criteria are not met.
Specific target organ toxicity - single exposure	Based on available data, the classification criteria are not met.
Specific target organ toxicity - repeated exposure	Based on available data, the classification criteria are not met.
Aspiration hazard	Based on available data, the classification criteria are not met.
Further information	Complete toxicity data are not available for this specific formulation Refer to Section 2 for potential health effects and Section 4 for first aid measures.

Components	Species	Test Results
2-pyrrolidone (CAS 616-45-5)		
Acute		
<i>Oral</i>		
LD50	Guinea pig	6500 mg/kg
	Rat	6500 mg/kg

12. Ecological information

Aquatic toxicity Not expected to be harmful to aquatic organisms.

Ecotoxicity

Product	Species	Test Results
F9J64Series (CAS Mixture)		
Aquatic		
<i>Acute</i>		
Fish	LC50	Fathead minnow (<i>Pimephales promelas</i>) > 750 mg/l, 96 hours

Components	Species	Test Results
2-pyrrolidone (CAS 616-45-5)		
Aquatic		
Crustacea	EC50	Water flea (<i>Daphnia pulex</i>) 13.21 mg/l, 48 hours
Glycerol (CAS 56-81-5)		
Aquatic		
Fish	LC50	Rainbow trout, donaldson trout (<i>Oncorhynchus mykiss</i>) 51000 - 57000 mg/l, 96 hours

Persistence and degradability Not available.

Bioaccumulative potential Not available.

Partition coefficient n-octanol / water (log Kow)

2-pyrrolidone	-0.85
Glycerol	-1.76

Mobility in soil Not available.

Other adverse effects Not available.

13. Disposal considerations

Disposal instructions

Do not allow this material to drain into sewers/water supplies.
Dispose of waste material according to Local, State, Federal, and Provincial Environmental Regulations.

HP's Planet Partners (trademark) supplies recycling program enables simple, convenient recycling of HP original inkjet and LaserJet supplies. For more information and to determine if this service is available in your location, please visit <http://www.hp.com/recycle>.

14. Transport information

DOT

Not regulated as dangerous goods.

IATA

Not regulated as dangerous goods.

IMDG

Not regulated as dangerous goods.

ADR

Not regulated as dangerous goods.

Further information

Not a dangerous good under DOT, IATA, ADR, IMDG, or RID.

15. Regulatory information

US federal regulations

US TSCA 12(b): Does not contain listed chemicals.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not listed.

Superfund Amendments and Reauthorization Act of 1986 (SARA)**Hazard categories**

Immediate Hazard - No
Delayed Hazard - No
Fire Hazard - No
Pressure Hazard - No
Reactivity Hazard - No

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312

No

Hazardous chemical**Other federal regulations****Safe Drinking Water Act (SDWA)**

Not regulated.

US state regulations**US. Massachusetts RTK - Substance List**

2-pyrrolidone (CAS 616-45-5)

Glycerol (CAS 56-81-5)

US. New Jersey Worker and Community Right-to-Know Act

Glycerol (CAS 56-81-5)

US. Pennsylvania Worker and Community Right-to-Know Law

2-pyrrolidone (CAS 616-45-5)

Glycerol (CAS 56-81-5)

US. Rhode Island RTK

Not regulated.

US. California Proposition 65

Not Listed.

Other information VOC content (less water, less exempt compounds) = < 958 g/L (U.S. requirement, not for emissions)
VOC data based on formulation (Organic compounds minus solids)

Regulatory information All chemical substances in this HP product have been notified or are exempt from notification under chemical substances notification laws in the following countries: US (TSCA), EU (EINECS/ELINCS), Switzerland, Canada (DSL/NDSL), Australia, Japan, Philippines, South Korea, New Zealand, and China.

16. Other information, including date of preparation or last revision

Issue date 07-Aug-2015

Revision date 05-Dec-2015

Version # 02

Disclaimer This Safety Data Sheet document is provided without charge to customers of HP. Data is the most current known to HP at the time of preparation of this document and is believed to be accurate. It should not be construed as guaranteeing specific properties of the products as described or suitability for a particular application. This document was prepared to the requirements of the jurisdiction specified in Section 1 above and may not meet regulatory requirements in other countries.

Manufacturer information HP
1501 Page Mill Road
Palo Alto, CA 94304-1112 US
Direct 1-650-857-5020

Explanation of abbreviations

ACGIH	American Conference of Governmental Industrial Hygienists
CAS	Chemical Abstracts Service
CERCLA	Comprehensive Environmental Response Compensation and Liability Act
CFR	Code of Federal Regulations
COC	Cleveland Open Cup
DOT	Department of Transportation
EPCRA	Emergency Planning and Community Right-to-Know Act (aka SARA)
IARC	International Agency for Research on Cancer
NIOSH	National Institute for Occupational Safety and Health
NTP	National Toxicology Program
OSHA	Occupational Safety and Health Administration
PEL	Permissible Exposure Limit
RCRA	Resource Conservation and Recovery Act
REC	Recommended
REL	Recommended Exposure Limit
SARA	Superfund Amendments and Reauthorization Act of 1986
STEL	Short-Term Exposure Limit
TCLP	Toxicity Characteristics Leaching Procedure
TLV	Threshold Limit Value
TSCA	Toxic Substances Control Act
VOC	Volatile Organic Compounds