



PIP® Kilimanjaro™

Full Brim Hard Hat with HDPE Shell, 4-Point Textile Suspension and Pin-Lock Adjustment

- Lightweight shell made with UV stabilized High Density Polyethylene (HDPE) reduces worker fatigue
- 4-Point quick release suspension with strong textile straps and crown comfort pad provides a comfortable and secure fit
- SURE LOCK wheel adjustment system for one hand size adjustments
- Precise height adjustment settings to ensure proper depth
- Low nape strap provides a secure fit, allowing the hard hat to stay on your head even when workers are looking down or bending over
- Non-chaffing, replaceable foam sweatband for maximum sweat absorption

Applications

- Construction Applications
- Road Work
- Excavation
- Industrial Applications

Technical Data

Color	Hi-Vis Orange, Yellow, Sky Blue, Royal, White, Red, Black, Navy, Orange, Hi-Vis Yellow, Gray, Light Gray
Sizes Available	OS
Packaging	Bagged Each
Packed	12/Case
Case Dimensions (in)	26.00 x 15.50 x 28.50
Case Weight (lbs)	15.98
Country of Origin	Canada
Shell Material	HDPE
Shell	Non-Vented
Brim Style	Full
Brim Length	Standard
Size Adjustment	Pin-Lock
Suspension	4 Point Nylon Webbing Cradle
Sweatband	Felt Lined Foam
Size Range	53cm-63cm
Certifications	ANSI/ISEA Z89.1, CSA Z94.1 Certified, TAA Compliant

Performance Data

ANSI Type	Type I
Electrical Class	Class E

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-HP641-11	Black	OS	620606001357	10616314414968	10620606001354
280-HP641-09	Gray	OS	620606001333		10620606001330
280-HP641-31	Hi-Vis Orange	OS	620606002330		10620606002337
280-HP641-44	Hi-Vis Yellow	OS	620606002347	10616314418850	10620606002344
280-HP641-82	Light Gray	OS			
280-HP641-08	Navy	OS	10620606001323	10620606001385	620606001326
280-HP641-03	Orange	OS	620606001272		10620606001279
280-HP641-15	Red	OS	620606001371	10616314422895	10620606001378
280-HP641-17	Royal	OS	620606001388	10616314415002	10620606001385
280-HP641-07	Sky Blue	OS	620606001319	10616314422840	10620606001316
280-HP641-01	White	OS	620606001258		10620606001255
280-HP641-02	Yellow	OS	620606001265	10616314357241	10620606001262