DATA SHEET

Premium Efficiency Motor: **PEWWE5-12-215T** **60 Hz**

WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net

Document Generated: 8-Oct-2024
Document ID:

Customer:

MOTOR INFORMATION

HP	5
RPM	1200
Phase	3
Frequency	60 Hz
Voltage	230/460 V
Frame Size	215T
Enclosure	TEFC
Degree of Protection	IP55
Service Factor	1.25
Poles	6
Full Load Speed	1175
Insulation Class	F
Temp Rise	80°C
NEMA Code Letter	J
Duty Cycle	S1 / Continuous
Slip	2.08%
NEMA Design	B
Moment of Inertia	0.799 lb.ft.^2
Locked Rotor Time (Hot)	15 seconds
Sound Pressure Level	64 dB(A)
Number of Starts	2 Cold/ 1 Hot
Max Ambient Temperature	40°C
Max Elevation	1000 m.a.s.l (3300 f.a.s.l)
Mounting	F1
Rotation	Bi-Directional
Area of Classification	Class 1 Division 2 Groups A,B,C,D T3C(160°C)
Inverter Rating	10:1 CT / 20:1 VT PWM Type
Standard	NEMA MG-1
Approvals	CSA-US, CE

ADDITIONAL DATA

F2 Suitable	Yes
Shaft Material	1045 Carbon Steel
Connection Diagram	230 / 460 V - 9 Lead Y
Approximate Weight	179 lbs.

EFFICIENCY/POWER FACTOR

LOAD	EFF	P. F.
100%	89.5 %	0.72
75%	89.6 %	0.67
50%	89.3 %	0.55

TORQUE

FULL LOAD	LRT	BDT
22.3 lb.ft.	155 %	250 %

AMPERAGE INFORMATION

	230V	460V
Full Load Amps	14.5A	7.27A
Locked Rotor Amps	92A	46A
No Load Current	7.6A	3.8A
Usable at 208V	16.1A	

BEARING INFORMATION


DE Bearing	6308ZZ C3
ODE Bearing	6207ZZ C3
Grease Type	-
DE Regreasing Interval	- Hours
ODE Regreasing Interval	- Hours

This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization

MOTOR DRAWING

Premium Efficiency Motor: **PEWWE5-12-215T**

WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net



DIMENSION - INCHES

MOUNTING					A	B	C	D	G	J	P	O	T	AB
E	2F1	2F	H	BA										
4.25	5.5	7	0.41	3.5	10.315	8.819	19.319	5.25	0.709	2.362	10.389	10.526	1.732	8.178

SHAFT & KEY				
S	ES	R	N-W	U
0.312	2.41	1.201	3.38	1.375

TERMINAL BOX				
AA	XB	XC	XD	XF
1	3.296	5.098	4.567	7.002

This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization

PERFORMANCE CURVES


Premium Efficiency Motor: **PEWWE5-12-215T**


WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net

Document Generated:	8-Oct-2024
Document ID:	

Customer:

Motor Type	PEWWE						
Output Rating (HP)	5		FL Speed	1175			
Full Load Torque	22.3	lb.ft	LRT (%FLT)	155	460 volt FLA	7.27	A
Rotor Wk^2	0.799	lb-ft^2	BDT (%FLT)	250	230 volt FLA	14.5	A





This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization.


NAMEPLATE / WIRING

Premium Efficiency Motor: **PEWWE5-12-215T**

WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net

Document Generated: 8-Oct-2024 Document ID:	Customer:

SAMPLE NAMEPLATE DATA



Model	PEWWE5-12-215T						
HP	5	S.F.	1.25	IP	IP55	Encl	TEFC
Frame	215T	P.F.	0.72	Code	J	Type	
Voltage	230/460 V	Hz	60 Hz	Ins Cl	F	Ambient	40°C
Amps	14.5/7.27	RPM	1175	Design	B	DE Brng	6308ZZ C3
Nom.Eff.	FL 89.5%	3/4	89.6%			ODE Brng	6207ZZ C3
Class 1 Division 2 Groups A,B,C,D T3C(160℃)						Grease type:	-

50Hz				
5 HP	200/400 V	17.7/8.8 A	970 rpm	84.6%

This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization