

## CHASE fittings and multi-hole grips



CHASE liquidtight cord fittings are ideal for installation where space is limited inside the enclosure.

CHASE liquidtight cord fittings



Diagram	Cat. no.	Cable size range min. max. (in.)	Hub size (in.)	Throat dia. (in.)	Dimensions (in.)	
					A	B
	2631	0.125–0.250	½	9/16	1 1/16	1 5/8
	2632	0.250–0.375	½	9/16	1 1/16	1 5/8
	2633	0.375–0.500	½	9/16	1 1/16	1 5/8
	2634	0.450–0.560	½	9/16	1 1/16	1 5/8
	2637	0.125–0.250	¾	25/32	1 3/8	1 3/16
	2638	0.250–0.375	¾	25/32	1 3/8	1 3/16
	2639	0.375–0.500	¾	25/32	1 3/8	1 3/16
	2640	0.500–0.625	¾	25/32	1 3/8	1 3/16
	2641	0.625–0.750	¾	25/32	1 3/8	1 3/16

CSA certified watertight.  
 UL Listed as liquidtight strain-relief, and outlet bushing  
 Temperature rating: 105 °C

In many applications you have only room for one fitting but you need to run two cables, for example, proximity switches. Now you can provide strain relief and liquidtight protection with ABB's multi-hole liquidtight strain-relief fittings. With the ever-increasing number of signal cables, now you have a solution to the problem of how to strain relieve multiple cables in one fitting.



Multi-hole cord grips

Diagram	Cat. no.	Hub size (in.)	No. of holes	Cord dia. (in.)	Dimensions (in.)		
					A	B	C
	2520-2	½	2	0.220	1.125	1.687	0.625
	2530-2	¾	2	0.220	1.375	1.750	0.625
	2531-2	¾	2	0.260	1.375	1.750	0.625
	2531-3	¾	3	0.260	1.375	1.750	0.625
	2541-2*	1	2	0.300	1.625	1.718	0.781
	2542-2*	1	2	0.375	1.625	1.718	0.781
	2540-3	1	3	0.225	1.625	1.718	0.781
	2541-3	1	3	0.300	1.625	1.718	0.781
	2540-4	1	4	0.220	1.625	1.718	0.781
	2555-2	1 ¼	2	0.500	2.093	2.375	0.812

Range of cord diameter ±0.010 in.  
 \*UL Listed only  
 Temperature: 105 °C