

SPECS SHEET


30" WALL OVEN DOUBLE DOORS TOUCH PANEL

MODES

- Bake / Broil / Warm / Proof
- Convection / Air Fryer / Easy
- Sabbath Mode
- Self Cleaning
- 80°F - 550°F (27°C - 288°C)

ELECTRICAL

- 240 V, 60 Hz, 8.5kW, 40 A Breaker
- 208 V, 60 Hz, 6.3kW, 35 A Breaker
- Single Phase 3 or 4-Wire
- ETL Certified to UL & CSA Standards



IMPORTANT

Oven must be connected to the proper electrical voltage and frequency as specified on the model/serial number rating plate. The rating plate is located under the control panel on single ovens and under the control panel of the upper oven cavity on double ovens. All models are dual rated and designed to be connected to either 120/208 V or 120/240 V AC, 60 Hz, 3-wire or 4-wire, single-phase power supply.

