

	BELLINZONI S.R.L.	Revision nr. 3
	Super Crystal Yellow Powder for Marble	Dated 02/12/2020 Printed on 02/12/2020 Page n. 1/12 Replaced revision:2 (Dated: 17/05/2018)

Safety Data Sheet

According to Annex II to REACH - Regulation 2015/830

SECTION 1. Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Code: 091PSCMA - 091PSCMA001 - 091PSCMA005 - 091PSCMA025
Product name: Super Crystal Yellow Powder for Marble
UFI : 2X20-50MN-400Y-5E4V

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use: Polishing powder for marble.

Identified Uses	Industrial	Professional	Consumer
Powder polisher	LCS = IS	LCS = PW	-

1.3. Details of the supplier of the safety data sheet

Name: BELLINZONI S.R.L.
Full address: Via Mezzano 64
District and Country: 28069 Trecate (NO) Italia
Tel. +39 0321 770558

e-mail address of the competent person responsible for the Safety Data Sheet: laboratorio@bellinzoni.com

Product distribution by: BELLINZONI S.r.l.

1.4. Emergency telephone number

For urgent inquiries refer to E.U.: Centro Antiveleni - Ospedale di Niguarda - Milano - Tel. +39 0266101029

SECTION 2. Hazards identification

2.1. Classification of the substance or mixture

The product is classified as hazardous pursuant to the provisions set forth in (EC) Regulation 1272/2008 (CLP) (and subsequent amendments and supplements). The product thus requires a safety datasheet that complies with the provisions of (EU) Regulation 2015/830. Any additional information concerning the risks for health and/or the environment are given in sections 11 and 12 of this sheet.

Hazard classification and indication:

Acute toxicity, category 4	H302	Harmful if swallowed.
Acute toxicity, category 4	H312	Harmful in contact with skin.
Skin irritation, category 2	H315	Causes skin irritation.

2.2. Label elements

Hazard labelling pursuant to EC Regulation 1272/2008 (CLP) and subsequent amendments and supplements.

	BELLINZONI S.R.L.	Revision nr. 3
	Super Crystal Yellow Powder for Marble	Dated 02/12/2020 Printed on 02/12/2020 Page n. 2/12 Replaced revision:2 (Dated: 17/05/2018)

Hazard pictograms:



Signal words: Warning

Hazard statements:

H302+H312 Harmful if swallowed or in contact with skin.
H315 Causes skin irritation.
EUH210 Safety data sheet available on request.

Precautionary statements:

P280 Wear protective gloves / clothing.
P312 Call a POISON CENTRE / doctor / . . . if you feel unwell.
P264 Wash your hands thoroughly with water after use.

Contains: POTASSIUM HYDROGEN OXALATE

2.3. Other hazards

On the basis of available data, the product does not contain any PBT or vPvB in percentage $\geq$ than 0,1%.

SECTION 3. Composition/information on ingredients

3.1. Substances

Information not relevant

3.2. Mixtures

Contains:

Identification	x = Conc. %	Classification 1272/2008 (CLP)
POTASSIUM HYDROGEN OXALATE		
CAS 127-96-8	$57 \leq x < 59$	Acute Tox. 4 H302, Acute Tox. 4 H312, Classification note according to Annex VI to the CLP Regulation: A
EC 204-874-6		
INDEX 607-007-00-3		
Reg. no. 01-2119979573-22-0000		
SULFUR		
CAS 7704-34-9	$24 \leq x < 26$	Skin Irrit. 2 H315
EC 231-722-6		

	BELLINZONI S.R.L.	Revision nr. 3
	Super Crystal Yellow Powder for Marble	Dated 02/12/2020 Printed on 02/12/2020 Page n. 3/12 Replaced revision:2 (Dated: 17/05/2018)

INDEX 016-094-00-1

Reg. no. 01-2119487295-27-XXXX

The full wording of hazard (H) phrases is given in section 16 of the sheet.

SECTION 4. First aid measures

4.1. Description of first aid measures

EYES: Remove contact lenses, if present. Wash immediately with plenty of water for at least 15 minutes, opening the eyelids fully. If problem persists, seek medical advice.

SKIN: Remove contaminated clothing. Wash immediately with plenty of water. If irritation persists, get medical advice/attention. Wash contaminated clothing before using it again.

INHALATION: Remove to open air. In the event of breathing difficulties, get medical advice/attention immediately.

INGESTION: Get medical advice/attention. Induce vomiting only if indicated by the doctor. Never give anything by mouth to an unconscious person, unless authorised by a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Specific information on symptoms and effects caused by the product are unknown.

4.3. Indication of any immediate medical attention and special treatment needed

Information not available

SECTION 5. Firefighting measures

5.1. Extinguishing media

SUITABLE EXTINGUISHING EQUIPMENT

The extinguishing equipment should be of the conventional kind: carbon dioxide, foam, powder and water spray.

UNSUITABLE EXTINGUISHING EQUIPMENT

None in particular.

5.2. Special hazards arising from the substance or mixture

HAZARDS CAUSED BY EXPOSURE IN THE EVENT OF FIRE

Do not breathe combustion products.

POTASSIUM HYDROGEN OXALATE

Combustion could cause the formation of caustic potassium oxide fumes.

5.3. Advice for firefighters

GENERAL INFORMATION

Use jets of water to cool the containers to prevent product decomposition and the development of substances potentially hazardous for health. Always wear full fire prevention gear. Collect extinguishing water to prevent it from draining into the sewer system. Dispose of contaminated water used for extinction and the remains of the fire according to applicable regulations.

SPECIAL PROTECTIVE EQUIPMENT FOR FIRE-FIGHTERS

Normal fire fighting clothing i.e. fire kit (BS EN 469), gloves (BS EN 659) and boots (HO specification A29 and A30) in combination with self-contained open circuit positive pressure compressed air breathing apparatus (BS EN 137).

	BELLINZONI S.R.L.	Revision nr. 3
	Super Crystal Yellow Powder for Marble	Dated 02/12/2020 Printed on 02/12/2020 Page n. 4/12 Replaced revision:2 (Dated: 17/05/2018)

SECTION 6. Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

If there are no contraindications, spray powder with water to prevent the formation of dust.
Wear suitable protective equipment (including personal protective equipment referred to under Section 8 of the safety data sheet) to prevent any contamination of skin, eyes and personal clothing. These indications apply for both processing staff and those involved in emergency procedures.

6.2. Environmental precautions

The product must not penetrate into the sewer system or come into contact with surface water or ground water.

6.3. Methods and material for containment and cleaning up

Collect the leaked product and place it in containers for recovery or disposal. If there are no contraindications, use jets of water to eliminate product residues.
Make sure the leakage site is well aired. Evaluate the compatibility of the container to be used, by checking section 10. Contaminated material should be disposed of in compliance with the provisions set forth in point 13.

6.4. Reference to other sections

Any information on personal protection and disposal is given in sections 8 and 13.

SECTION 7. Handling and storage

7.1. Precautions for safe handling

Before handling the product, consult all the other sections of this material safety data sheet. Avoid leakage of the product into the environment. Do not eat, drink or smoke during use. Remove any contaminated clothes and personal protective equipment before entering places in which people eat.

7.2. Conditions for safe storage, including any incompatibilities

Store only in the original container. Store the containers sealed, in a well ventilated place, away from direct sunlight. Keep containers away from any incompatible materials, see section 10 for details.

7.3. Specific end use(s)

Information not available

SECTION 8. Exposure controls/personal protection

8.1. Control parameters

POTASSIUM HYDROGEN OXALATE

Predicted no-effect concentration - PNEC

Normal value in fresh water	0,1622	mg/l
Normal value in marine water	0,01622	mg/l
Normal value for water, intermittent release	1,622	mg/l

Health - Derived no-effect level - DNEL / DMEL

Effects on
consumers

Effects on
workers

	BELLINZONI S.R.L.		Revision nr. 3
	Super Crystal Yellow Powder for Marble		Dated 02/12/2020 Printed on 02/12/2020 Page n. 5/12 Replaced revision:2 (Dated: 17/05/2018)

Route of exposure	Acute local	Acute systemic	Chronic local	Chronic systemic	Acute local	Acute systemic	Chronic local	Chronic systemic
Oral				1,14 mg/m3				
Inhalation								4,03 mg/m3
Skin	0,35 mg/cm2			1,14 mg/kg bw/d	0,69 mg/cm2			2,29 mg/kg bw/d

VND = hazard identified but no DNEL/PNEC available ; NEA = no exposure expected ; NPI = no hazard identified.

8.2. Exposure controls

As the use of adequate technical equipment must always take priority over personal protective equipment, make sure that the workplace is well aired through effective local aspiration.

When choosing personal protective equipment, ask your chemical substance supplier for advice.

Personal protective equipment must be CE marked, showing that it complies with applicable standards.

Provide an emergency shower with face and eye wash station.

HAND PROTECTION

In the case of prolonged contact with the product, protect the hands with penetration-resistant work gloves (see standard EN 374).

Work glove material must be chosen according to the use process and the products that may form. Latex gloves may cause sensitivity reactions.

SKIN PROTECTION

Wear category II professional long-sleeved overalls and safety footwear (see Regulation 2016/425 and standard EN ISO 20344). Wash body with soap and water after removing protective clothing.

EYE PROTECTION

Wear airtight protective goggles (see standard EN 166).

In the presence of risks of exposure to splashes or squirts during work, adequate mouth, nose and eye protection should be used to prevent accidental absorption.

RESPIRATORY PROTECTION

None required, unless indicated otherwise in the chemical risk assessment.

ENVIRONMENTAL EXPOSURE CONTROLS

The emissions generated by manufacturing processes, including those generated by ventilation equipment, should be checked to ensure compliance with environmental standards.

SECTION 9. Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	powder
Colour	yellow
Odour	odourless
Odour threshold	Not available
pH	3 (3% w/w water solution)
Melting point / freezing point	Not available
Initial boiling point	Not available
Boiling range	Not available
Flash point	> 60 °C
Evaporation Rate	Not available

	BELLINZONI S.R.L.	Revision nr. 3
	Super Crystal Yellow Powder for Marble	Dated 02/12/2020 Printed on 02/12/2020 Page n. 6/12 Replaced revision:2 (Dated: 17/05/2018)

Flammability of solids and gases	Not available
Lower inflammability limit	Not available
Upper inflammability limit	Not available
Lower explosive limit	Not available
Upper explosive limit	Not available
Vapour pressure	Not available
Vapour density	Not available
Relative density	1 g/cm3
Solubility	partially soluble in water
Partition coefficient: n-octanol/water	Not available
Auto-ignition temperature	Not available
Decomposition temperature	Not available
Viscosity	Not applicable
Explosive properties	not explosive
Oxidising properties	non oxidizing

9.2. Other information

Information not available

SECTION 10. Stability and reactivity

10.1. Reactivity

There are no particular risks of reaction with other substances in normal conditions of use.

10.2. Chemical stability

The product is stable in normal conditions of use and storage.

10.3. Possibility of hazardous reactions

No hazardous reactions are foreseeable in normal conditions of use and storage.

10.4. Conditions to avoid

None in particular. However the usual precautions used for chemical products should be respected.

10.5. Incompatible materials

Information not available

10.6. Hazardous decomposition products

Information not available

SECTION 11. Toxicological information

	BELLINZONI S.R.L.	Revision nr. 3
	Super Crystal Yellow Powder for Marble	Dated 02/12/2020 Printed on 02/12/2020 Page n. 7/12 Replaced revision:2 (Dated: 17/05/2018)

11.1. Information on toxicological effects

Metabolism, toxicokinetics, mechanism of action and other information

Information not available

Information on likely routes of exposure

Information not available

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Information not available

Interactive effects

Information not available

ACUTE TOXICITY

ATE (Inhalation) of the mixture:
Not classified (no significant component)
ATE (Oral) of the mixture:
847,46 mg/kg
ATE (Dermal) of the mixture:
1864,41 mg/kg

SULFUR

LD50 (Oral) 2000 mg/kg rat

LD50 (Dermal) 2000 mg/kg rat

LC50 (Inhalation) 5430 mg/m3

SKIN CORROSION / IRRITATION

Causes skin irritation

SERIOUS EYE DAMAGE / IRRITATION

Does not meet the classification criteria for this hazard class

RESPIRATORY OR SKIN SENSITISATION

Does not meet the classification criteria for this hazard class

GERM CELL MUTAGENICITY

Does not meet the classification criteria for this hazard class

	BELLINZONI S.R.L.	Revision nr. 3
	Super Crystal Yellow Powder for Marble	Dated 02/12/2020 Printed on 02/12/2020 Page n. 8/12 Replaced revision:2 (Dated: 17/05/2018)

CARCINOGENICITY

Does not meet the classification criteria for this hazard class

REPRODUCTIVE TOXICITY

Does not meet the classification criteria for this hazard class

STOT - SINGLE EXPOSURE

Does not meet the classification criteria for this hazard class

STOT - REPEATED EXPOSURE

Does not meet the classification criteria for this hazard class

ASPIRATION HAZARD

Does not meet the classification criteria for this hazard class

SECTION 12. Ecological information

Use this product according to good working practices. Avoid littering. Inform the competent authorities, should the product reach waterways or contaminate soil or vegetation.

12.1. Toxicity

POTASSIUM HYDROGEN OXALATE

LC50 - for Fish

160 mg/l/96h pesci d`acqua dolce

EC50 - for Crustacea

162,2 mg/l/48h invertebrati acquatici

12.2. Persistence and degradability

POTASSIUM HYDROGEN OXALATE

Solubility in water

> 10000 mg/l

Rapidly degradable

SULFUR

Solubility in water

0,005 mg/l

Degradability: information not available

12.3. Bioaccumulative potential

POTASSIUM HYDROGEN OXALATE

	BELLINZONI S.R.L.	Revision nr. 3
	Super Crystal Yellow Powder for Marble	Dated 02/12/2020 Printed on 02/12/2020 Page n. 9/12 Replaced revision:2 (Dated: 17/05/2018)

Partition coefficient: n-octanol/water

-4,961

12.4. Mobility in soil

Information not available

12.5. Results of PBT and vPvB assessment

On the basis of available data, the product does not contain any PBT or vPvB in percentage $\geq$ than 0,1%.

12.6. Other adverse effects

Information not available

SECTION 13. Disposal considerations

13.1. Waste treatment methods

Reuse, when possible. Product residues should be considered special hazardous waste. The hazard level of waste containing this product should be evaluated according to applicable regulations.

Disposal must be performed through an authorised waste management firm, in compliance with national and local regulations.

CONTAMINATED PACKAGING

Contaminated packaging must be recovered or disposed of in compliance with national waste management regulations.

SECTION 14. Transport information

The product is not dangerous under current provisions of the Code of International Carriage of Dangerous Goods by Road (ADR) and by Rail (RID), of the International Maritime Dangerous Goods Code (IMDG), and of the International Air Transport Association (IATA) regulations.

14.1. UN number

Not applicable

14.2. UN proper shipping name

Not applicable

14.3. Transport hazard class(es)

Not applicable

	BELLINZONI S.R.L.	Revision nr. 3
	Super Crystal Yellow Powder for Marble	Dated 02/12/2020 Printed on 02/12/2020 Page n. 10/12 Replaced revision:2 (Dated: 17/05/2018)

14.4. Packing group

Not applicable

14.5. Environmental hazards

Not applicable

14.6. Special precautions for user

Not applicable

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Information not relevant

SECTION 15. Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Seveso Category - Directive 2012/18/EC: None

Restrictions relating to the product or contained substances pursuant to Annex XVII to EC Regulation 1907/2006

None

Substances in Candidate List (Art. 59 REACH)

On the basis of available data, the product does not contain any SVHC in percentage $\geq$ than 0,1%.

Substances subject to authorisation (Annex XIV REACH)

None

Substances subject to exportation reporting pursuant to (EC) Reg. 649/2012:

None

Substances subject to the Rotterdam Convention:

None

Substances subject to the Stockholm Convention:

	BELLINZONI S.R.L.	Revision nr. 3
	Super Crystal Yellow Powder for Marble	Dated 02/12/2020 Printed on 02/12/2020 Page n. 11/12 Replaced revision:2 (Dated: 17/05/2018)

None

Healthcare controls

Workers exposed to this chemical agent must not undergo health checks, provided that available risk-assessment data prove that the risks related to the workers' health and safety are modest and that the 98/24/EC directive is respected.

15.2. Chemical safety assessment

A chemical safety assessment has not been performed for the preparation/for the substances indicated in section 3.

SECTION 16. Other information

Text of hazard (H) indications mentioned in section 2-3 of the sheet:

Acute Tox. 4	Acute toxicity, category 4
Skin Irrit. 2	Skin irritation, category 2
H302	Harmful if swallowed.
H302+H312	Harmful if swallowed or in contact with skin.
H312	Harmful in contact with skin.
H315	Causes skin irritation.
EUH210	Safety data sheet available on request.
	PW
LCS	Widespread use by professional workers

LEGEND:

- ADR: European Agreement concerning the carriage of Dangerous goods by Road
- CAS NUMBER: Chemical Abstract Service Number
- CE50: Effective concentration (required to induce a 50% effect)
- CE NUMBER: Identifier in ESIS (European archive of existing substances)
- CLP: EC Regulation 1272/2008
- DNEL: Derived No Effect Level
- EmS: Emergency Schedule
- GHS: Globally Harmonized System of classification and labeling of chemicals
- IATA DGR: International Air Transport Association Dangerous Goods Regulation
- IC50: Immobilization Concentration 50%
- IMDG: International Maritime Code for dangerous goods
- IMO: International Maritime Organization
- INDEX NUMBER: Identifier in Annex VI of CLP
- LC50: Lethal Concentration 50%
- LD50: Lethal dose 50%
- OEL: Occupational Exposure Level
- PBT: Persistent bioaccumulative and toxic as REACH Regulation
- PEC: Predicted environmental Concentration
- PEL: Predicted exposure level
- PNEC: Predicted no effect concentration
- REACH: EC Regulation 1907/2006
- RID: Regulation concerning the international transport of dangerous goods by train
- TLV: Threshold Limit Value
- TLV CEILING: Concentration that should not be exceeded during any time of occupational exposure.
- TWA STEL: Short-term exposure limit
- TWA: Time-weighted average exposure limit
- VOC: Volatile organic Compounds

	BELLINZONI S.R.L.	Revision nr. 3
	Super Crystal Yellow Powder for Marble	Dated 02/12/2020 Printed on 02/12/2020 Page n. 12/12 Replaced revision:2 (Dated: 17/05/2018)

- vPvB: Very Persistent and very Bioaccumulative as for REACH Regulation
- WGK: Water hazard classes (German).

GENERAL BIBLIOGRAPHY

1. Regulation (EC) 1907/2006 (REACH) of the European Parliament
 2. Regulation (EC) 1272/2008 (CLP) of the European Parliament
 3. Regulation (EU) 790/2009 (I Atp. CLP) of the European Parliament
 4. Regulation (EU) 2015/830 of the European Parliament
 5. Regulation (EU) 286/2011 (II Atp. CLP) of the European Parliament
 6. Regulation (EU) 618/2012 (III Atp. CLP) of the European Parliament
 7. Regulation (EU) 487/2013 (IV Atp. CLP) of the European Parliament
 8. Regulation (EU) 944/2013 (V Atp. CLP) of the European Parliament
 9. Regulation (EU) 605/2014 (VI Atp. CLP) of the European Parliament
 10. Regulation (EU) 2015/1221 (VII Atp. CLP) of the European Parliament
 11. Regulation (EU) 2016/918 (VIII Atp. CLP) of the European Parliament
 12. Regulation (EU) 2016/1179 (IX Atp. CLP)
 13. Regulation (EU) 2017/776 (X Atp. CLP)
 14. Regulation (EU) 2018/669 (XI Atp. CLP)
 15. Regulation (EU) 2018/1480 (XIII Atp. CLP)
 16. Regulation (EU) 2019/521 (XII Atp. CLP)
- The Merck Index. - 10th Edition
 - Handling Chemical Safety
 - INRS - Fiche Toxicologique (toxicological sheet)
 - Patty - Industrial Hygiene and Toxicology
 - N.I. Sax - Dangerous properties of Industrial Materials-7, 1989 Edition
 - IFA GESTIS website
 - ECHA website
 - Database of SDS models for chemicals - Ministry of Health and ISS (Istituto Superiore di Sanità) - Italy

Note for users:

The information contained in the present sheet are based on our own knowledge on the date of the last version. Users must verify the suitability and thoroughness of provided information according to each specific use of the product.

This document must not be regarded as a guarantee on any specific product property.

The use of this product is not subject to our direct control; therefore, users must, under their own responsibility, comply with the current health and safety laws and regulations. The producer is relieved from any liability arising from improper uses.

Provide appointed staff with adequate training on how to use chemical products.

CALCULATION METHODS FOR CLASSIFICATION

Chemical and physical hazards: Product classification derives from criteria established by the CLP Regulation, Annex I, Part 2. The data for evaluation of chemical-physical properties are reported in section 9.

Health hazards: Product classification is based on calculation methods as per Annex I of CLP, Part 3, unless determined otherwise in Section 11.

Environmental hazards: Product classification is based on calculation methods as per Annex I of CLP, Part 4, unless determined otherwise in Section 12.

Changes to previous review:

The following sections were modified:

01 / 02 / 03 / 05 / 08 / 09 / 11 / 12 / 15 / 16.