

PORCELAIN AND PLASTIC LAMP HOLDERS

- UL Listed. File Number: E236781.
- Nickel-plated brass screw shell will not corrode.
- Fits 3.25" or 4.0" outlet box.
- UV resistant Lamp Holders will not fade or discolor.
- Optional Plastic and Metal Safety Cages fit all Lamp Holders.
- Includes corrosion resistant mounting screws.
- Meets the requirements of the 2017 National Electrical Code:
 - Part Numbers: 16500, 16502, 16510, 16512 and 16514 — Articles 410.74(A)(B) and 410.122
 - Part Numbers: 16520, 16522, 16524 and 16526 — Articles 410.52, 410.74(A)(B) and 410.122



Catalog Number	UPC Number	Description	Order Unit	Unit Qty	Unit Pkg	Units/Case	TL Case Qty	Min Order Qty	MM Req	Ship Wt (Lbs)
16500	16500	Porcelain Lamp Holder: Keyless, 4-Terminal	EA	1	BX	48	48	48	Yes	33
16502	16502	Porcelain Lamp Holder: Pull Chain	EA	1	BX	48	48	48	Yes	35
16510	16510	Plastic Lamp Holder: Keyless, 4-Terminal	EA	1	BX	48	48	48	Yes	11
16512	16512	Plastic Lamp Holder: Pull Chain	EA	1	BX	48	48	48	Yes	13
16514	16514	Porcelain Lamp Holder: Pull Chain and 15 AMP Receptacle	EA	1	BX	48	48	48	Yes	40
16520	16520	Porcelain Lamp Holder: Keyless, 4-Terminal with 7" Black and White Conductors	EA	1	BX	48	48	48	Yes	33
16522	16522	Porcelain Lamp Holder: Pull Chain with 7" Black and White Conductors	EA	1	BX	48	48	48	Yes	35
16524	16524	Plastic Lamp Holder: Keyless, 4-Terminal with 7" Black and White Conductors	EA	1	BX	48	48	48	Yes	11
16526	16526	Plastic Lamp Holder: Pull Chain with 7" Black and White Conductors	EA	1	BX	48	48	48	Yes	13

Accessories

15680	15680	Compact Fluorescent Lamp: 23-Watt, Self-Ballasted Lamp (5000K); Lumen output is equal to 100-Watt Incandescent Lamp	EA	1	BX	50	50	1	No	1
15681	15681	LED A21 Lamp: 15.5-Watt, 5000K, dimmable, Energy Star rated; Lumen output is equal to 100-Watt Incandescent Lamp	EA	1	BX	12	12	1	No	1
16100	16100	Safety Cage: Yellow	EA	1	BX	10	10	10	Yes	1
16501	16501	Safety Cage: Metal	EA	1	BX	12	12	12	Yes	6

UNITS OF MEASURE KEY Order Unit: The Unit to be ordered; Unit Qty: Number of pieces in each Unit; Unit Pkg: Unit Packages contained in the case - Packaging types - BG (Bag), BRL (Barrel), BX (Box), BN (Bulk), PKG (Package), EA (Each), RL (Roll), LB (Pound), C (Hundred), M (Thousand); Units/Case: Unit packages contained in the Case; TL Case Qty: The total number of items in each Master Case; Min Order Qty: The smallest Unit that can be ordered; MM Req: Must order multiples of the Unit in the stated quantities; Ship Wt (Lbs): Total weight of the units per Carton

INSTALLING LAMP HOLDERS FOR POULTRY FARMING APPLICATIONS

EPCO recommends using only Porcelain Lamp Holder(s) for poultry farming applications. The lamp holder must be installed in a manner that will not permit dust or moisture to enter the junction box. In addition, the porcelain lamp holder must be mounted vertically with the lamp positioned below the lamp holder on a water-tight, dust-tight non-metallic junction box with an effective gasket between the junction box and the lamp holder as shown in the photo to the right.

Use any of the combined part numbers below to complete the installation as shown.



Porcelain Lamp Holder (P/N 16500),
Cork Gasket (P/N PE05-003-000), and
Junction Box (P/N 15246)

Catalog Number	UPC Number	Description	Order Unit	Unit Qty	Unit Pkg	Units/Case	TL Case Qty	Min Order Qty	MM Req	Ship Wt (Lbs)
PE05-003-000	10055	Cork Gasket	EA	1	BG	12	12	12	Yes	1
15045	15045	12 Cubic Inch Junction Box: 1/2" and 3/4" Knockout Combo	EA	1	BX	12	12	12	Yes	6
15046	15046	12 Cubic Inch Junction Box: 1/2" Knockouts	EA	1	BX	12	12	12	Yes	6
15047	15047	12 Cubic Inch Junction Box: 3/4" Knockouts	EA	1	BX	12	12	12	Yes	6
15049	15049	19 Cubic Inch Junction Box: 3/4" Knockouts	EA	1	BX	12	12	12	Yes	6
15246	15246	12 Cubic Inch SPIDERBOX Junction Box: 1/2" Knockouts	EA	1	BX	12	12	12	Yes	6
15247	15247	12 Cubic Inch SPIDERBOX Junction Box: 3/4" Knockouts	EA	1	BX	12	12	12	Yes	6
16500	16500	Porcelain Lamp Holder: Keyless, 4-Terminal	EA	1	BX	48	48	48	Yes	33
16502	16502	Porcelain Lamp Holder: Pull Chain	EA	1	BX	48	48	48	Yes	35
16514	16514	Porcelain Lamp Holder: Pull Chain and 15 AMP Receptacle	EA	1	BX	48	48	48	Yes	40

- Note:** 1. Junction boxes include screws to affix the lamp holder to the junction box.
2. Plastic Lamp Holders are NOT suitable for this application and will VOID the 1-Year Warranty!

WARNING: EPCO Lamp Holders Must Be Installed in Accordance with the following 2017 National Electric Code Articles that state:

Where the wiring method is conduit, tubing, Type AC cable, or other cables, a box or conduit body shall be installed at each conductor splice point, outlet point, switch point, junction point, termination point, or pull point, unless otherwise permitted in NEC 300.15(A).

In addition, Article 502.130(2) requires luminaires for fixed lighting shall be provided with enclosures that are dust tight or otherwise identified for the location as well as protected from physical damage by suitable guards for areas described in Article 547.1(A)(B). See example shown above.

If the Contractor has taken care to install the porcelain lamp holder(s) in the proper manner as described and shown above and believes the lamp holder is defective, and wants to file a warranty claim, EPCO will require an "Affidavit of Inspection" from the Contractor's local Electrical Inspector to validate the defined installation procedure. This document is intended to protect the integrity of the company (EPCO) and the Distributor.