marathon®

General Purpose Motors

Model No: 284TTDBD6026
Catalog No: GT0065

General Purpose Motor, 25 & 20 HP, 3 Ph, 60 & 50 Hz, 230/460 & 190/380 V, 1800 RPM, 284T Frame, DP

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: 284TTDBD6026, Catalog No: GT0065 General Purpose Motor, 25 & 20 HP, 3 Ph, 60 & 50 Hz, 230/460 & 190/380 V, 1800 RPM, 284T Frame, DP

Nameplate Specifications

Phase	**3**	Output HP	**25 & 20 Hp**
Output KW	**18.7 & 14.9 kW**	Voltage	**230/460 & 190/380 V**
Speed	**1775 & 1475 r/min**	Synchronous RPM	**1800 & 1500 r/min**
Service Factor	**1.15 & 1.15**	Frame	**284T**
Enclosure	**Drip Proof**	Thermal Protection	**No Protection**
Efficiency	**93.6 & 92.6 %**	Ambient Temperature	**40 °C**
Frequency	**60 & 50 Hz**	Current	**63/31.5 & 61/30.5 A**
Power Factor	**80**	Duty	**Continuous**
Insulation Class	**F**	Design Code	**B**
KVA Code	**G**	Drive End Bearing Size	**6311**
Opp Drive End Bearing Size	**6210**	UL	**Recognized**
CSA	**Y**	CE	**Y**
IP Code	**22**	Number of Speeds	**1**

Technical Specifications


Electrical Type	**Squirrel Cage Inverter Rated**	Starting Method	**Part Wdg Start Low Volt Only & Wye Start Delta Run Or Inverter**
Poles	**4**	Rotation	**Reversible**
Resistance Main	**.3745 O**	Mounting	**Rigid Base**
Motor Orientation	**Horizontal**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Rolled Steel**
Shaft Type	**T**	Overall Length	**25.71 in**
Shaft Diameter	**1 7/8 in**	Shaft Extension	**4.62 in**
Assembly/Box Mounting	**F1/F2 Capable**	Inverter Load	**Constant 2:1/Variable 10:1**


Drawings

Connection Drawing	**EE7308AA**	Outline Drawing	**SS620687-100**


This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 16/10/2026

DASH NO.	B	C	D	E	2E	2F	2FF	BA	BS	MOUNTING	FRAME
100	15.55	25.60	7.00	5.50	11.00	9.50	11.00	4.75	10.80	F1 OR F2	284T
200		26.98							12.18		286T





F2 VIEW



DRAWING REVISION	REVISION BY	REV DATE/© DATE
F	SB	07/22/2025
REQUEST NUMBER	APPROVED BY	DATE
CR-0023556	SBD	07/22/2025


REQUEST NUMBER DESCRIPTION
DRAWING TITLE BLOCK UPDATED

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.


PRIMARY DIMENSIONS ARE INCH
mm DIMENSIONS IN [BRACKETS]
ARE FOR REFERENCE ONLY

DRAWN BY	DESCRIPTION
XZ	OUTLINE
DATE: 17/04/2017	284/286T FR NEMA ODP RS
APPROVED BY	
DATE	
REFERENCE	MATERIAL / PROCESS/FINISH
THIRD ANGLE PROJECTION	SIZE: B / DRAWING NUMBER: SS620687 / SHEET: 1 OF 1


marathon™



LOW VOLTAGE



HIGH VOLTAGE



VIEW OF TERMINAL END

DRAWING REVISION: L	REVISION BY: SB	REV DATE/© DATE: 08/01/2025	PRIMARY DIMENSIONS ARE INCH mm DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY	DRAWN BY: LZ	marathon™
REQUEST NUMBER: CR-0023654	APPROVED BY: SBD	DATE: 08/01/2025		DATE: 01-12-1994	
REQUEST NUMBER DESCRIPTION: DRAWING TITLE BLOCK UPDATED				APPROVED BY: GK	DESCRIPTION: CONN DIAGRAM-EXTERNAL 3Ø-2/1 DELTA-12 LEADS
				DATE: 01-14-1994	
				REFERENCE	MATERIAL / PROCESS/FINISH
				THIRD ANGLE PROJECTION	SIZE: A / DRAWING NUMBER: EE7308AA / SHEET: 1 OF 1

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

Data Sheet

Date: 12/1/2021
Customer:
Attention:
Submitted by:

marathon® Motors

284TTDBD6026

Submittal


Data @ 460 V

Motor Load Data

Load	0%	25%	50%	75%	100%	115%	125%	LR	
Current (Amps)	15.0	16.5	20.0	25.0	31.2	35.0	38.0	190	
Torque (ft-lb)	0.00	18.3	36.7	55.2	74.0	85.0	92.8	140	
RPM	1800	1795	1788	1782	1775	1,770	1768	0	
Efficiency (%)		88.5	92.4	93.6	93.6	93.0	92.4		
P.F. (%)	4.5	40.0	62.0	74.0	80.0	82.0	83.0	36.0	

Motor Speed Data

	LR	Pull-Up	BD	Rated	Idle
Speed (RPM)	0	900	1645	1775	1800
Current (Amps)	190	150	110	31.2	15.0
Torque (ft-lb)	140	118	195	74.0	0.00



Information Block

HP	25.0
Sync. RPM	1800
Frame	284
Enclosure	DP
Construction	TDB
Voltage	208-230/460#190/380 V
Frequency	60 Hz
Design	B
LR Code letter	G
Service Factor	1.15
Temp Rise @ FL	50 ° C
Duty	CONT
Ambient	40 ° C
Elevation	3,300 feet
Rotor/Shaft wk²	4.2 Lb-Ft²
Ref Wdg	HA31804016 NONE
Sound Pressure @ 1M	75 dBA
VFD Rating	VARIABLE 20:1
Outline Dwg	SS620687-100
Conn. Diag	EE7308AA
Additional Specifications:	
0	
0	

EQUIV CKT (OHMS / PHASE)

R1	R2	X1	X2	Xm
0.2270	0.1320	0.8740	1.0100	18.9460

Speed -Torque Curve

