

EAN:	4013288093561	Size:	62x22x8 mm
Part number:	05026360001	Weight:	5 g
Article number:	1267 A TORX PLUS®	Country of origin:	CZ
		Customs tariff number:	82054000

- TORX PLUS® flagdriver for recessed TORX PLUS® screws
- Multi-component handle
- Circular blade with BlackLaser treatment for outstanding surface protection and long service life
- High torque transfer for small screws






High quality Wera flagdriver for recessed TORX PLUS® screws. TORX PLUS® profile: in comparison to normal TORX® profiles, the enlargement of the 6 torque-transferring flanks between the tool and the screw is effected by means of an ellipse-shaped profile design and not a circular one. This means that the power applied when screwdriving is spread over a larger area. Higher torque is transferred and the service life of the screw and tool is also enhanced. High torque transfer for small screws. Particularly suitable for exchanging indexable inserts. The BlackLaser surface treatment provides outstanding surface protection, even against corrosion, and a long service life. Multi-component for outstanding grip.

Web link
<https://www.wera.de/en/05026360001>

Wera - 1267 A TORX PLUS®
 05026360001 - 4013288093561

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de

Further versions in this product family:

		 mm	 mm	 mm	 inch
05026360001	6 IP	33	62.0	3.0	1 19/64"
05026361001	7 IP	33	62.0	3.0	1 19/64"
05026362001	8 IP	40	69.0	3.0	1 37/64"
05026363001	9 IP	40	69.0	3.0	1 37/64"
05026364001	10 IP	40	69.0	3.0	1 37/64"

Web link

<https://www.wera.de/en/05026360001>

Wera - 1267 A TORX PLUS®
05026360001 - 4013288093561

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de