

PRODUCT SPECIFICATIONS

MODEL NO.	MOTOR	RPM		RUNNING AMPS		STARTING AMPS (0-500 RPM)		HP	kW	NET WT.		CAPACITOR	
		60HZ	50HZ.	60HZ	50HZ.	60HZ	50HZ.			lbs.	kg	mfd.	VOLT
DOA-P704-AA	115V	1575	N/A	4.5	N/A	5.1	N/A	1/8	.096	14.39	6.54	N/A	N/A

SOUND LEVEL LESS THAN 70 db(A)

NORMAL AMBIENT +5°C - +40°C



RELATIVE HUMIDITY 20% - 80%

ENVIRONMENT CLEAN DUST FREE

NOTES:

1. ALL DIMENSIONS ARE FOR REF. USE ONLY.
2. PRODUCT DIMENSIONS: U.S. IMPERIAL (INCHES), METRIC (mm).
3. TECHNICAL DATA SUBJECT TO CHANGE WITHOUT NOTICE.

PRODUCT PERFORMANCE:



PRODUCT DIMENSIONS:

