



SAFETY DATA SHEET

Supersedes Date: 13 Feb 2023

Revision Date: 05 May 2023

Version: 3.0

1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

Product identifier

Product Label Name Bio Release

Other means of identification

UPC Code(s) Not applicable

Product code CD02

Synonyms None

Recommended use of the chemical and restrictions on use

Recommended Use Specialty spot cleaner

Uses advised against Follow label instructions. Not recommended for any use except intended use.

Supplier's details

Supplier Address

Aramco Inc.
4282 South 590 West
Salt Lake City, UT 84123
USA

Manufacturer Address

Aramco Inc.
4282 South 590 West
Salt Lake City, UT 84123
USA

Emergency telephone number

Company Phone Number 1-800-658-5314

Company Emergency Phone United States: 1-800-535-5053 (INFOTRAC – 24 hours, 7 days a week)

Number International: 1-352-323-3500 (INFOTRAC – 24 hours, 7 days a week)

Emergency telephone Poison Control 1-800-222-1222 (24 hour)

2. HAZARDS IDENTIFICATION

Classification

OSHA Regulatory Status

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Skin corrosion/irritation	Category 2
Serious eye damage/eye irritation	Category 2
Skin sensitization	Category 1

GHS Label elements, including precautionary statements

Emergency Overview

Warning

Hazard Statements

Causes skin irritation

Causes serious eye irritation

May cause an allergic skin reaction

Skin contact Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Remove and wash contaminated clothing before re-use. Wash off immediately with plenty of water. If skin irritation persists, call a physician. Immediate medical attention is not required.

Toxic - Inhalation Move to fresh air. Consult a physician. If breathing is irregular or stopped, administer artificial respiration. Use barrier to give mouth-to-mouth resuscitation. Immediate medical attention is not required. If symptoms persist, call a physician.

Ingestion Rinse mouth. Drink plenty of water. If symptoms persist, call a physician. Do NOT induce vomiting. Clean mouth with water and drink afterwards plenty of water. Never give anything by mouth to an unconscious person.

Protection of First-aiders Use personal protective equipment.

Most important symptoms/effects, acute and delayed

Main Symptoms No information available.

Indication of immediate medical attention and special treatment needed, if necessary

Notes to physician Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Use: Dry chemical. Carbon dioxide (CO₂). Water spray. Alcohol-resistant foam.

Unsuitable Extinguishing Media Do not use a solid water stream as it may scatter and spread fire.

Specific hazards arising from the chemical

In the event of fire and/or explosion do not breathe fumes. May cause sensitization by inhalation and skin contact. Thermal decomposition can lead to release of irritating and toxic gases and vapors. Keep product and empty container away from heat and sources of ignition.

Hazardous Combustion Products No information available.

Explosion Data

Sensitivity to Mechanical Impact None.

Sensitivity to Static Discharge None.

Protective Equipment and Precautions for Firefighters

Wear self contained breathing apparatus for fire fighting if necessary.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Use personal protective equipment. Remove all sources of ignition. Evacuate personnel to safe areas. Keep people away from and upwind of spill/leak. Pay attention to flashback. Take precautionary measures against static discharges.

Advice for emergency responders For personal protection see section 8.

Environmental precautions

Environmental precautions Prevent entry into waterways, sewers, basements or confined areas. Do not flush into surface water or sanitary sewer system. Prevent further leakage or spillage if safe to do so. Prevent product from entering drains.

Methods and materials for containment and cleaning up

Methods for Containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Cover liquid spill with sand, earth or other noncombustible absorbent material. Cover powder spill with plastic sheet or tarp to minimize spreading. Pick up and transfer to properly labeled containers. Soak up with inert absorbent material. Dam up. Take precautionary measures against static discharges.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Avoid contact with skin, eyes and clothing. Wear personal protective equipment. Remove and wash contaminated clothing before re-use. Do not breathe vapors or spray mist. Do not eat, drink or smoke when using this product. Use only in area provided with appropriate exhaust ventilation. To avoid ignition of vapors by static electricity discharge, all metal parts of the equipment must be grounded. Keep away from heat, sparks and open flame. Take necessary action to avoid static electricity discharge (which might cause ignition of organic vapors).

Conditions for safe storage, including any incompatibilities

Technical measures/Storage conditions Keep container tightly closed in a dry and well-ventilated place. Keep out of the reach of children. Keep containers tightly closed in a cool, well-ventilated place. Keep away from heat and sources of ignition. Keep in properly labeled containers. Keep away from heat.

Packaging material Keep product in packaging product is initially sold in.

Incompatible products None known based on information supplied.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
None			

NIOSH IDLH: *Immediately Dangerous to Life or Health*

Other Exposure Guidelines Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962 (11th Cir., 1992).

Appropriate engineering controls

Engineering Measures Showers
Eyewash stations
Ventilation systems.

Individual protection measures, such as personal protective equipment

Eye/Face Protection Tightly fitting safety goggles. Face-shield.

Skin and body protection No special protective equipment required.

Respiratory protection

If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

Hygiene measures

Provide regular cleaning of equipment, work area and clothing. Do not eat, drink or smoke when using this product. Remove and wash contaminated clothing before re-use.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical and chemical properties

Physical state	liquid	Odor	Fruity Floral
Appearance	Clear Liquid	Odor threshold	No information available
Color	None		

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	7.5	7.0 – 8.0
Melting point	No information available	
Boiling point/boiling range	> 100 °C / 212 °F	
Flash Point	> 100 °C / 212 °F	54 °C / 135 °F
Evaporation rate	Same as water	
Flammability (solid, gas)	No information available	
Flammability Limits in Air		
Upper Flammability Limit	No information available	
Lower Flammability Limit	No information available	
Vapor pressure	1.8	
Vapor density	4.9	
Specific Gravity	1.045	
Water solubility	Miscible in water	
Solubility in other solvents	No information available	
Partition coefficient: n-octanol/water	No information available	
Autoignition temperature	No information available	
Decomposition temperature	No information available	
Viscosity, kinematic	No information available	
Viscosity, dynamic	No information available	
Explosive properties	No information available	
Oxidizing Properties	No information available	

Other information

Softening point	No information available
Molecular weight	No information available
VOC Content(%)	No information available
Density VALUE	No information available
Bulk Density VALUE	No information available

10. STABILITY AND REACTIVITY

Reactivity

Chemical stability

Stable under recommended storage conditions.

Possibility of hazardous reactions

None under normal processing.

Hazardous Polymerization None under normal processing.

Conditions to Avoid

Heat, flames and sparks.

Incompatible Materials

None known based on information supplied.

Hazardous Decomposition Products

None known based on information supplied.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information

- Toxic - Inhalation** May be harmful if inhaled. Avoid breathing vapors or mists.
- Eye contact** Risk of serious damage to eyes. Avoid contact with eyes.
- Skin contact** Irritating to skin. Avoid contact with skin.
- Ingestion** May be harmful if swallowed.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
None			

Information on toxicological effects

Symptoms No information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

- Skin corrosion/irritation** No information available.
- Eye damage/irritation** No information available.
- Sensitization** No information available.
- Germ Cell Mutagenicity** No information available.
- Carcinogenicity** The table below indicates whether each agency has listed any ingredient as a carcinogen.

Chemical Name	ACGIH	IARC	NTP	OSHA
None	-	-	-	-

OSHA (Occupational Safety and Health Administration of the US Department of Labor)
X - Present
IARC: (International Agency for Research on Cancer)
Group 3 - Not Classifiable as to Carcinogenicity in Humans

- Reproductive toxicity** No information available.
- Developmental Toxicity** No information available.
- STOT - single exposure** No information available.
- STOT - repeated exposure** No information available.
- Chronic toxicity** Repeated contact may cause allergic reactions in very susceptible persons. Avoid repeated exposure.
- Target Organ Effects** Eyes, Respiratory system, Skin, Central nervous system.
- Aspiration hazard** No information available.

Numerical measures of toxicity - Product Information

The following values are calculated based on chapter 3.1 of the GHS document .

- ATEmix (oral)** >5000 mg/kg
- ATEmix (dermal)** >5000 mg/kg

12. ECOLOGICAL INFORMATION

Ecotoxicity

0% of the mixture consists of component(s) of unknown hazards to the aquatic environment

Chemical Name	Toxicity to algae	Toxicity to fish	Toxicity to daphnia and other aquatic invertebrates
None			

Persistence and degradability

No information available.

Bioaccumulation

No information available.

Other adverse effects

No information available

13. DISPOSAL CONSIDERATIONS

Waste treatment

Waste Disposal Methods

Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging

Do not re-use empty containers.

US EPA Waste Number

None

This product contains one or more substances that are listed with the State of California as a hazardous waste.

Chemical Name	California Hazardous Waste Status

14. TRANSPORT INFORMATION

DOT

Not regulated

IMDG

Not regulated

IATA

Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA

Complies

DSL/NDSL

Complies

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372.

SARA 311/312 Hazard Categories

Acute Health Hazard

Yes

Chronic Health Hazard

No

Fire Hazard	No
Sudden Release of Pressure Hazard	No
Reactive Hazard	No

Clean Water Act

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

US State Regulations

California Proposition 65

This product can expose you to chemicals including 1,4-Dioxane and Ethylene Oxide, which are known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
None			

U.S. EPA Label information

EPA Pesticide Registration Number Not applicable

16. OTHER INFORMATION

<u>NFPA</u>	Health hazard 2	Flammability 1	Instability 0	Physical and chemical hazards -
<u>HMIS</u>	Health hazard 2	Flammability 1	Physical Hazard 0	Personal protection X

Prepared By Aramsco
Environmental Health & Safety

Revision Date 05 May 2023

Revision Note
05 May 2023 – Update Prop 65 Warning
13 Feb 2023 – Update Prop 65 Warning

Disclaimer

The (M)SDS is intended to provide a brief summary of our knowledge and guidance regarding the use of this material. The information contained here has been compiled from sources considered by Aramsco to be dependable and is accurate to the best of the Company’s knowledge. It is not meant to be an all-inclusive document on worldwide hazard communication regulations.

This information is offered in good faith. Each user of this material needs to evaluate the conditions of use and design the appropriate protective mechanisms to prevent employee exposures, property damage or release to the environment. Aramsco assumes no responsibility for injury to the recipient of third persons, or for any damage to any property resulting from misuse of the product.

End of Material Safety Data Sheet