ABB BALDOR RELIANCE

Customer information packet

XM251522T

34M 2P XPFC HOR 254T T'STATS INV DUTY
Class - CLI GP D; CLII GP F,G
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 9:29:20 AM

Specifications

Enclosure	XPFC
Frame	254T
Frame Material	Iron
Frequency	50.00 Hz
	60.00 Hz
Haz Area Class and Group	CLI GP D; CLII GP F,G
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	15.000 HP @ 60 HZ
	10.000 HP @ 50 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	190.0 V @ 50 HZ
	230.0 V @ 60 HZ
	380.0 V @ 50 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA EEV
	UL
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	14.500 A @ 380.0 V
	17.200 A @ 460.0 V
	29.000 A @ 190.0 V
	34.400 A @ 230.0 V
	37.000 A @ 208.0 V
Design Code	A
Drip Cover	No Drip Cover

Part Detail

Revision	L
Type	AC
Mech. spec.	09E270
Base	
Status	PRD/A
Elec. spec.	09WGZ864
Layout	09LYE270
Eff. date	11-14-2023
CD Diagram	CD0180
Poles	02
Leads	9#12
Proprietary	False
Created date	03-27-2019

Duty Rating	CONT
Efficiency @ 100% Load	91.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	14.5 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	NONE
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	5400 rpm
Motor Lead Quantity/Wire Size	9 @ 12 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	X0934M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	25.50 IN
Power Factor	88
Product Family	Hazardous Location Motor
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	None
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger

Speed	2940 rpm
	3530 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP0887XPSLEV										
NO.				**CC**	010A					
S/N				**TEMP CODE**	T3C					
SPEC.	09E270Z864G1			**INV.TYPE**	PWM					
CAT.NO.	XM251522T			**C HP FR**	60	**C HP TO**	90			
HP	15//10			**CT HZ FROM**	6			**CT HZ TO**	60	
VOLTS	230/460//190/380			**VT HZ FROM**	6			**VT HZ TO**	60	
AMPS	34.4/17.2//29/14.5			**MAG CUR**	11.8/5.9					
RPM	3530//2940			**MX RPM**	5400					
HZ	60//50	**PH**	3	**CL**	F	**NOM.EFF.**	91			
SER.F.	1.15	**DES**	A	**SL HZ**	1.2	**WK2**	0.87			
FRAME	254T	**RATING**	40C AMB-CONT							
	55C AMB @1.0SF ON VFD,60C RISE									
	NEMA MG-1 PT.5,IP54									

AC Induction Motor Performance Data
Record # 38686
Typical performance - not guaranteed values


Winding: 09WGZ864-R001	**Type:** 0934M	**Enclosure:** XPFC

Nameplate Data			
Rated Output (HP)			15//10
Volts			230/460//190/380
Full Load Amps			34.4/17.2//29/14.5
R.P.M.			3530//2940
Hz	60//50	**Phase**	3
NEMA Design Code	A	**KVA Code**	H
Service Factor (S.F.)			1.15
NEMA Nom. Eff.	91	**Power Factor**	88
Rating - Duty			40C AMB-CONT
S.F. Amps			

460 V, 60 Hz: High Voltage Connection	
Full Load Torque	22.2 LB-FT
Start Configuration	direct on line
Breakdown Torque	102 LB-FT
Pull-up Torque	32.9 LB-FT
Locked-rotor Torque	40.8 LB-FT
Starting Current	128 A
No-load Current	5.9 A
Line-line Res. @ 25ºC	0.591 Ω
Temp. Rise @ Rated Load	56°C
Temp. Rise @ S.F. Load	70°C
Locked-rotor Power Factor	29.4
Rotor inertia	0.868 LB-FT2

Load Characteristics 460 V, 60 Hz, 15 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	57	78	86	89	90	90	90
Efficiency	86.2	90.8	91.7	91.6	91.3	90.5	91.5
Speed	3583	3567	3550	3533	3514	3493	3522
Line amperes	7.2	10	13.4	17.2	21.2	25.6	19.6


ABB Motors and Mechanical Inc.
WINDING # 09WGZ864
15 HP 3 PH 60 HZ 3533 RPM 460 V 0934M
Typical performance - not guaranteed values.
TORQUES(LB-FT): PO=102 PU=32.9 LR=40.8 LRA=128
TORQUE
RPM
KW
AMPS
EFF
PF
%EFF %PF
TORQUE (LB-FT)
RPM
KW
AMPS
PERCENT OF RATED OUTPUT (15 HP)
11/5/2026 ACPERF, record # 38686

AC Induction Motor Performance Data
Record # 38687
Typical performance - not guaranteed values


Winding: 09WGZ864-R001	**Type:** 0934M	**Enclosure:** XPFC


Nameplate Data			
Rated Output (HP)			15//10
Volts			230/460//190/380
Full Load Amps			34.4/17.2//29/14.5
R.P.M.			3530//2940
Hz	60//50	**Phase**	3
NEMA Design Code	A	**KVA Code**	H
Service Factor (S.F.)			1.15
NEMA Nom. Eff.	91	**Power Factor**	88
Rating - Duty			40C AMB-CONT
S.F. Amps			

380 V, 50 Hz: High Voltage Connection	
Full Load Torque	17.7 LB-FT
Start Configuration	direct on line
Breakdown Torque	97.6 LB-FT
Pull-up Torque	34.9 LB-FT
Locked-rotor Torque	43.2 LB-FT
Starting Current	125 A
No-load Current	5.79 A
Line-line Res. @ 25ºC	0.591 Ω
Temp. Rise @ Rated Load	42°C
Temp. Rise @ S.F. Load	51°C
Locked-rotor Power Factor	33.3
Rotor inertia	0.868 LB-FT2


Load Characteristics 380 V, 50 Hz, 10 HP


% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	51	73	82	87	89	89	88
Efficiency	84.8	90.1	91.3	91.2	91	90.6	91.1
Speed	2986	2973	2959	2946	2931	2914	2937
Line amperes	6.62	8.7	11.3	14.2	17.3	20.7	16.1



ABB Motors and Mechanical Inc.
WINDING # 09WGZ864
Typical performance - not guaranteed values.
10 HP 3 PH 50 HZ 2946 RPM 380 V 0934M
TORQUES(LB-FT): PO=97.6 PU=34.9 LR=43.2 LRA=125
TORQUE
RPM
KW
AMPS
EFF
PF
%EFF %PF
TORQUE (LB-FT)
RPM
KW
AMPS
PERCENT OF RATED OUTPUT (10 HP)
11/5/2026 ACPERF, record # 38687


09LYE270
(922-964) = 25.54
12.29
4.20
4.00
.38 KEY
2.88 LONG
Ø 1.625
1.624
8 HOLES
Ø .53
8.25
8.25
.75
10.00
4.25
11.50
13.65
11.23
6.96
2.50
13.15
6.25
6.19
LEAD HOLE
1.25 N.P.T.
5.00
5.00
8.57
5.85
11.70
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT AUTOCAD DRW TO SWD
REV: K
VERSION: 07
REVISED: 12:31:31 05/20/2023
TDR: 000001208005
MODEL NO. 09LYE270
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
HORZ XPFC 254-6T CL.I GP.D,CL.II GP.F&G
09LYE270

CD0180







NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1