



## G-Tek® Perfect Fit®

Seamless Knit A4 Engineered Yarn Glove with Polyurethane Coated Grip on Palm & Fingers - Touchscreen - Vend-Ready

- Vend pack ready for Personal Protective Equipment (PPE) vending machines in the industrial workplace
- Seamless construction offers increased comfort and breathability
- Lightweight 18-gauge engineered blend liner provides excellent dexterity, tactile sensitivity, and cut resistance
- Polyurethane is thin, yet durable and provides excellent tactility, abrasion resistance and grip on dry surfaces
- Touchscreen compatible to allow the user to operate a touch screen phone or device without removing gloves
- ESD safe construction makes these gloves safe for use with static sensitive materials



## Technical Data

|                      |                                                        |
|----------------------|--------------------------------------------------------|
| Color                | Gray                                                   |
| Sizes Available      | XS-2XL                                                 |
| Packaging            | Vend Packed                                            |
| Packed               | 100 Pair/Case                                          |
| Case Dimensions (in) | 98.30 x 5.00 x 35.00                                   |
| Case Weight (lbs)    | 13.03                                                  |
| Country of Origin    | China                                                  |
| Liner Material       | HPPE, Nylon                                            |
| Coating              | Polyurethane                                           |
| Coating Color        | Black                                                  |
| Coating Coverage     | Palm & Fingers                                         |
| Gauge                | 18                                                     |
| Cuff                 | Knit Wrist                                             |
| Construction         | Coated Seamless Knit, Touchscreen Compatible, ESD Safe |
| Certifications       | 21 CFR, Silicone Free, EN 16350                        |

## Performance Data

|                     |       |
|---------------------|-------|
| Cut Level           | A4    |
| ANSI Abrasion Level | 3     |
| ANSI Puncture Level | 3     |
| EN 388              | 3X42D |

## Care Instructions



## SKU Information

| SKU              | COLOR | SIZE | UPC          | UPC (INNER)  | UPC (CASE)   |
|------------------|-------|------|--------------|--------------|--------------|
| NPF24-0118N-V-6  | Gray  | XS   | 883940459561 | 883940463544 | 883940463544 |
| NPF24-0118N-V-7  | Gray  | S    | 883940459578 | 883940463551 | 883940463551 |
| NPF24-0118N-V-8  | Gray  | M    | 883940459585 | 883940463568 | 883940463568 |
| NPF24-0118N-V-9  | Gray  | L    | 883940459592 | 883940463575 | 883940463575 |
| NPF24-0118N-V-10 | Gray  | XL   | 883940459608 | 883940463582 | 883940463582 |
| NPF24-0118N-V-11 | Gray  | 2XL  | 883940459615 | 883940463599 | 883940463599 |