ABB BALDOR RELIANCE

Customer information packet

VEM4108T

30HP, 3520RPM, 3PH, 60HZ, 286TSC, 0950M, TEFC
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 6:10:07 PM

Specifications

Enclosure	TEFC
Frame	286TSC
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	30.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	CURUSEEV
	NEMA PREMIUM
	NEMA PREMIUM (OLD LOGO)
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	68.000 A @ 230.0 V
	74.000 A @ 208.0 V
	34.000 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part Detail

Revision	P
Type	AC
Mech. spec.	09F909
Base	
Status	PRD/A
Elec. spec.	09WGT474
Layout	09LYF909
Eff. date	06-27-2024
CD Diagram	CD0180
Poles	02
Leads	9#10
Proprietary	False
Created date	11-09-2017

Heater Indicator	No Heater
High Voltage Full Load Amps	34.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 10 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0950M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	22.45 IN
Power Factor	89
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	3520 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2	None

Nameplate

NP3443LUA												
CAT.NO.	VEM4108T			**CUST. P/N**							**ENCL**	TEFC
SPEC.	09F909T474G1	**CC**	010A	**FRAME**	286TSC		**SER.NO.**					
HP	30		**CLASS**	F	**HZ**	60						
R.P.M.	3520		**PH.**	3	**DES.**	A						
VOLTS	230/460			**CODE**	J		**ODE BRG**	6208	**DE BRG**	6311		
AMPS	68/34											
RATING	40C AMB-CONT			**NEMA NOM. EFF.**	91.7			**GREASE**	POLYREX EM			
P.F.	89	**SER.F.**	1.15	**CT6-60H(10:1)VT3-60H(20:1**								
USABLE AT	50Hz 30HP 190/380V 82/41A			1.0SF								
VOLTS	**AMPS**		**MAX. SPACE HEATER TEMP.**									

AC Induction Motor Performance Data
Record # 67631
Typical performance - not guaranteed values

Winding: 09WGT474-R001	**Type:** 0950M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			30	**Full Load Torque**	44.65 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			68/34	**Breakdown Torque**	173 LB-FT
R.P.M.			3520	**Pull-up Torque**	87.6 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	104 LB-FT
NEMA Design Code	A	**KVA Code**	J	**Starting Current**	283 A
Service Factor (S.F.)			1.15	**No-load Current**	10.9 A
NEMA Nom. Eff.	91.7	**Power Factor**	90	**Line-line Res. @ 25ºC**	0.2527 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	79°C
S.F. Amps				**Temp. Rise @ S.F. Load**	97°C
				Locked-rotor Power Factor	28

Load Characteristics 460 V, 60 Hz, 30 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	58	78	86	89	90	91	90
Efficiency	87.7	91.8	92.4	92.1	91.3	90.2	91.6
Speed	3580.7	3562.2	3542.3	3521	3497.7	3471	3507
Line amperes	13.7	19.4	26.4	34.2	42.4	51.3	39.1


ABB Motors and Mechanical Inc.


WINDING # 09WGT474

30 HP 3 PH 60 HZ 3520 RPM 460 V 0950M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=173 PU=87.6 LR=104 LRA=283





09LYF909
(932 - 952)
(954 - 956 4,6,8 PL ONLY)
22.45
10.11
.25
3.00
.38 KEY
1.88 LONG
Ø10.500
10.497
Ø11.21
Ø1.625
1.624
SLINGER
AUTO DRAIN
(EA. END)
13.04
11.56
6.70
2.72
45°
45°
LEAD HOLE
Ø2.00
9.01
4 HOLES
.50 - 13 TAP
.88 DEEP ON
Ø9.00 B.C
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LIFECYCLE, REPLACE 09SF1113A14 W/09SF1108A28
REV: J
VERSION: 09
REVISED: 02:27:44 03/01/2022
TDR: 000001186553
MODEL NO. 09LYF909
REF: -
BY: ENFRAJ0
B
BALDOR - RELIANCE®
VERT TEFC 284-6TSC W/SPL SHOVE
09LYF909

CD0180







NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1