ABB BALDOR RELIANCE

Customer information packet

EJMM3313T

10HP, 1770RPM, 3PH, 60HZ, 215JM, 3742M, OPSB
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 3:28:55 PM

Specifications

Enclosure	OPSB
Frame	215JM
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	CSA
	CSA EEV
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	25.000 A @ 230.0 V
	26.000 A @ 208.0 V
	12.500 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part Detail

Revision	AB
Type	AC
Mech. spec.	37F784
Base	
Status	PRD/A
Elec. spec.	37WGT853
Layout	37LYF784
Eff. date	06-11-2024
CD Diagram	CD0005
Poles	04
Leads	9#14
Proprietary	False
Created date	01-01-0001

Heater Indicator	No Heater
High Voltage Full Load Amps	12.5 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3742M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	19.31 IN
Power Factor	82
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	Included
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor

Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3553LUA									
CAT.NO.	EJMM3313T								
SPEC.	37F784T853								
HP	10								
VOLTS	230/460								
AMPS	25/12.5								
RPM	1770								
FRAME	215JM	**HZ**	60			**PH**	3		
SF	1.15	**CODE**	H	**DES**	B	**CLASS**	F		
NEMA NOM. EFF	91.7	**PF**	82						
RATING	40C AMB-CONT								
CC	010A								
ENCL	OPSB	**SN**							
DE	6309	**ODE**	6206						
VPWM INVERTER READY									
CT30-60(2:1) VT3-60(20:1)									
USABLE AT	50HZ 7.5HP 190/380V 23.2/11.6A								SF1.0

AC Induction Motor Performance Data
Record # 53404
Typical performance - not guaranteed values

Winding: 37WGT853-R026	**Type:** 3742M	**Enclosure:** OPSB

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			10	**Full Load Torque**	29.7 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			25/12.5	**Breakdown Torque**	87.58 LB-FT
R.P.M.			1770	**Pull-up Torque**	44.18 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	51.57 LB-FT
NEMA Design Code	B	**KVA Code**	H	**Starting Current**	86.72 A
Service Factor (S.F.)			1.15	**No-load Current**	4.91 A
NEMA Nom. Eff.	91.7	**Power Factor**	82	**Line-line Res. @ 25ºC**	1.18 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	34°C
S.F. Amps				**Temp. Rise @ S.F. Load**	43°C
				Locked-rotor Power Factor	37.9
				Rotor inertia	1.03 LB-FT2

Load Characteristics 460 V, 60 Hz, 10 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	48	70	80	84	86	86	83
Efficiency	87.7	91.8	92.2	91.7	90.8	89.5	91.4
Speed	1793	1785	1777	1769	1759	1749	1763
Line amperes	5.6	7.31	9.53	12.15	15	18.24	14.2


ABB Motors and Mechanical Inc.


WINDING # 37WGT853

10 HP 3 PH 60 HZ 1770 RPM 460 V 3742M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=87.58 PU=44.18 LR=51.57 LRA=86.72




37LYF784
717-735 = 18.19
736-744 = 19.32
745-750 = 20.07
751-756 = 20.82
4.25
CHECK
W/GAUGE T-9038
2.890
2.860
.26
.640
.610
.188 KEYWAY
1.69 LONG
ENDMILLED
(KEY
1.38 LONG)
3.44
GREASE FITTING
(EA. END)
NAMEPLATE
Ø9.09
Ø 1.0000
.9995
Ø 1.250
1.248
Ø .8745
.8740
Ø8.500
8.497
.38-16 R.H.TAP
.88 DEEP
6 HOLES
Ø.43
5.50
.50
7.00
4.25
8.00
GREASE RELIEF
(EA. END)
Ø9.57
7.90
45°
45°
4 HOLES
.50-13 TAP ON
Ø7.25 B.C.
LIFTING LUG
(1 EA. END)
10.03
5.25
5.19
LEAD
HOLE
Ø1.38
4.25
4.25
6.72
4.75
9.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERSION OF ACAD TO SWD INOPC PKG 19
REV: J
VERSION: 03
REVISED: 10:13:02 10/11/2022
TDR: 000001197758
MODEL NO. 37LYF784
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
STD HORZ 213-5JM OPSB 37M SUPER-E
37LYF784

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS