

Product Specifications



Post Office Box 97
Benton Harbor, Michigan
Ph: 616/926-6171
Fax: 616/925-8288

Model Number	MAX. PRESS.		MAX. SPEED	HP	kW	Net Wt.	
	bar.	PSI				lbs.	kg
16AM-FRV-13	7,0	100	2,000 RPM	9.0	6,7	80	36.3
* 16AM-FRV-33	7,0	100	2,000 RPM	9.0	6,7	80	36.3
* 16AM-FRV-13B	7,0	100	2,000 RPM	9.0	6,7	80	36.3

PART NUMBER: LTD111
REVISION: G

NOTES:

1. TECHNICAL DATA SUBJECT TO CHANGE WITHOUT NOTICE.
2. * DENOTES INACTIVE MODEL.

SOUND LEVEL 113 dba MAX.

NORMAL AMBIENT +1°C. - 120°C.

RELATIVE HUMIDITY 0% - 100%

ENVIRONMENT HAZARDOUS AMBIENT COMBUSTIBLE
GAS AND DUST +1°C TO +40°C

CONFORMS TO EUROPEAN STANDARD EN13463-1
NON-ELECTRICAL EQUIPMENT FOR EXPLOSIVE
ATMOSPHERES GROUP II CAT 2 (GAS & DUST).
PROTECTED BY CONSTRUCTION
(SURFACE TEMP. RATED 135±C).

