

Door Skin Replacement		
1		<p>Door Frame Preparation</p> <p>Using a grade 80 abrasive belt, remove remaining weld nugget material from door frame. Clean and prep remaining mating flanges on door frame with a coarse Scotch-Brite™ belt.</p>
2		<p>Clean</p> <p>Clean door frame and replacement panel mating flange areas with a VOC compliant surface cleaner.</p>
3		<p>Replacement Skin Prep</p> <p>Scuff replacement skin mating flange areas using Scotch-Brite™ hand pad.</p>
4		<p>Dry Fit Panel</p> <p>Dry fit replacement panel and complete any necessary metal straightening at flanges areas. Remove door skin in preparation for adhesive application.</p>
5		<p>NVH Replacement</p> <p>Apply NVH material at original locations on intrusion beam.</p>
6		<p>Apply Bonding Adhesive</p> <p>Re-clean bonding surfaces with a VOC compliant surface cleaner. Apply adhesive to door frame covering all bare metal areas. Apply an additional bead of adhesive at mating flange areas to ensure proper bond line thickness.</p>
7		<p>Install Door Skin</p> <p>Install replacement door skin onto door frame. Crimp hem flange using hammer and dolly. Clamp as necessary. (For aluminum panels, follow OEM recommended flanging procedures.)</p>
8		<p>Clamp and Cure</p> <p>Follow recommended adhesive clamp and cure times. Clean any adhesive squeeze-out from hem flange area with a VOC compliant cleaner.</p>
9		<p>Seam Sealing</p> <p>Re-apply seam sealer to hem flange as required following general seam sealing guidelines.</p>

Visit www.3MCollision.com for more SOPs and videos

Product List	
3M™ File Belt Sander, PN 28366	
3M™ Cubitron™ II File Belt, grade 80+, PN 33446	
Scotch-Brite™ Durable Flex Belt, CRS, PN 64475	
Scotch-Brite™ Durable Flex Hand Pad, MX-HP, 4-1/2 in. x 9 in., Very Fine, PN 64659	
Scotch-Brite™ 7447 PRO Hand Pads, Very Fine, 6 in. x 9 in., PN 64926	
3M™ NVH Dampening Material, PN 04274	
3M™ Urethane Seam Sealer, PN 08361	
3M™ MSP Seam Sealer, PN 08370	
3M™ Panel Bonding Adhesive, 50mL, PN 38315; 200mL, PN 08115; 200mL, PN 08116; 450mL DMS, PN 58115	
3M™ SMC/FRP Panel Adhesive, 200mL, PN 08219	
3M™ Bare-Metal Seam Sealer 200mL, PN 08310; 600mL DMS, PN 58310	
3M™ EZ Sand Multi-Purpose Flexible Adhesive, 200mL, PN 05887; 600mL DMS, PN 55887	

Think About Your Health	
3M™ E-A-R™ Skull Screws™ Ear Plug, PN P1300	
3M™ Half Facepiece Respirator, PN 07182	
3M™ Lexa™ Protective Eyewear, PN 15200	

Individual Product Instruction and Safety Information

For individual product instructions and applicable precautions see product labels and associated literature for the individual product at www.3MCollision.com

For product material safety data sheets see www.3MCollision.com

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy and Disclaimer: Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

IMPORTANT NOTE: There are of course many factors and variables that can affect an individual repair, so the technician and repair facility need to evaluate each specific application and repair process, including relevant vehicle, part and OEM guidelines, and determine what is appropriate for that repair.



3M Automotive Aftermarket Division
3M Center, Building 223-6N-01
St. Paul, MN 55144-1000
U.S.A.

3M, Accuspray, Body Schutz, Cubitron, E-A-R, Green Corps, Hookit, Lexa, Perfect-It, Platinum, PPS, Roloc, Scotch, Scotchblok, Scotch-Brite, Skull Screws, SUN GUN and Trizact are trademarks of 3M. All other trademarks are property of their respective owners.

Web: www.3MCollision.com

Please recycle. Printed in U.S.A. © 3M 2016. All rights reserved. (Rev 5/2016)