ABB BALDOR RELIANCE

Customer information packet

EL11209M

.5HP, 1725RPM, 1PH, 60HZ, 48, 3424LC, OPEN, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 11:54:05 AM

Specifications

Enclosure	OPEN
Frame	48
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	.500 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	115.0 V @ 60 HZ
Agency Approvals	CURUSEEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	4.400 A @ 115.0 V
	2.500 A @ 208.0 V
	2.200 A @ 230.0 V
Design Code	N
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	76.2 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	2.2 a

Part Detail

Revision	H
Type	AC
Mech. spec.	34F868
Base	
Status	PRD/A
Elec. spec.	34WGR217
Layout	34LYF868
Eff. date	10-29-2024
CD Diagram	CD0881
Poles	04
Leads	7#18
Proprietary	False
Created date	10-02-2014

Insulation Class	F
Inverter Code	Not Inverter
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	7 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3424LC
Mounting Arrangement	F1
Number of Poles	4
Overall Length	10.63 IN
Power Factor	98
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.25
Shaft Diameter	0.500 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1725 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	Manual Thermal Overload
Winding Thermal 1 Location	SB

Winding Thermal 2	None

Nameplate

NP3273L									
CAT.NO.	EL11209M								
SPEC.	34F868R217G1								
HP	.5								
VOLTS	115/230								
AMP	4.4/2.2								
RPM	1725								
FRAME	48	**HZ**	60				**PH**	1	
SER.F.	1.25	**CODE**	K	**DES**	N	**CL**	F		
F.L. AVG. EFF.	76.2	**PF**	98						
RATING	40C AMB-CONT								
CC									
DE	6203	**ODE**	6203						
ENCL	OPEN	**SN**							
	SFA 5.8/2.9								

AC Induction Motor Performance Data
Record # 62065
Typical performance - not guaranteed values

Winding: 34WGR217-R002	**Type:** 3424LC	**Enclosure:** OPEN

Nameplate Data				**115 V, 60 Hz: Low Voltage Connection**	
Rated Output (HP)			.5	**Full Load Torque**	1.51 LB-FT
Volts			115/230	**Start Configuration**	direct on line
Full Load Amps			4.4/2.2	**Breakdown Torque**	4.01 LB-FT
R.P.M.			1725	**Pull-up Torque**	3.75 LB-FT
Hz	60	**Phase**	1	**Locked-rotor Torque**	6.42 LB-FT
NEMA Design Code	N	**KVA Code**	K	**Starting Current**	31.9 A
Service Factor (S.F.)			1.25	**No-load Current**	1.06 A
NEMA Nom. Eff.	76.2	**Power Factor**	98	**Line-line Res. @ 25ºC**	1.6786 Ω A Ph 2.0496 Ω B Ph
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	37°C
S.F. Amps			5.8/2.9	**Temp. Rise @ S.F. Load**	55°C

Load Characteristics 115 V, 60 Hz, 0.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	89	94	95	95	95	94	95
Efficiency	59.9	73	76.8	76.6	73.3	67.1	73.3
Speed	1782.8	1767.7	1748.6	1726.8	1694.2	1648.1	1694
Line amperes	1.56	2.34	3.34	4.39	5.8	7.69	5.8


ABB Motors and Mechanical Inc.


WINDING # 34WGR217

0.5 HP 1 PH 60 HZ 1725 RPM 115 V 3424LC


Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=4.01 PU=3.75 LR=6.42 LRA=31.9




34LYF868
408-419 = 9.76
420-426 = 10.63
427-430 = 11.13
1.82
1.75
1.50
NAMEPLATE
.453
.433
Ø .5000
.4995
4 SLOTS
.34 WIDE
.63
2.75
2.50
4.00
Ø 5.67
5.07
2.28
5.80
3.00
2.94
LEAD HOLE
.88 DIA.
2.13
2.13
3.54
2.88
5.75
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT FROM AUTOCAD TO SWD
REV: A
VERSION: 01
REVISED: 01:06:14 10/17/2023
TDR: 000001218663
MODEL NO. 34LYF868
REF: -
BY: USALMAZ
B
BALDOR - RELIANCE®
STD HOR 34LC NEMA 48 OPEN W/ 3 PHASE ENDRINGS
34LYF868

CD0881



	LINE A	LINE B	JOIN	JOIN
HIGH STD	1	4	2,3,8	J,5
HIGH OPP	1	4	2,3,5	J,8
LOW STD	1,3,8	4	–	2,J,5
LOW OPP	1,3,5	4	–	2,J,8

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
3. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REMOVE OPTIONAL THERMAL CONNECTION			BALDOR ELECTRIC Co.
REV. LTR: C	VERSION: 01	TDR: 000000373051	
CD0881	FILE: \AAA\00007\429	REVISED: 11:52:48 09/09/2005	TYPE LC, DV, REV, THERMAL, 7 LEAD
	MTL: –	BY: ENJOEP0	

CD0881