

GENERAL PURPOSE PORTABLE SHOP VACUUMS

Portable shop vacuums are designed to provide excellent cleaning maintenance where portability and versatility is required. For moderate frequency use in general purpose applications.

- Compact and lightweight
- Durable plastic tank with top carry handle
- Powerful single stage motor
- On-Board tool storage



61HV76

61HV77



61HV78



61HV79



61HV80

2, 3 & 4 Gallon Plastic Tanks

Includes:

- Nos. 61HV76 and 61HV77 feature 6 ft. x 1.25 in. diameter hose, reusable cloth filter, foam filter sleeve and deluxe 4-piece 1.25 in. diameter tool set.
- No. 61HV78 features 8 ft. x 1.25 in. diameter clip attached hose, standard cartridge filter, disposable filter bag, foam filter sleeve, deluxe 9-piece 1.25 in. diameter tool set, integral wide stance caster system and convertible blower port with muffler/diffuser accessory.
- No. 61HV79 features 7 ft. x 1.25 in. diameter clip attached hose, standard cartridge filter, disposable filter bag, foam filter sleeve, and deluxe 5-piece 1.25 in. diameter tool set.
- No. 61HV80 features 8 ft. x 1.25 in. diameter clip attached hose, standard cartridge filter, disposable bag and foam sleeve, convertible blower port with muffler/diffuser accessory, integral wide stance caster system with large rear wheels and deluxe 8-piece 1.25 in. diameter tool set.

Item No.	Tank Size (Gal)*	Tank Type	Peak HP ¹	Amps @120V	Average Brush Life (Hrs.)	CFM Air Flow ¹	Static Pressure (In.) ¹	Air Watts ¹	Power Cord Length (Ft.)
2, 3, & 4 Gallon Plastic Tanks									
61HV76	2	Plastic	1.5	5.0	300	40	58	90	18
61HV77	3	Plastic	3.0	8.0	300	60	56	121	18
61HV78	4	Plastic	4.0	8.0	300	63	53	123	18
61HV79	4	Plastic	5.0	9.0	400	73	53	142	20
61HV80	4	Plastic	5.0	9.0	400	70	53	135	18
Filters and Bags									
783GC3	Reusable cloth filter for 61HV76 and 61HV77								
61HV97	Cartridge filter for 61HV78, 61HV79 and 61HV80								
783GC2	Disposable filter bag for 61HV78, 61HV79 and 61HV80								
61HW04	Foam filter sleeve for 61HV76								

GENERAL PURPOSE SHOP VACUUMS

General purpose shop vacuums are designed for moderate frequency use in general purpose applications.

- Standard cartridge filter, disposable filter bag and foam filter sleeve
- Convertible blower port with muffler/diffuser accessory
- Integral wide stance swivel caster system
- Durable plastic and stainless steel tanks
- On-Board tool storage
- Large water-resistant on/off switch

6, 8, 10 & 12 Gallon Tanks

Includes:

- No. 61HV81 features 8 ft. x 1.25 in. diameter clip attached hose, single-stage motor, deluxe 7-piece 1.25 in. diameter tool set.
- No. 61HV82 features 8 ft. x 1.25 in. diameter clip attached hose, single-stage motor, deluxe 6-piece 1.25 in. diameter tool set and tank drain.
- No. 61HV90 features 12 ft. x 1.88 in. diameter clip attached hose, powerful long life 2-stage by-pass motor, platform dolly, deluxe 9-piece 1.88 in. diameter tool set and tank drain.
- No. 61HV83 features 8 ft. x 1.25 in. diameter clip attached hose, single-stage motor, deluxe 6-piece 1.25 in. diameter tool set.
- No. 61HV84 features 8 ft. x 2.5 in. diameter clip attached hose, single stage motor, deluxe 8-piece 2.5 in. diameter tool set and tank drain.
- No. 61HV89 features 12 ft. x 1.88 in. diameter clip attached hose, powerful 2-stage by-pass motor, heavy duty casters with large rear wheel dolly, metal transport handle, deluxe 9-piece 1.88 in. diameter tool set and tank drain.



61HV81



61HV82



61HV90



61HV83



61HV84



61HV89

Item No.	Tank Size (Gal)*	Tank Type	Peak HP [†]	Amps @120V	Average Brush Life (Hrs.)	CFM Air Flow [†]	Static Pressure (In.) [†]	Air Watts [†]	Power Cord Length (Ft.)
6, 8, 10, & 12 Gallon Tanks									
61HV81	6	Plastic	4.0	9.0	400	72	53	140	12
61HV82	8	Plastic	5.0	10.0	400	78	78	230	12
61HV90	8	SS	6.0	10.0	1000	85	84	275	18
61HV83	10	Plastic	5.0	10.0	400	75	80	235	12
61HV84	12	Plastic	6.5	10.5	600	103	78	272	18
61HV89	12	Plastic	6.0	10.0	1000	85	80	265	18
Filters and Bags									
61HV96	Cartridge filter for 61HV81, 61HV82, 61HV90, 61HV83 and 61HV84								
61HV98	Cartridge filter for 61HV89								
61HW05	Disposable filter bag for 61HV81, 61HV82 and 61HV90								
61HW06	Disposable filter bag for 61HV83 and 61HV84								
61HW09	Disposable filter bag for 61HV89								
61HW04	Foam filter sleeve for 61HV81, 61HV82, 61HV90, 61HV83, 61HV84 and 61HV89								

GENERAL PURPOSE SHOP VACUUMS (CONTINUED)



61HV86



61HV91



61HV85



61HV87

12 & 16 Gallon Tanks

Includes:

- No. 61HV86 features 8 ft. x 1.25 in. diameter clip attached hose, single stage motor, deluxe 7-piece 2.5 in. diameter tool set and tank drain.
- No. 61HV91 features 12 ft. x 1.88 in. diameter clip attached hose, powerful long life 2-stage by-pass motor, large rear wheel dolly, metal transport, deluxe 9-piece 1.88 in. diameter tool set and tank drain.
- No. 61HV85 features 8 ft. x 2.5 in. diameter clip attached hose, single stage motor, deluxe 8-piece 2.5 in. diameter tool set and tank drain.
- No. 61HV87 features 8 ft. x 2.5 in. diameter clip attached hose, single stage motor, large rear wheel dolly, metal transport handle, deluxe 8-piece 2.5 in. diameter tool set and tank drain.

Item No.	Tank Size (Gal)*	Tank Type	Peak HP ¹	Amps @120V	Average Brush Life (Hrs.)	CFM Air Flow ¹	Static Pressure (In.) ¹	Air Watts ¹	Power Cord Length (Ft.)
12 & 16 Gallon Tanks									
61HV86	12	SS	6.0	10.5	600	114	75	285	18
61HV91	12	SS	6.0	10.0	1000	85	80	275	18
61HV85	16	Plastic	6.5	10.5	600	102	80	269	18
61HV87	16	SS	6.0	10.5	600	105	80	275	18
Filters and Bags									
61HV96	Cartridge filter for 61HV86, 61HV91, 61HV85 and 61HV87								
61HW06	Disposable filter bag for 61HV86 and 61HV91								
61HW10	Disposable filter bag for 61HV85 and 61HV87								
61HW04	Foam filter sleeve for 61HV86, 61HV91, 61HV85 and 61HV87								



GENERAL PURPOSE SHOP VACUUMS WITH NEW QUIET TECHNOLOGY

General purpose shop vacuums are designed for moderate frequency use in general purpose applications.



807HR6

- Sound level 65dB
- Standard cartridge filter, disposable filter bag and foam filter sleeve
- Study handle with tabs for easy cord storage
- Convertible blower port with muffler/diffuser accessory
- Durable plastic tank
- Integral wide stance swivel caster system
- On-Board tool storage
- Large water-resistant on/off switch
- Powerful single-stage motor

**50%
QUIETER™**



807HR7

9, 12 & 16 Gallon Plastic Tanks

- No. 807HR6 features 7 ft. x 1.88 in. diameter clip attached hose, and 8-piece 1.88 in. diameter tool set.
- Nos. 807HR7 and 807HR8 feature 8 ft. x 2.5 in. diameter clip attached hose, deluxe 7-piece 2.5 in. diameter tool set and tank drain.



807HR8

Item No.	Tank Size (Gal)*	Tank Type	Peak HP†	Amps @120V	Average Brush Life (Hrs.)	CFM Air Flow†	Static Pressure (In.)†	Air Watts†	Power Cord Length (Ft.)
9, 12 & 16 Gallon Plastic Tanks									
807HR6	9	Plastic	5.5	8.0	500	97	75	250	10
807HR7	12	Plastic	6.0	8.0	500	104	75	260	16
807HR8	16	Plastic	6.5	8.0	500	108	78	260	16
Filters and Bags									
61HV96	Cartridge filter for 807HR6, 807HR7, 807HR8								
61HV06	Disposable filter bag for 807HR6 and 807HR7								
61HV10	Disposable filter bag for 807HR8								
61HW06	Foam filter sleeve for 807RH6, 807RH7, 807RH8								



SPECIALTY WALL-MOUNT SHOP VACUUMS

Specialty wall-mount shop vacuums feature 18 foot long hoses to tackle tough and unique cleaning applications.

- Powerful single stage motor
- Deluxe 7-Piece 1.25 in. diameter tool set
- 18 ft. x 1.25 in. diameter clip attached hose
- Large water-resistant on/off switch

4.5 Gallon Wall-Mount Vacuums

Includes:

- No. 61HV94 features standard cartridge filter, disposable filter bag, foam filter sleeve and plastic tank.
- No. 61HV95 features HEPA cartridge filter, disposable filter bag, foam filter sleeve and stainless steel tank.



61HV94



61HV95

Item No.	Tank Size (Gal)*	Tank Type	Peak HP [†]	Amps @120V	Average Brush Life (Hrs.)	CFM Air Flow [†]	Static Pressure (In.) [†]	Air Watts [†]	Power Cord Length (Ft.)
4.5 Gallon Wall-Mount Vacuums									
61HV94	4.5	Plastic	3.0	6.0	300	48	55	97	6
61HV95	4.5	SS	3.5	6.0	300	48	51	90	18
Filters and Bags									
61HV97	Cartridge filter for 61HV94								
61HW02	HEPA cartridge filter for 61HV95								
61HW15	Disposable filter bag for 61HV94 and 61HV95								

COMMERCIAL SHOP VACUUMS

Commercial shop vacuums are designed for high frequency use in heavy duty and Jan-San applications.

- Large water-resistant on/off switch
- Quiet operation motor housing
- Standard cartridge filter, disposable filter bag and foam filter sleeve
- Durable plastic tank
- On-Board tool storage
- Convertible blower port with muffler/diffuser accessory
- Heavy duty integral wide stance swivel caster system

6 Gallon Plastic Tank

Includes:

- No. 61HV88 features 8 ft. x 1.25 in. diameter clip attached hose and deluxe 8-piece 1.25 in. diameter tool set.



61HV88

Item No.	Tank Size (Gal)*	Tank Type	Peak HP [†]	Amps @120V	Average Brush Life (Hrs.)	CFM Air Flow [†]	Static Pressure (In.) [†]	Air Watts [†]	Power Cord Length (Ft.)
6 Gallon Plastic Tank									
61HV88	6	Plastic	4.5	10.0	400	73	84	225	18
Filters and Bags									
61HV96	Cartridge filter for 61HV88								
61HW08	Disposable filter bag for 61HV88								
61HW04	Foam filter sleeve for 61HV88								

INDUSTRIAL SHOP VACUUMS

Industrial shop vacuums are designed for high frequency use in heavy duty and Jan-San applications.

- Powerful long life 2-stage by-pass motor
- HEPA cartridge filter, disposable filter bag and foam filter sleeve
- Convertible blower port with muffler/diffuser accessory
- Metal transport handle
- Large water-resistant on/off switch
- Quiet operation motor housing
- Durable stainless steel tank
- Heavy duty large rear wheel dolly
- On-Board tool storage
- Large tank drain



61HV92

16 Gallon Stainless Steel Tank

Includes:

- No. 61HV92 features 12 ft. x 1.88 in. diameter clip attached hose and deluxe 9-piece 1.88 in. diameter tool set.

Item No.	Tank Size (Gal)*	Tank Type	Peak HP [†]	Amps @120V	Average Brush Life (Hrs.)	CFM Air Flow [†]	Static Pressure (In.) [†]	Air Watts [†]	Power Cord Length (Ft.)
16 Gallon Stainless Steel Tank									
61HV92	16	SS	6.0	10.0	800	80	85	250	18
Filters and Bags									
61HW01	Cartridge filter for 61HV92								
61HW10	Disposable filter bag for 61HV92								
61HW04	Foam filter sleeve for 61HV92								

DRUM-TOP VACUUM HEAD

Drum-Top vacuum heads are designed to mount on 55 gallon full remove head (FRH) drums to suction industrial debris for storage or disposal.



61HV93

Includes:

- No. 61HV93 features heavy duty durable metal housing, 12 ft. x 1.88 in. diameter hose, powerful 2-stage by-pass motor, convertible blower port, standard cartridge filter, foam filter sleeve, deluxe 2-piece 1.88 in. diameter tool set and three lid latches.

Item No.	Peak HP [†]	Amps @120V	Average Brush Life (Hrs.)	CMF Air Flow [†]	Static Pressure (In.) [†]	Air Watts [†]	Power Cord Length (Ft.)
Drum-Top Vacuum Head							
61HV93	3.0	10	600	88	84	288	18
Filters and Bags							
61HV98	Cartridge filter for 61HV93						
61HW04	Foam filter sleeve for 61HV93						

DRY & WET/DRY VACUUM FILTERS AND ACCESSORIES

Cartridge Filters



61HV96

Standard Cartridge Filter

Large size filter, standard filtration type, for shop vacuums. Fits vacuum Item Nos. 61HV81, 61HV82, 61HV83, 61HV84, 61HV85, 61HV86, 61HV87, 61HV88, 61HV89, 61HV90, 61HV91, 61HV92, 61HV93, 807HR6, 807HR7 & 807HR8. Replaces filter Item No. 2W435.



61HV97

Standard Cartridge Filter

Small size filter, standard filtration type, for shop vacuums. Fits vacuum Item Nos. 61HV78, 61HV79, 61HV80, 61HV94 & 61HV95.



783GA8

Standard Cartridge Filter

Small size filter, standard filtration type, for shop vacuums. Replaces filter Item No. 4TB95.



61HV98

Standard Cartridge Filter

Large size filter, high efficiency filtration type, for shop vacuums. Up to 97% efficient on particle sizes as small as 0.3 microns. Fits vacuum Item Nos. 61HV81, 61HV82, 61HV83, 61HV84, 61HV85, 61HV86, 61HV87, 61HV88, 61HV89, 61HV90, 61HV91, 61HV92 & 61HV93. Replaces filter Item No. 45UZ58.



61HV99

Standard Cartridge Filter

Small size filter, high efficiency filtration type, for shop vacuums. Up to 97% efficient on particle sizes as small as 0.3 microns. Fits vacuum Item Nos. 61HV78, 61HV79, 61HV80, 61HV94 & 61HV95.



783GA9

Standard Cartridge Filter

Small size filter, high efficiency filtration type, for shop vacuums. Up to 97% efficient on particle sizes as small as 0.3 microns. Replaces filter Item No. 55EY33.



61HW01

HEPA Cartridge Filter

Large size filter, HEPA filtration type, for shop vacuums. Up to 99.97% efficient on particle sizes as small as 0.3 microns. Fits vacuum Item Nos. 61HV81, 61HV82, 61HV83, 61HV84, 61HV85, 61HV86, 61HV87, 61HV88, 61HV89, 61HV90, 61HV91, 61HV92 & 61HV93. Replaces filter Item No. 4TB93.



61HW02

HEPA Cartridge Filter

Small size filter, HEPA filtration type, for shop vacuums. Up to 99.97% efficient on particle sizes as small as 0.3 microns. Fits vacuum Item Nos. 61HV78, 61HV79, 61HV80, 61HV94 & 61HV95.



783GC0

HEPA Cartridge Filter

Small size filter, HEPA filtration type, for shop vacuums. Up to 99.97% efficient on particle sizes as small as 0.3 microns. Replaces filter Item No. 6AKY8.



783GC1

Cartridge Filter Retainer Cap

Cartridge filter retainer cap for large size cartridge filters. Fits filter Item Nos. 2W435, 61HV96, 45UZ58, 61HV98, 4TB93 & 61HW01.

Reusable & Foam Filters



Reusable Filter

Disc filter, cloth, standard filtration type, for shop vacuum. Replaces filter Item No. 6H008.



Reusable Filter

Disc filter, cloth, standard filtration type, for shop vacuums. Fits vacuum Item Nos. 61HV76 & 61HV77.



Foam Filter

Foam filter sleeve, for wet pick-up. Fits vacuum Item Nos. 61HV76, 61HV81, 61HV82, 61HV83, 61HV84, 61HV85, 61HV86, 61HV87, 61HV88, 61HV89, 61HV90, 61HV91, 61HV92, 61HV93, 807HR6, 807HR7 & 807HR8.



Foam Filter

Foam filter sleeve, for wet pick-up. Fits vacuum Item No. 48UH44.

Disposable Filter Bags



Single Ply Filter Bags

- Standard filtration efficiency
- Use for everyday pick-up needs of general dirt and debris
- Dry filtration only

Item No.	Bags/Pkg.	Product Description
Single Ply Filter Bags		
61HW15	5	Fits vacuum Item Nos. 61HV94 & 61HV95
61HW05	5	Fits vacuum Item Nos. 61HV81, 61HV82 & 61HV90 Replaces filter bag Item No. 55EY35
61HW06	5	Fits vacuum Item Nos. 61HV83, 61HV84, 61HV86, 61HV91, 807HR6 & 807HR7. Replaces filter bag Item No. 55EY36
61HW07	5	Replaces filter bag Item No. 55EY37
783GZ0	3	Replaces filter bag Item No. 48UH45
783GC2	3	Fits vacuum Item Nos. 61HV78, 61HV79 & 61HV80

2-Ply Filter Bags

- Filtration efficiency 98% at 0.3 microns
- Improve air quality in fine dust applications
- Durable 2-ply construction with micro inner liner
- Dry filtration only



Item No.	Bags/Pkg.	Product Description
2-Ply Filter Bags		
783G99	5	Replaces filter bag Item No. 3UP64
61HW08	5	Fits vacuum Item No. 61HV88 Replaces filter bag Item No. 3UP65
61HW09	5	Fits vacuum Item No. 61HV89 Replaces filter bag Item No. 3UP66
61HW10	5	Fits vacuum Item Nos. 61HV85, 61HV87, 61HV92 & 807HR8. Replaces filter bag Item No. 1UG85



61HW11/61HW12



61HW13/61HW14

Tear Resistant Filter Bags

- Nos. 61HW11 and 61HW12 for dry filtration only
- Nos. 61HW13 and 61HW14 for wet/dry filtration
- Built-in collar handle to facilitate full bag removal
- Cap to plug bag intake to reduce dust escape while changing
- Made of durable material with plastic mounting collars to resist tears



Item No. Bags/Pkg.

Product Description

Tear Resistant Filter Bags		
61HW11	2	Fits vacuum Item Nos. 61HV81, 61HV82, 61HV83, 61HV88 & 61HV90 Replaces filter bag Item No. 45UZ59
61HW12	2	Fits Vacuum Item Nos. 61HV84, 61HV85, 61HV86, 61HV87, 61HV89, 61HV91 & 61HV92 Replaces filter bag Item No. 45UZ60.
61HW13	2	Fits vacuum Item Nos. 61HV81, 61HV82, 61HV83, 61HV88 & 61HV90 Replaces filter bag Item No. 45UZ61
61HW14	2	Fits vacuum Item Nos. 61HV84, 61HV85, 61HV86, 61HV87, 61HV89, 61HV91 & 61HV92 Replaces filter bag Item No. 45UZ62

Accessory Tools

For wet/dry vacuums with hose systems



61HW16

Round Brush

Fits 1.88 in. diameter hose, plastic, 5.5 in. long, 3 in. diameter brush head.



61HW17

Claw Nozzle

Fits 1.25 in., 1.5 in., 1.88 in. and 2.5 in. diameter hose, plastic, 11.8 in. long, 4.41 in. wide, includes hose adapter.



61HW18

Crevice Nozzle

Fits 1.88 in. diameter hose, plastic, 7.99 in. long, 2.17 in. wide.



61HW19

Utility Nozzle

Fits 1.25 in. diameter hose, plastic, 5.35 in. long, 5.43 in. wide.



61HW23

Vacuum Hose Adapter

Universal hose & tool adapter for use with shop vacuums & accessory tools, fits 1 in., 1.25 in., 1.5 in., 1.88 in. and 2.5 in. diameter hoses, vinyl, 6.65 in. long.



783GA7

Muffler/Diffuser Accessory

Muffler/Diffuser accessory installs on vacuum exhaust port for quieter operation and to diffuse exhaust port air flow, fits vacuum Item Nos. 61HV78, 61HV80, 61HV81, 61HV82, 61HV83, 61HV84, 61HV85, 61HV86, 61HV87, 61HV88, 61HV89, 61HV90, 61HV91, 61HV92, 807HR6, 807HR7 and 807HR8.

Vacuum Hoses



61HW20

Standard Hose with Hose Ends

- 8 ft. long, plastic, black.

Item No.	Product Description
Hose with Hose Ends	
61HW20	1.25 in. diameter hose with 2-piece hose end adapters
61HW22	2.5 in. diameter hose with 2-piece hose end adapters and 2.5 in. to 1.25 in. diameter hose adapter

Hose with Hose Ends

61HW20	1.25 in. diameter hose with 2-piece hose end adapters
61HW22	2.5 in. diameter hose with 2-piece hose end adapters and 2.5 in. to 1.25 in. diameter hose adapter



61HW22



783GA0/783GA1/783GA2

Crush-Resistant Vacuum Hose

- 1.88 in. diameter hose, plastic, black.

Item No.	Product Description
Crush-Resistant Vacuum Hose	
783GA0	12 ft. long hose
783GA1	18 ft. long hose
783GA2	25 ft. long hose

Crush-Resistant Vacuum Hose

783GA0	12 ft. long hose
783GA1	18 ft. long hose
783GA2	25 ft. long hose



61HW21/783GA3

Premium Crush-Resistant Vacuum Hose

- 1.88 in. diameter hose, plastic, black & red.

Item No.	Product Description
Premium Crush-Resistant Vacuum Hose	
61HW21	12 ft. long hose
783GA3	25 ft. long hose

Premium Crush-Resistant Vacuum Hose

61HW21	12 ft. long hose
783GA3	25 ft. long hose

Wet/Dry Vacuum Accessory Kits



783GA4

1.25 in. Diameter Clean Up Kit

Fits 1.25 in. diameter hose, kit contains (2) plastic extension wands, deluxe 12 in. floor nozzle with brush & squeegee inserts, utility nozzle, round brush and crevice nozzle.



783GA6

Vehicle Detailing/Cleaning Kit

Fits 1.88 in. diameter hose, kit contains 12 ft. x 1.88 in. diameter clip attached hose, claw nozzle, round brush and crevice nozzle.



783GA5

2.5 in. Diameter Clean Up Kit

Fits 2.5 in. diameter hose, kit contains 6 ft. x 2.5 in. diameter hose, (2) plastic extension wands, (2) hose end adapters, floor nozzle, car nozzle, round brush and crevice nozzle.



61HW24

Micro Cleaning Kit

Fits 1.25 in. diameter hose, 6-piece kit for cleaning keyboards, computers and small appliances.

All specifications contained within are subject to change.

All vacuums are ETL certified and conform to UL Standard 1017.

† "Peak Horsepower" (PHP) is a term used in the wet-dry vacuum industry for consumer comparison purposes. It does not denote the operational horsepower of a wet-dry vacuum, but rather the horsepower output of a motor, including the motor's inertial contribution, achieved in laboratory testing. In actual use, wet dry vacuum motors do not operate at the peak horsepower shown.

* Tank capacity refers to actual tank volume, and does not reflect capacity available during operation.

‡ Tested to ASTM standard with same hose length & diameter supplied with vacuum.

Call or visit your local branch or go to [grainger.com/dayton](https://www.grainger.com/dayton)
for complete product line information.

©2024 W.W. Grainger, Inc. W-BUPX115-01

