




## TEGERA® INFINITY 8815

Learn more

### THIN NITRILE DIPPED CUT F

Dexterous cut resistant glove with highest cut level F, suitable for precision work. Ultra light thanks to 18 gg knitted with CRF® Omni cut resistant technology. Palm dipped with super soft nitrile foam that provides excellent grip on dry surfaces. Reinforced thumb crotch for improved longevity. Breathable materials for all day comfort. Wide range of sizes means a perfectly fitting glove for everyone. Skin friendly with Derma-test and Oeko-Tex certificate.

#### CHARACTERISTICS

- Highest level of protection
- Good fingertip sensitivity
- Extra flexible
- Durable
- Good grip
- Extra comfortable

#### FUNCTIONS

- Withstands contact heat up to 100°C
- Approved for handling foodstuffs
- Reinforcement between index finger and thumb
- Ultra thin
- Super soft

CRF® omni

ORIGINAL EXCELLENT dermatest 2019 dermatest-guarantee.de

OEKO TEX® STANDARD 100 SE 14-214 RISE



*All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.*

## PREVENTS RISK OF

Cut injuries, Abrasion injuries, Blisters, Grazes, Scratches, lacerations, Contact with dirt

## PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Dry environments, Moist environments, Dirty environments

## PRIMARY AREAS OF USE

Assembly, Building and construction, Carpentry, Engineering, Fine assembly, Glass industry work, Machine driving, Machine operating, Metalwork, Paper industry work, Repair work, Sheet-metal work

## PRIMARY INDUSTRIES OF USE

Agriculture, forestry and fishing, Automotive manufacturing, Automotive repair and maintenance, Basic metals manufacturing, Building and construction, Electrical equipment manufacturing, Electricity and gas supply, Glass, ceramics and construction materials, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Mining and quarrying, Pulp and paper, Retail and wholesale, Rubber and plastics manufacturing, Transport equipment manufacturing, Transportation and logistics, Warehousing

## TYPE OF WORK

Medium weight

## SPECIFICATION

**TYPE** Cut resistant gloves, Heat protection gloves
**CATEGORY** Cat. II
**COLLECTION** Infinity
**KNITTING GAUGE (GG)** 18
**LINING MATERIAL** CRF® Omni Technology, HPPE, Nylon, Spandex, Tungsten fiber thread
**LENGTH** 220-270 mm
**DEXTERITY** 5
**GRIP DESIGN** Foam grip pattern
**COLOUR** Black
**PAIRS PER: BUNDLE/CARTON** 6/120
**DISPLAY TYPE** Bulk pack
**DIPPING** Palm-dipped
**DIPPING MATERIAL** Nitrile foam
**CUFF STYLE** Knitwrist cuff
**CUFF MATERIAL** Textile
**CUT RESISTANCE (EN ISO 13997)** Cut resistance level F
**CUT RESISTANCE (EN ISO 13997) TDM:** 31.2 N
**INNER MATERIAL SPECIFICATION** HPPE (High performance polyethylene), Nylon, Tungsten fibre thread , Elastane
**OUTER MATERIAL SPECIFICATION** Nitrile

## COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018 4X43F

EN 407:2020 (No flame protection) X1XXXX

ANSI A6 CUT

ANSI 4 ABR

Contact heat rating valid for palm area only

## FEATURES

Cut protection

| SIZE | | ARTICLE NUMBER | EAN |
|---|---|---|---|
| 6 | XS | 8815-6 | 7340118370965 |
| 7 | S | 8815-7 | 7340118371054 |
| 8 | M | 8815-8 | 7340118371146 |
| 9 | L | 8815-9 | 7340118371238 |
| 10 | XL | 8815-10 | 7340118371320 |
| 11 | XXL | 8815-11 | 7340118371412 |
| 12 | 3XL | 8815-12 | 7333506023871 |

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com



*All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.*