

Thermal Unit — Table 16			
Motor FLC (A)			Thermal Unit Number
1.T.U.	2 T.U.	3 T.U.	
18.9–20.5	17.4–19.5	16.5–18.5	CC24.6
20.6–22.2	19.6–20.7	18.6–19.6	CC26.3
22.3–23.7	20.8–22.3	19.7–21.1	CC28.8
23.8–25.4	22.4–24.0	21.2–22.7	CC31.0
25.5–27.3	24.1–25.7	22.8–24.4	CC33.3
27.4–29.3	25.8–27.5	24.5–26.1	CC36.4
29.4–31.5	27.6–29.6	26.2–28.1	CC39.6
31.6–33.9	29.7–31.7	28.2–30.0	CC42.7
34.0–36.2	31.8–33.9	30.1–32.1	CC46.6
36.3–39.3	34.0–36.6	32.2–34.7	CC50.1
39.4–42.3	36.7–39.3	34.8–37.3	CC54.5
42.4–45.3	39.4–42.3	37.4–40.1	CC59.4
45.4–48.3	42.4–44.9	40.2–42.6	CC64.3
48.4–52.0	45.0–48.3	42.7–45.8	CC68.5
52.1–54.9	48.4–50.9	45.9–48.3	CC74.6
55.0–59.7	51.0–55.5	48.4–52.6	CC81.5
59.8–65.4	55.6–59.9	52.7–56.8	CC87.7
65.5–69.6	60.0–64.2	56.9–60.9	CC94.0
69.7–74.8	64.3–68.7	61.0–65.1	CC103.0
74.9–79.7	68.8–71.4	65.2–67.7	CC112.0
79.8–83.1	71.5–74.8	67.8–70.9	CC121.0
83.2–86.0	74.9–78.0	71.0–73.9	CC132.0
—	78.1–80.7	74.0–76.5	CC143.0
—	80.8–86.0	76.6–80.2	CC156.0
—	—	80.3–83.1	CC167.0
—	—	83.2–86.0	CC180.0

Table 17

For additional information and instructions for thermal units, see the previous sections Introduction, page 46 through Mounting the Thermal Units , page 56 in this chapter.

Thermal Unit — Table 17			
Motor FLC (A)			Thermal Unit Number
1.T.U.	2 T.U.	3 T.U.	
0.42–0.46	0.39–0.43	0.38–0.40	A.49
0.47–0.50	0.44–0.47	0.41–0.44	A.54
0.51–0.55	0.48–0.52	0.45–0.49	A.59
0.56–0.62	0.53–0.58	0.50–0.55	A.65
0.63–0.67	0.59–0.64	0.56–0.60	A.71
0.68–0.73	0.65–0.68	0.61–0.65	A.78
0.74–0.81	0.69–0.77	0.66–0.72	A.86
0.82–0.89	0.78–0.84	0.73–0.79	A.95

Thermal Unit — Table 17			
Motor FLC (A)			Thermal Unit Number
1.T.U.	2 T.U.	3 T.U.	
0.90–0.98	0.85–0.93	0.80–0.88	A1.02
0.99–1.12	0.94–1.05	0.89–0.98	A1.16
1.13–1.20	1.06–1.13	0.99–1.07	A1.25
1.21–1.34	1.14–1.25	1.08–1.17	A1.39
1.35–1.41	1.26–1.33	1.18–1.25	A1.54
1.42–1.51	1.34–1.42	1.26–1.33	A1.63
1.52–1.62	1.43–1.52	1.34–1.44	A1.75
1.63–1.73	1.53–1.63	1.45–1.53	A1.86
1.74–1.86	1.64–1.75	1.54–1.65	A1.99
1.87–2.02	1.76–1.90	1.66–1.79	A2.15
2.03–2.25	1.91–2.13	1.80–1.99	A2.31
2.26–2.46	2.14–2.33	2.00–2.18	A2.57
2.47–2.77	2.34–2.73	2.19–2.45	A2.81
2.78–2.99	2.74–2.86	2.46–2.65	A3.61
3.00–3.26	2.87–3.14	2.66–2.90	A3.95
3.27–3.59	3.15–3.47	2.91–3.19	A4.32
3.60–3.99	3.48–3.83	3.20–3.56	A4.79
4.00–4.42	3.84–4.16	3.57–3.83	A5.30
4.43–4.61	4.17–4.43	3.84–4.08	A5.78
4.62–5.23	4.44–5.00	4.09–4.64	A6.20
5.24–5.39	5.01–5.16	4.65–5.00	A6.99
5.40–5.88	5.17–5.56	5.01–5.36	A7.65
5.89–6.56	5.57–6.22	5.37–5.87	A8.38
6.57–7.18	6.23–6.89	5.88–6.43	A9.25
7.19–7.80	6.90–7.00	6.44–6.79	A9.85
7.81–9.00	—	6.80–7.00	A11.0

Table 18

For additional information and instructions for thermal units, see the previous sections Introduction, page 46 through Mounting the Thermal Units , page 56 in this chapter.

Thermal Unit — Table 18			
Motor FLC (A)			Thermal Unit Number
1.T.U.	2 T.U.	3 T.U.	
15.5–16.4	14.4–15.3	13.6–14.5	CC20.9
16.5–17.6	15.4–16.4	14.6–15.5	CC22.8
17.7–19.1	16.5–18.4	15.6–17.4	CC24.6
19.2–20.4	18.5–19.6	17.5–18.5	CC26.3
20.5–22.1	19.7–21.0	18.6–19.9	CC28.8
22.2–23.4	21.1–22.7	20.0–21.5	CC31.0
23.5–25.6	22.8–24.2	21.6–22.9	CC33.3
25.7–27.3	24.3–25.9	23.0–24.5	CC36.4

Thermal Unit — Table 31	
Motor FLC (A)	Thermal Unit Number
1.98–2.14	B2.65
2.15–2.47	B3.00
2.48–2.91	B3.30
2.92–3.31	B3.70
3.32–3.75	B4.15
3.76–4.05	B4.85
4.06–4.94	B6.25
4.95–5.52	B6.90
5.53–6.11	B7.70
6.12–6.52	B8.20
6.53–7.31	B9.10
7.32–8.43	B10.2
8.44–9.83	B11.5
9.84–10.7	B12.8
10.8–11.6	B14.0
11.7–12.9	B15.5
13.0–14.3	B17.5
14.4–15.7	B19.5
15.8–17.8	B22.0
17.9–20.3	B25.0
20.4–23.3	B28.0
23.4–26.6	B32.0
26.7–30.3	B36.0
30.4–35.3	B40.0
35.4–41.5	B45.0
41.6–45	B50.0

Table 34

For additional information and instructions for thermal units, see the previous sections Introduction, page 46 through Mounting the Thermal Units , page 56 in this chapter.

Thermal Unit — Table 34	
Motor FLC (A)	Thermal Unit Number
15.1–16.2	CC20.9
16.3–17.5	CC22.8
17.6–19.1	CC24.6
19.2–20.7	CC26.3
20.8–22.2	CC28.8
22.3–24.0	CC31.0
24.1–25.7	CC33.3
25.8–27.8	CC36.4
27.9–30.1	CC39.6
30.2–32.5	CC42.7

Table 67

For additional information and instructions for thermal units, see the previous sections Introduction, page 46 through Mounting the Thermal Units , page 56 in this chapter.

Thermal Unit — Table 67	
Motor FLC (A)	Thermal Unit Number
3.79–4.14	B5.50
4.15–4.44	B6.25
4.45–5.22	B6.90
5.23–5.29	B7.70
5.30–5.99	B8.20
6.00–6.82	B9.10
6.83–7.68	B10.2
7.69–7.92	B11.5
7.93–8.47	B12.8
8.48–9.99	B14.0
10.0–10.8	B15.5
10.9–12.3	B17.5
12.4–12.9	B19.5
13.0–15.1	B22.0
15.2–16.7	B25.0
16.8–17.9	B28.0
18.0–20.1	B32.0
20.2–23.8	B36.0
23.9–25.8	B40.0
25.9–28.3	B45.0
28.4–29.6	B50.0
29.7–32.1	B56.0
32.2–34.4	B62.0
34.5–38.3	B70.0
38.4–39.9	B79.0
40.0–45.0	B88.0

Table 68

For additional information and instructions for thermal units, see the previous sections Introduction, page 46 through Mounting the Thermal Units , page 56 in this chapter.

Thermal Unit — Table 68	
Motor FLC (A)	Thermal Unit Number
14.9–16.1	CC20.9
16.2–17.3	CC22.8
17.4–19.5	CC24.6
19.6–20.7	CC26.3
20.8–22.4	CC28.8
22.5–23.9	CC31.0