

H-x156 - Pro-Pal Ball Drain Strainers

H-x156W Series

Pro-Pal Ball Drain Strainer

Full Port Forged DZR Brass Ball Valve
w/ Hi-Flow Multi-Function Hose Drain,
Integral Y-Strainer (20 Mesh),
1/2" Plugged NPT Port
& Adjustable Packing Glands



Certifications

Certified to NSF/ANSI/CAN 61 & 372





Size (in)	Item#	Weight (lbs)	CTN Qty	Case Qty	A	B	C		
FIP								250 PSI CWP Max	200°F Max
1/2"	H-41562W	1.06	4	32	3.58	3.00	3.25		
3/4"	H-41563W	1.64	2	24	4.30	3.00	3.75		
1"	H-41564W	2.14	2	20	4.72	3.00	4.00		
1 1/4"	H-41565W	3.44	2	12	5.75	3.50	4.50		
Press								250 PSI CWP Max	200°F Max
1/2"	H-81562W	1.16	2	24	5.09	3.00	3.25		
3/4"	H-81563W	1.75	2	20	6.18	3.00	3.75		
1"	H-81564W	2.29	2	12	6.46	3.00	4.00		
1 1/4"	H-81565W	3.63	2	8	7.78	3.50	4.50		





NO.	DESCRIPTION	MATERIAL
1	Cap	Brass
2	Gasket	EPDM
3	Screw	Stainless Steel
4	Handle	Aluminum
5	Stem	Brass
6	Strap	PVC
7	Cap	Brass
8	Ball	Brass HCP
9	Seat	PTFE
10	Seat	PTFE
11	Packing	PTFE
12	Packing Gland	Brass
13	Body	Lead-Free DZR Brass
14	Stem	Brass
15	Ball	Brass HCP
16	Handle Nut	Stainless Steel
17	Cap	Lead-Free DZR Brass
18	Handle	Steel CP
19	O Ring	EPDM
20	strainer	Stainless Steel
21	1/2"NPT Plug	Lead-Free DZR Brass
22	Cap	Lead-Free DZR Brass
23	O Ring	EPDM
24	O Ring	EPDM
25	Packing	PTFE
26	Packing Gland	Brass



Specifications: Threaded (NPT) ends comply with ANSI B1.20.1. Solder joint temperature ratings are per ASME B16.18 Annex A for 95-5 solder. Do not silver braze or overheat valves when soldering. EPDM o-rings for press ends.

REV:9/24/2024

LEAD-FREE: Weighted
average lead content ≤ 0.25%

WWW.WEBSTONEVALVES.COM



WARNING: Cancer and Reproductive
Harm - www.P65Warnings.ca.gov