

ART VERSION #: 4

ART REVISION DATE: 10/06/2016

FINAL ART DATE: 10/XX/2016

US SPEC #: A01-1116-1532 C

DIE LINE #: 3241 642 95961

US/CH PART #: 3235 826798 03

PHILIPS LIGHTING USA			
Brand	PHILIPS		
Product Family	LED 3-Way Bulb		
Shape	A21		
Wattage	5/8/18w		
Master Brand Template Ref.	3235 829480 02		
SGS number	4433610		
6NC #	459164		
PKG PART #	3235 826798 03		
DIE #	3241 642 95961		
CRC #	CRC_014US		
Barcode No.	0 46677 45916 1		
Operator(s)	Jannett.Corraea-Lynch@sgsco.com		
VERSION No.	v4		
Date	OCTOBER 06, 2016		
Cyan	Magenta	Yellow	Black
<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
Die			
<b>Date Check</b>			
<input type="checkbox"/> Check briefing Traffic			
<b>Artwork document</b>			
<input type="checkbox"/> Legend	<input type="checkbox"/> Number of colors		
<input type="checkbox"/> 12NC	<input type="checkbox"/> Trapping/Bleed		
<input type="checkbox"/> Barcode	<input type="checkbox"/> Images hires		
<input type="checkbox"/> Diecut	<input type="checkbox"/> Jobsizes		
<b>Approval</b>			
<input type="checkbox"/> QC Lithographer			
<input type="checkbox"/> Product Manager			
<input type="checkbox"/> Traffic Manager			

299.5

13

13

R13

289

**LASTS 22+ YEARS\*\***

**SAVES \$225 IN ENERGY COST\***

**3-WAY**   **INSTANT-ON**   **E26d Standard**   **MEDIUM BASE**

**Lighting Facts** Per Bulb

**Brightness** 450/800/1600 lumens

**Estimated Yearly Energy Cost** \$0.60/\$0.96/\$2.17

Based on 3 hrs/day, 11¢/kWh

Cost depends on rates and use

**Life** Based on 3 hrs/day **22.8 years**

**Light Appearance** Warm ————— Cool

2700 K

**Energy Used** 5/8/18 watts

**LIMITED WARRANTY for Consumers:** Philips warrants that this bulb will be free from defects in material and workmanship and will operate for 5 years based on up to 3 hours average usage per day/7 days per week, when used as directed. If this bulb does not conform to the warranty, Philips will send you, at its election, a replacement bulb or refund your original purchase price upon receipt of the returned bulb, register receipt and proof of purchase. Please call our toll-free number, write to Philips or send an email at the website below to find out how to return the bulb. This limited warranty does not cover bulbs subject to accident, neglect, abuse, misuse or acts of God. REPLACEMENT OR REFUND IS YOUR SOLE REMEDY. EXCEPT TO THE EXTENT PROHIBITED BY APPLICABLE LAW, ANY IMPLIED WARRANTIES ARE LIMITED IN DURATION TO THE DURATION OF THIS WARRANTY. LIABILITY FOR INCIDENTAL OR CONSEQUENTIAL DAMAGES IS HEREBY EXPRESSLY EXCLUDED. Some states do not allow exclusion of incidental or consequential damages, so the above limitation or exclusion may not apply to you. This warranty gives you specific legal rights, and you may also have other rights which vary from state to state.

**LIMITED WARRANTY for Professional, Industrial/Commercial Customers and applications:** Philips warrants that this bulb will be free from defects in material and workmanship and will operate for 3 years based on lamp operation of 12 hours average usage per day/7 days per week, when used as directed. Visit [http://www.usa.lighting.philips.com/connect/tools\\_literature/warranties.wpd](http://www.usa.lighting.philips.com/connect/tools_literature/warranties.wpd) for full details and restrictions.

**NOTES:** This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) This device must accept any interference received, including interference that may cause undesired operation.

Any changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

This Class B complies with Canadian ICES-005.

\*At \$0.11 per kWh, this 18 watt, 1600 lumen A21 LED uses \$49.50 of electricity over its 25,000 hour life. This is a \$225.50 savings when compared to the \$275.00 required to run a 100 watt, 1840 lumen, A21 incandescent over the same period. Actual savings will vary depending on cost per kWh.

\*\*LED lifetime means the length of time (in years) until half of the LED light sources maintain at least 70% of their initial lumen output (B50L70), where the lamp is used on average 3 hours/day.

3235 826798 03  
Model: 9290011742  
Ordering Code: 18A21/LED/827 3WAY ND 120V  
Assembled in one or more of the following countries: China, Mexico  
Philips Lighting North America Corporation  
200 Franklin Square Drive, Somerset, NJ 08873, USA  
Questions or Comments:  
1-800-555-0050 or [www.philips.com](http://www.philips.com)

**PHILIPS**

40w  
60w  
100w  
replacement\*  
reemplazo

5/8 /18w LED

Soft white light  
luz blanca suave

3-Way

**PHILIPS**

40w  
60w  
100w  
replacement\*  
reemplazo

5/8 /18w LED

Soft white light  
luz blanca suave

Lasts 22+ Years\*  
Más de 22 años de vida útil

Brightness/ Brillo	Estimated Energy Cost/ Estimado de Energía Costo
450/ 800/ 1600 lumens/lúmenes	\$0.60/ \$0.96/ \$2.17 per year/por año

ENERGY STAR

**WARNINGS AND CAUTIONS:** Not suitable for use with dimmers. This device is not intended for use with emergency exit fixtures or emergency lights. Not for use in totally enclosed or recessed luminaires (fixtures). Risk of electric shock – Do not use where directly exposed to water. Before replacing, turn off power and let lamp cool to avoid electrical shock or burn. Only install in operating environments between -4°F and +113°F (-20°C and +45°C).

**PRECAUCIONES Y CUIDADOS:** No atenuable/dimmable. Este dispositivo no está diseñado para usar como iluminación de emergencia o dentro de luminarias de señalización en salida de emergencia. No debe utilizarse en luminarias empotradas o totalmente cerradas (accesorios). Riesgo de choque eléctrico – No utilizar donde haya contacto directo con agua. Antes de reemplazar, apague la corriente eléctrica y enfríe la lámpara para evitar un choque eléctrico o incendio. Solo instalar en ambientes entre -4 grados F y + 113 grados F (-20 grados Centígrados y 45 grados C.)

**Información sólo para el mercado Mexicano-**  
Lámpara LED Omnidireccional A21/5/8/18W  
Tensión Eléctrica 120V~  
Frecuencia 60Hz  
Corriente Eléctrica 60/86/170mA  
Vida Nominal : 25,000 h

Ensamblado en alguno de los siguientes países:  
México y/o China

Contenido 1 pieza

**Importado y/o Distribuido por:**  
PHILIPS MEXICANA S.A DE C.V.  
Av. La Palma No. 6  
Col. San Fernando La Herradura  
Huixquilucan Estado de México CP. 52784  
R.F.C. PME-620620-EB4

**Línea de Atención al Cliente**  
01800 508 9000 (55) 5269 9139  
[smartlight.mexico@philips.com](mailto:smartlight.mexico@philips.com)  
Garantía 5 años, para términos y condiciones consultar el siguiente link:  
<http://www.lighting.philips.com.mx/connect/garantias.wpd>

PROOF OF PURCHASE  
18A21/LED/827 3WAY ND 120V

0 46677 45916 1

**UL** US  
LISTED  
LED Lamp  
3PM5  
80CRI 2700K

UPC-A code generated in US. To be confirmed by China prior to printing.