

381

ART REVISION #: 2

ART REVISION DATE: 03/05/2015

FINAL ART DATE: 03/05/2015

MX PART #: 4435 285 04121

PRODUCTION NOTES:	ARTWORK SPECIFICATIONS:
<ul style="list-style-type: none"> This proof indicates approximate color only! All colors print 100% unless otherwise indicated. All structure and holding lines do not print unless otherwise indicated. This is prepared as a color digital mechanical, no traps have been made. All trapping is the responsibility of the engraver and/or separator and/or printer. 	<p>Date: 03/05/2015 Project Name: Gen5 Prof/Cors Base Shared BR30 Package Product Name/Description: 9W BR30 Warm Glow DIM 120V File Name: 457044_9BR30_LED_827-22_DIM_120V_4435 285 04121.ai</p> <p>Component Type: Folding Box Die Line No.: 443528504120 / 077-078-04-01 Product Number: 457044 Artwork Program: AI CS6 Manufacturing Site: Mexico</p> <p>Version No.: 2 Print Method: Number of colors: 4 color process Barcode No.: 0 46677 45704 4 Language(s): English</p> <p>COLORS: Note: All colors for reference only, printer to use pre-approved color drawdowns when printing.</p> <p>MATERIALS & COATINGS: CHIPBOARD & WATER BASED Note: Refer to applicable Component (PC) Specification for exact details/requirements on substrates and coatings/varnishes</p> <p>Account Rep: Production Artist: ES Packaging Engineer: MBF Agency:</p>
<p>PRINT SPECIFICATIONS:</p> <p>Varnishes/Special Coatings: Graphic Specialist: ES Packaging Engineer: MBF Agency:</p> <p>COLORS: Cyan Magenta Yellow Black</p> <p>TARGETED COLORS: PMS 300 CMYK</p> <p>FONTS: Gill Sans Art One WGL Regular Gill Sans Art One WGL Bold Gill Sans Art One WGL Light Helvetica Regular Helvetica Medium Condensed</p> <p>OCRB Medium Anal Bold Anal Regular</p>	<p>PHILIPS</p>

301.6



5 YEARS LIMITED WARRANTY	22+ LASTS YEARS**	SAVES \$154 IN ENERGY COST*
2200K - 2700K DIMMABLE	ON OFF INSTANT-ON	E26 Standard MEDIUM BASE

Lighting Facts Per Bulb, Brightness 650 lumens, Estimated Yearly Energy Cost \$1.08 (Based on 3 hrs/day, 11¢/kWh. Cost depends on rates and use), Life 22.8 years (Based on 3 hrs/day), Color Temperature 2700 K, Energy Used 9 watts

PROOF OF PURCHASE
9BR30/LED/827-22 DIM 120V

0 46677 45704 4

UL LISTED LED Lamp 3PMS B0CR1 2700K

SEE THE LIGHT lighting facts

LIMITED WARRANTY: Philips warrants that this bulb will be free from defects in material and workmanship and will operate for 5 years based on up to 3 hours average usage per day/7 days per week, when used as directed. If this bulb does not conform to the warranty, Philips will send you, at its election, a replacement bulb or refund your original purchase price upon receipt of the returned bulb. Please call our toll-free number, write to Philips or send an email at the website on this package to find out how to return the bulb. This limited warranty does not cover bulbs subject to accident, neglect, abuse, misuse or acts of God. REPLACEMENT OR REFUND IS YOUR SOLE REMEDY. EXCEPT TO THE EXTENT PROHIBITED BY APPLICABLE LAW, ANY IMPLIED WARRANTIES ARE LIMITED IN DURATION TO THE DURATION OF THIS WARRANTY. LIABILITY FOR INCIDENTAL OR CONSEQUENTIAL DAMAGES IS HEREBY EXPRESSLY EXCLUDED. Some states do not allow exclusion of incidental or consequential damages, so the above limitation or exclusion may not apply to you. This warranty gives you specific legal rights, and you may also have other rights which vary from state to state.

*For Professional, Industrial/Commercial Customers and applications, the warranty period is based on lamp operation of 12 hours a day/7 days a week. See insert for full details and restrictions.

NOTES: This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. This Class B digital apparatus complies with Canadian ICES-003.

*At \$0.11 per kWh, this 9 watt, 650 lumen BR30 LED uses \$24.75 of electricity over its 25,000 hour life. This is a \$154.00 savings when compared to the \$178.75 required to run a 65 watt, 650 lumen, BR30 incandescent over the same period. Actual savings will vary depending on cost per kWh.

**22.8 years means rated average life based on engineering testing and probability analysis where the lamp is used on average 3 hours/day, 7 days a week.

4435 285 04121
Model: 9290011555
Ordering Code: 9BR30/LED/827-22 DIM 120V
Assembled in one or more of the following countries:
China, Mexico

Philips Lighting North America Corporation
200 Franklin Square Drive
Somerset, NJ 08873
Questions or Comments:
1-800-555-0050

PHILIPS

65w replacement
9w LED
Soft white light
luz blanca suave

Warm Glow
Dimmable Light
The more you dim the warmer the light.

Brightness/Brillo
650
lumens/lúmenes

Estimated Energy Cost/Costo Estimado de Energía
\$1.08
per year/por año

PHILIPS

WARNINGS AND CAUTIONS: This device is not intended for use with emergency exit fixtures or emergency lights. Suitable for use with dimmers. Visit www.philips.com/dimmercompatibility to find up-to-date dimmer and lighting control compatibility information. Risk of electric shock - Do not use where directly exposed to water. Before replacing, turn off power and let lamp cool to avoid electrical shock or burn. Only install in operating environments between -4°F and +113°F (-20°C and +45°C).

PRECAUCIONES Y CUIDADOS: Este dispositivo no está diseñado para usarse como iluminación de emergencia o dentro de luminarios de señalización de salida de emergencia. Se pueden usar con atenuadores de luz. Visita www.philips.com/dimmercompatibility para encontrar la compatibilidad con atenuadores y controles de luz. Riesgo de choque eléctrico - No utilizar con agua. Antes de reemplazar, apague la corriente eléctrica y enfríe la lámpara para evitar un choque eléctrico o incendio. Solo instalar en ambientes entre -4 grados F y +113 grados F (-20 grados Centígrados y 45 grados C.)

Información sólo para el mercado mexicano
Lámpara LED bulbo BR30 9W
Tensión Eléctrica 120V~
Frecuencia 60Hz
Corriente Eléctrica 92mA

Ensamblado en alguno de los siguientes países:
México y/o China

Distribuido por:
PHILIPS MEXICANA SA DE CV.
Av. La Palma No. 6
Col. San Fernando La Herradura
Hauquehulcan Estado de México CP 52784
R.F.C. PME-620620-E84

Línea de Atención al Cliente
01800 508 9000 (55) 5269 9139
smartlight.mexico@philips.com
Garantía 3 años, para términos y condiciones consultar el siguiente link:
<http://www.lighting.philips.com.mx/connect/garantias.wpd>

43.5

131

45.5

18

91

91

91

90