marathon®

General Purpose Motors

Model No: 404TSTDCD6001
Catalog No: GT0048A

General Purpose Motor, 125 & 100 HP, 3 Ph, 60 & 50 Hz, 460 & 380 V, 3600 RPM, 404TS Frame, DP

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: 404TSTDCD6001, Catalog No: GT0048A General Purpose Motor, 125 & 100 HP, 3 Ph, 60 & 50 Hz, 460 & 380 V, 3600 RPM, 404TS Frame, DP

Nameplate Specifications

Phase	**3**	Output HP	**125 & 100 Hp**
Output KW	**93.0 & 75.0 kW**	Voltage	**460 & 380 V**
Speed	**3575 & 2975 r/min**	Synchronous RPM	**3600 & 3000 r/min**
Service Factor	**1.15 & 1.15**	Frame	**404TS**
Enclosure	**Drip Proof**	Thermal Protection	**No Protection**
Efficiency	**95 & 94.5 %**	Ambient Temperature	**40 °C**
Frequency	**60 & 50 Hz**	Current	**139 & 136 A**
Power Factor	**89**	Duty	**Continuous**
Insulation Class	**F**	Design Code	**B**
KVA Code	**G**	Drive End Bearing Size	**6313**
Opp Drive End Bearing Size	**6313**	UL	**Recognized**
CSA	**Y**	CE	**Y**
IP Code	**22**	Number of Speeds	**1**

Technical Specifications


Electrical Type	**Squirrel Cage Inverter Rated**	Starting Method	**Wye Start Delta Run Or Inverter**
Poles	**2**	Rotation	**Reversible**
Resistance Main	**.053 O**	Mounting	**Rigid Base**
Motor Orientation	**Horizontal**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Cast Iron**
Shaft Type	**TS**	Overall Length	**33.86 in**
Shaft Diameter	**2 1/8 in**	Shaft Extension	**4.25 in**
Assembly/Box Mounting	**F1/F2 Capable**	Inverter Load	**Variable 10:1**


Drawings


Connection Drawing	**EE7340**	Outline Drawing	**SS620752-100**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 16/10/2026

DASH NO.	B	C	D	E	2E	2F	2FF	BA	BS	MOUNTING	FRAME
100	19.29	33.70	10.00	8.00	16.00	---	12.25	6.62	8.54	F1 OR F2	404TS
200	20.87	35.27				12.25	13.75		9.32		404/405TS







DRAWING REVISION	REVISION BY	REV DATE/© DATE
D	SB	10/16/2025
REQUEST NUMBER	APPROVED BY	DATE
CR-0024344	SBD	10/16/2025

REQUEST NUMBER DESCRIPTION
DRAWING TITLE BLOCK UPDATED


COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC, ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

PRIMARY DIMENSIONS ARE INCH
mm DIMENSIONS IN [BRACKETS]
ARE FOR REFERENCE ONLY

DRAWN BY	DESCRIPTION	
WY	OUTLINE	
DATE	404/405TS FR NEMA ODP CAST IRON	
21/07/2016		
APPROVED BY		
DATE		
REFERENCE	MATERIAL	PROCESS/FINISH
THIRD ANGLE PROJECTION	SIZE B / DRAWING NUMBER SS620752	SHEET 1 OF 1

marathon™

THREE PHASE
WYE START DELTA RUN



DRAWING REVISION: G	REVISION BY: SB	REV DATE/© DATE: 08/04/2025	PRIMARY DIMENSIONS ARE INCH mm DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY	DRAWN BY: LZ	marathon™
REQUEST NUMBER: CR-0023654	APPROVED BY: SBD	DATE: 08/04/2025		DATE: 01-06-1994	
REQUEST NUMBER DESCRIPTION: DRAWING TITLE BLOCK UPDATED				APPROVED BY: GK	DESCRIPTION: CONNECTION DIAGRAM 3∅ - WYE START DELTA RUN
				DATE: 01-18-1994	
				REFERENCE	MATERIAL / PROCESS/FINISH
				THIRD ANGLE PROJECTION	SIZE: A / DRAWING NUMBER: EE7340 / SHEET: 1 OF 1

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

Data Sheet

Date: 12/1/2021
Customer:
Attention:
Submitted by:

marathon® Motors

404TSTDCD6001

Submittal


Data @ 460 V

Motor Load Data

Load	0%	25%	50%	75%	100%	115%	125%	LR	
Current (Amps)	40.5	52.5	77.0	107	139	159	173	900	
Torque (ft-lb)	0.00	46.0	92.0	138	184	212	230	340	
RPM	3600	3592	3588	3580	3575	3,565	3560	0	
Efficiency (%)		91.7	93.6	94.1	94.1	94.1	93.6		
P.F. (%)	7.5	61.5	81.0	87.5	89.5	90.0	90.0	31.0	

Motor Speed Data

	LR	Pull-Up	BD	Rated	Idle
Speed (RPM)	0	1800	3460	3575	3600
Current (Amps)	900	720	513	139	40.5
Torque (ft-lb)	340	285	478	184	0.00



Information Block

HP	125.0	
Sync. RPM	3600	
Frame	404	
Enclosure	DP	
Construction	TDC	
Voltage	460#380	V
Frequency	60	Hz
Design	B	
LR Code letter	G	
Service Factor	1.15	
Temp Rise @ FL	35	° C
Duty	CONT	
Ambient	40	° C
Elevation	3,300	feet
Rotor/Shaft wk²	15.0	Lb-Ft²
Ref Wdg	HA32502010 NONE	
Sound Pressure @ 1M	80	dBA
VFD Rating	VARIABLE 20:1	
Outline Dwg	SS620752-100	
Conn. Diag	EE7341C	

Additional Specifications:


0

0

EQUIV CKT (OHMS / PHASE)

R1	R2	X1	X2	Xm
0.0300	0.0130	0.1840	0.1910	6.5830

Speed -Torque Curve



Uncontrolled Copy

CERTIFICATION DATA SHEET

Model#:	404TSTDCD6001 AA	**WINDING#:**	HE32502010 NONE 1
CONN. DIAGRAM:	EE7341C	**ASSEMBLY:**	F1/F2 CAPABLE
OUTLINE:	SS620752		

TYPICAL MOTOR PERFORMANCE DATA

HP	KW	SYNC. RPM	F.L. RPM	FRAME	ENCLOSURE	KVA CODE	DESIGN
125&100	93&75	3600	3575&2975	404TS	DP	G	B

PH	Hz	VOLTS	FL AMPS	START TYPE	DUTY	INSL	S.F	AMB°C	ELEVATION
3	60/50	460#380	139&135	PWS OR INVERTER	CONTINUOUS	F7	1.15/1.15	40	3300

FULL LOAD EFF: 94.1&94.1	3/4 LOAD EFF: 94.1	1/2 LOAD EFF: 93.6	GTD. EFF	ELEC. TYPE	NO LOAD AMPS
FULL LOAD PF: 89.5&89.5	3/4 LOAD PF: 87.5	1/2 LOAD PF: 81	93.6	SQ CAGE INV RATED	40.5

F.L. TORQUE	LOCKED ROTOR AMPS	L.R. TORQUE	B.D. TORQUE	F.L. RISE°C
184 LB-FT	900	340 LB-FT 185	478 LB-FT 260	35

SOUND PRESSURE @ 3 FT.	SOUND POWER	ROTOR WK^2	MAX. WK^2	SAFE STALL TIME	STARTS /HOUR	APPROX. MOTOR WGT
80 dBA	90 dBA	15 LB-FT^2	- LB-FT^2	10 SEC.	2	1000 LBS.

*** SUPPLEMENTAL INFORMATION ***

DE BRACKET TYPE	ODE BRACKET TYPE	MOUNT TYPE	ORIENTATION	SEVERE DUTY	HAZARDOUS LOCATION	DRIP COVER	SCREENS	PAINT
STANDARD	STANDARD	RIGID	HORIZONTAL	FALSE	NONE	FALSE	NONE	BLUE (ENAMEL)

BEARINGS		GREASE	SHAFT TYPE	SPECIAL DE	SPECIAL ODE	SHAFT MATERIAL	FRAME MATERIAL
DE	OPE						
BALL 6313	BALL 6313	POLYREX EM	TS	NONE	NONE	1045 HOT ROLLED (C-204)	CAST IRON

THERMO-PROTECTORS				THERMISTORS	CONTROL	SPACE /n HEATERS
THERMOSTATS	PROTECTORS	WDG RTDs	BRG RTDs			
NONE	NOT	NONE	NONE	NONE	FALSE	NONE VOLTS

If Inverter equals NONE, contact factory for further information

INVERTER TORQUE: VARIABLE 10:1
INV. HP SPEED RANGE: NONE

ENCODER: NONE
NONE NONE
NONE NONE PPR

BRAKE: NONE NONE
NONE P/N NONE
NONE NONE
NONE FT-LB NONE V NONE Hz

*
NOTES
*

DATE: 07/03/2017 04:09:04 AM
FORM 3531 REV.3 02/07/99
** Subject to change without notice.