

ART VERSION #: I

ART REVISION DATE: 05/31/2017

FINAL ART DATE: 05/00/2017

SPEC #: A01-I1116-1742 B

DIE LINE #: 3241 642 95961

PART #: 3235 829663 02

PHILIPS LIGHTING USA			
Brand	PHILIPS		
Product Family	LED bulb - Warm Glow		
Shape	A21		
Wattage	16w		
Master Brand Template Ref.	3235 829663 01		
SGS number			
6NC #	472514		
PKG PART #	3235 829663 02		
DIE #	3241 642 95961		
CRC #	CRC_129US		
Barcode No.	0 46677 47251 1		
Operator(s)	donna.raia@philips.com		
VERSION No.	v1		
Date	MAY 31, 2017		
Cyan	Magenta	Yellow	Black
			Die
Date Check			
<input type="checkbox"/> Check briefing Traffic			
Artwork document			
<input type="checkbox"/> Legend	<input type="checkbox"/> Number of colors		
<input type="checkbox"/> 12NC	<input type="checkbox"/> Trapping/Bleed		
<input type="checkbox"/> Barcode	<input type="checkbox"/> Images hires		
<input type="checkbox"/> Diecut	<input type="checkbox"/> Jobsizes		
Approval			
<input type="checkbox"/> QC Lithographer			
<input type="checkbox"/> Product Manager			
<input type="checkbox"/> Traffic Manager			

PHILIPS LIGHTING USA

Brand: PHILIPS

Product Family: LED bulb - Warm Glow

Shape: A21

Wattage: 16w

Master Brand Template Ref.: 3235 829663 01

SGS number:

6NC #: 472514

PKG PART #: 3235 829663 02

DIE #: 3241 642 95961

CRC #: CRC_129US

Barcode No.: 0 46677 47251 1

Operator(s): donna.raia@philips.com

VERSION No.: v1

Date: MAY 31, 2017

Cyan Magenta Yellow Black

Die

Date Check

Check briefing Traffic

Artwork document

Legend Number of colors

12NC Trapping/Bleed

Barcode Images hires

Diecut Jobsizes

Approval

QC Lithographer

Product Manager

Traffic Manager

Lighting Facts Per Bulb

Brightness 1600 lumens

Estimated Yearly Energy Cost \$1.93
Based on 3 hrs/day, 11¢/kWh
Cost depends on rates and use

Life
Based on 3 hrs/day **22.8 years**

Light Appearance
Warm ————— Cool
2700 K

Energy Used 16 watts

LIMITED WARRANTY for Consumers: Philips warrants that this bulb will be free from defects in material and workmanship and will operate for 5 years based on up to 3 hours average usage per day/7 days per week, when used as directed. If this bulb does not conform to the warranty, Philips will send you, at its election, a replacement bulb or refund your original purchase price upon receipt of the returned bulb, register receipt and proof of purchase. Please call our toll-free number, write to Philips or send an email at the website below to find out how to return the bulb. This limited warranty does not cover bulbs subject to accident, neglect, abuse, misuse or acts of God. REPLACEMENT OR REFUND IS YOUR SOLE REMEDY, EXCEPT TO THE EXTENT PROHIBITED BY APPLICABLE LAW. ANY IMPLIED WARRANTIES ARE LIMITED IN DURATION TO THE DURATION OF THIS WARRANTY. LIABILITY FOR INCIDENTAL OR CONSEQUENTIAL DAMAGES IS HEREBY EXPRESSLY EXCLUDED. Some states do not allow exclusion of incidental or consequential damages, so the above limitation or exclusion may not apply to you. This warranty gives you specific legal rights, and you may also have other rights which vary from state to state.

LIMITED WARRANTY for Professional, Industrial/Commercial Customers and applications, Philips warrants that this bulb will be free from defects in material and workmanship and will operate for 3 years based on lamp operation of 12 hours average usage per day/7 days per week, when used as directed. Visit http://www.usa.lighting.philips.com/connect/tools_literature/warranties.wpd for full details and restrictions.

NOTES: This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) This device must accept any interference received, including interference that may cause undesired operation.

Any changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

This Class B complies with Canadian ICES-005.

*At \$0.11 per kWh, this 16 watt, 1600 lumen A21 LED uses \$44.00 of electricity over its 25,000 hour life. This is a \$231.00 savings when compared to the \$275.00 required to run a 100 watt, 1600 lumen, A21 incandescent over the same period. Actual savings will vary depending on cost per kWh.

**LED lifetime means the length of time (in years) until half of the LED light sources maintain at least 70% of their initial lumen output (B50L70), where the lamp is used on average 3 hours/day.

3235 829663 02
Model: 9290012605
Ordering Code: 16A21/LED/822-27/E26/Dim 120V
Assembled in one or more of the following countries: China, Mexico
Philips Lighting North America Corporation
200 Franklin Square Drive, Somerset, NJ 08873, USA
Questions or Comments:
1-800-555-0050
www.philips.com

WARNINGS AND CAUTIONS: Not for use in totally enclosed or recessed luminaires (fixtures). This device is not intended for use with emergency exit fixtures or emergency lights. Suitable for use with dimmers. Visit www.philips.com/dimmercompatibility to find up-to-date dimmer and lighting control compatibility information. This lamp is not suitable for totally enclosed luminaires (fixtures). Risk of electric shock – Do not use where directly exposed to water. Before replacing, turn off power and let lamp cool to avoid electrical shock or burn. Only install in operating environments between -4°F and +113°F (-20°C and +45°C).

PRECAUCIONES Y CUIDADOS: No debe utilizarse en luminarias empotradas o totalmente cerradas (accesorios). Este dispositivo no está diseñado para usar como iluminación de emergencia o dentro de luminarias de señalización en salida de emergencia. Se pueden usar con atenuadores de luz. Visita www.philips.com/dimmercompatibility para encontrar la compatibilidad con atenuadores y controles de luz. Esta lámpara no debe usarse en luminarias cerradas o con poca ventilación. Riesgo de choque eléctrico – No utilizar donde haya contacto directo con agua. Antes de reemplazar, apague la corriente eléctrica y enfríe la lámpara para evitar un choque eléctrico o incendio. Solo instalar en ambientes entre -4 grados F y +113 grados F (-20 grados Centígrados y 45 grados C.)

Información sólo para el mercado Mexicano
Lámpara LED Omnidireccional A21/16W
Tensión Eléctrica 120V~
Frecuencia 60Hz
Corriente Eléctrica 180mA
Vida Nominal 25,000 h

Ensamblado en alguno de los siguientes países:
México y/o China

Contenido 1 pieza

Importado y/o Distribuido por:
PHILIPS MEXICANA S.A DE C.V.
Av. La Palma No. 6
Col. San Fernando La Herradura
Huilquillan Estado de México CP. 52784
R.F.C. PME-620620-E84

Línea de Atención al Cliente
01800 508 9000 (55) 5269 9139
smartlight.mexico@philips.com
Garantía 5 años, para términos y condiciones consultar el siguiente link:
<http://www.lighting.philips.com.mx/connect/garantias.wpd>

13

13

R13

289

PROOF OF PURCHASE
16A21/LED/822-27/E26/Dim 120V



0 46677 47251 1

UL LISTED
LED Lamp
3PM5
80CRI 2700K

UPC-A code generated in US. To be confirmed by China prior to printing.

PHILIPS

100w replacement
reemplazo

16w LED

Soft white light
luz blanca suave

*See side panel for details

Warm Glow
Dimmable Light
The more you dim the warmer the light

PHILIPS

100w replacement
reemplazo

16w LED

Soft white light
luz blanca suave

Lasts 22+ Years*
Más de 22 años de vida útil

*See side panel for details

Warm Glow
Dimmable Light
The more you dim the warmer the light

ENERGY STAR

Brightness/Brillo	Estimated Energy Cost/ Costo Estimado de Energía
1600 lumens/lúmenes	\$1.93 per year/por año

13