

Safety Data Sheet



www.rustoleum.com

1. Identification

Name on Label:	Moisture Grabbers Moisture Absorber		
Product Name:	CC 1CT 6PK MOISTURE GRBR SM BUCKET 1 TAB	Revision Date:	1/8/2026
Product Identifier:	378490	Supersedes Date:	6/9/2025
Recommended Use:	Desiccant		
Supplier:	Rust-Oleum Corporation 11 Hawthorn Parkway Vernon Hills, IL 60061 USA	Manufacturer:	Rust-Oleum Corporation 11 Hawthorn Parkway Vernon Hills, IL 60061 USA
	Siamons International, Inc. 48 Galaxy Blvd., Unit 413 Toronto, ON M9W 6C8 Canada Phone: 001-416-213-0219 Toll Free: 1-866-811-4148		Siamons International, Inc. 48 Galaxy Blvd., Unit 413 Toronto, ON M9W 6C8 Canada Phone: 001-416-213-0219 Toll Free: 1-866-811-4148
Preparer:	Regulatory Department		
Emergency Telephone:	24 Hour Hotline: 847-367-7700		

2. Hazard Identification

Classification

Symbol(s) of Product



Signal Word

Warning

GHS Hazard Statements

Acute Toxicity, Oral, category 4

H302

Harmful if swallowed.

Eye Irritation, category 2A

H319

Causes serious eye irritation.

GHS Label Precautionary Statements

P264

Wash thoroughly after handling.

P280

Wear protective gloves, protective clothing, eye protection, and face protection.

P305+P351+P338

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P312

Call a POISON CENTER or physician if you feel unwell.

P330

Rinse mouth.

P337+P317

If eye irritation persists: Get medical help.

Moisture Grabbers Moisture Absorber, 1ct, 6pk

P501 Dispose of contents and container in accordance with local, regional and national regulations.

GHS SDS Precautionary Statements
P270

Do not eat, drink or smoke when using this product.

3. Composition / Information on Ingredients

HAZARDOUS SUBSTANCES

<u>Chemical Name</u>	<u>CAS-No.</u>	<u>Wt. % Range</u>	<u>GHS Symbols</u>	<u>GHS Statements</u>
Calcium Chloride	10043-52-4	60-80	GHS07	H302-319
Magnesium stearate	557-04-0	0.1-1.0	Not Available	Not Available

Actual concentrations of ingredients are withheld as trade secret.

4. First Aid Measures

First Aid - Eye Contact: Immediately flush eyes with plenty of water for at least 15 minutes holding eyelids open. Get medical attention. Do NOT allow rubbing of eyes or keeping eyes closed. Remove contact lenses, if present and easy to do. Continue rinsing.

First Aid - Skin Contact: Wash skin with soap and water. Remove contaminated clothing. Get medical attention if irritation develops or persists.

First Aid - Inhalation: Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get immediate medical attention. Do NOT use mouth-to-mouth resuscitation. If you experience difficulty in breathing, leave the area to obtain fresh air. If continued difficulty is experienced, get medical assistance immediately.

First Aid - Ingestion: If swallowed, do not induce vomiting. If victim is conscious and alert, give 2 to 4 cupfuls of water or milk. Call a physician or poison control center immediately. Never give anything by mouth to an unconscious person. Treat symptomatically and supportively. If swallowed, get medical attention.

5. Fire-Fighting Measures

EXTINGUISHING MEDIA: None Known

Unusual Fire and Explosion Hazards: Keep containers tightly closed. No unusual fire or explosion hazards noted.

Special Fire Fighting Procedures: Water may be used to cool closed containers to prevent buildup of steam. If water is used, fog nozzles are preferred.

Special Fire and Explosion Hazard (Combustible Dust): Not a combustible dust.

6. Accidental Release Measures

Steps to Be Taken If Material Is Released or Spilled: If spilled, contain spilled material and remove with inert absorbent. Dispose of contaminated absorbent, container, and unused contents in accordance with local, state, and federal regulations. Do not incinerate closed containers. Dispose of according to local, state (provincial) and federal regulations. Do not incinerate closed containers. Local authorities should be advised if significant spillages cannot be contained.

7. Handling and Storage

Handling: Wash thoroughly after handling. Wash hands before eating. Remove contaminated clothing and launder before reuse. Use only with adequate ventilation. Follow all SDS and label precautions even after container is emptied because it may retain product residues. Avoid breathing fumes, vapors, or mist. Do not get in eyes, on skin or clothing. Do not swallow.

Storage: Store in a dry, well ventilated place. Keep container tightly closed when not in use.

Advice on Safe Handling of Combustible Dust: No Information

8. Exposure Controls / Personal Protection

<u>Chemical Name</u>	<u>CAS-No.</u>	<u>Weight % Less Than</u>	<u>ACGIH TLV-TWA</u>	<u>ACGIH TLV-STEL</u>	<u>OSHA PEL-TWA</u>	<u>OSHA PEL-CEILING</u>

Calcium Chloride	10043-52-4	75.0	N.E.	N.E.	N.E.	N.E.
Magnesium stearate	557-04-0	1.0	10 mg/m3	N.E.	N.E.	N.E.

PERSONAL PROTECTION

Engineering Controls: Use process enclosures, local exhaust ventilation, or other engineering controls to control airborne levels below recommended exposure limits. Facilities storing or utilizing this material should be equipped with an eyewash facility and a safety shower. Prevent build-up of vapors by opening all doors and windows to achieve cross-ventilation.

Respiratory Protection: A respiratory protection program that meets OSHA 1910.134 and ANSI Z88.2 (U.S.) and/or SOR/86-304 Part XII 12.13 and CSA Standard Z180.1 (Canada) requirements must be followed whenever workplace conditions warrant a respirator's use.

Skin Protection: Use gloves to prevent prolonged skin contact. Nitrile or Neoprene gloves may afford adequate skin protection.

Eye Protection: Use safety eyewear designed to protect against splash of liquids.

Other Protective Equipment: Refer to safety supervisor or industrial hygienist for further guidance regarding types of personal protective equipment and their applications.

Hygienic Practices: Wash thoroughly with soap and water before eating, drinking or smoking. Remove contaminated clothing immediately and launder before reuse.

Engineering Measures for Combustible Dust: No Information

9. Physical and Chemical Properties

Physical State	Liquid	Decomposition Temperature, °C	N.D.
Color	White	pH	N.A.
Odor	Solvent Like	Kinematic Viscosity	N.D.
Odor Threshold	N.E.	Solubility in Water	Slight
Freezing Point / Melting Point, °C	N.D.	Partition Coefficient, n-octanol/water	N.D.
Boiling Range, °C	537 - 537	Vapor Pressure	N.D.
Flammability	Does not Support Combustion	Evaporation Rate	Slower than Ether
Lower Explosion Limit, vol%	N.A.	Specific Gravity	2.144
Upper Explosion Limit, vol%	N.A.	Vapor Density	Heavier than Air
Flash Point, °C	537	Particle Characteristics	N.A.
Auto-Ignition Temperature, °C	N.D.		

(See "Other information" Section for abbreviation legend)

10. Stability and Reactivity

Conditions to Avoid: Avoid excess heat.

Incompatibility: Incompatible with strong oxidizing agents, strong acids and strong alkalis.

Hazardous Decomposition: When heated to decomposition, it emits acrid smoke and irritating fumes.

Hazardous Polymerization: Will not occur under normal conditions.

Stability: This product is stable under normal storage conditions.

11. Toxicological Information

Effects of Overexposure - Eye Contact: Can cause severe eye irritation. Causes eye and skin irritation which may lead to dermatitis with repeated exposures. Irritating, and may injure eye tissue if not removed promptly.

Effects of Overexposure - Skin Contact: Low hazard for usual industrial handling or commercial handling by trained personnel.

Effects of Overexposure - Inhalation: High gas, vapor, mist or dust concentrations may be harmful if inhaled. Avoid breathing fumes, spray, vapors, or mist.

Effects of Overexposure - Ingestion: Harmful if swallowed.

Effects of Overexposure - Chronic Hazards: No Information

PRIMARY ROUTE(S) OF ENTRY: No Information

ACUTE TOXICITY VALUES

The acute effects of this product have not been tested. Data on individual components are tabulated below:

<u>CAS-No.</u>	<u>Chemical Name</u>	<u>Oral LD50</u>	<u>Dermal LD50</u>	<u>Vapor LC50</u>
10043-52-4	Calcium Chloride	1000 mg/kg Rat	>5000 mg/kg Rabbit	N.E.
557-04-0	Magnesium stearate	>10000 mg/kg Rat	N.E.	N.E.

N.E. - Not Established

12. Ecological Information

Ecological Information: No ecotoxicity data was found for this product.

13. Disposal Considerations

Disposal: Dispose of material in accordance to local, state, and federal regulations and ordinances.

14. Transport Information

	<u>Domestic (USDOT)</u>	<u>International (IMDG)</u>	<u>Air (IATA)</u>	<u>TDG (Canada)</u>
UN Number:	N.A.	N.A.	N.A.	N.A.
Proper Shipping Name:	Not Regulated	Not Regulated	Not Regulated	Not Regulated
Hazard Class:	N.A.	N.A.	N.A.	N.A.
Packing Group:	N.A.	N.A.	N.A.	N.A.
Limited Quantity:	No	No	No	No

15. Regulatory Information

U.S. Federal Regulations:

CERCLA - SARA Hazard Category

This product has been reviewed according to the EPA 'Hazard Categories' promulgated under Sections 311 and 312 of the Superfund Amendment and Reauthorization Act of 1986 (SARA Title III) and is considered, under applicable definitions, to meet the following categories:

Acute Toxicity (any route of exposure), Serious eye damage or eye irritation

SARA Section 313

This product contains the following substances subject to the reporting requirements of Section 313 of Title III of the Superfund Amendment and Reauthorization Act of 1986 and 40 CFR part 372:

No Sara 313 components exist in this product.

Toxic Substances Control Act

This product contains the following chemical substances subject to the reporting requirements of TSCA 12(b) if exported from the United States:

No TSCA 12(b) components exist in this product.

16. Other Information**HMIS RATINGS**

Health: 2* Flammability: 1 Physical Hazard: 0 Personal Protection: X

NFPA RATINGS

Health: 2 Flammability: 1 Instability: 0

Volatile Organic Compounds: 0.00%

SDS REVISION DATE: 1/8/2026

REASON FOR REVISION: Substance and/or Product Properties Changed in
Section(s):
01 - Identification
09 - Physical & Chemical Properties

Legend: N.A. - Not Applicable, N.D. - Not Determined, N.E. - Not Established

The manufacturer believes, to the best of its knowledge, information and belief, the information contained herein to be accurate and reliable as of the date of this safety data sheet. However, because the conditions of handling, use, and storage of these materials are beyond our control, we assume no responsibility or liability for personal injury or property damage incurred by the use of these materials. The manufacturer makes no warranty, expressed or implied, regarding the accuracy or reliability of the data or results obtained from their use. All materials may present unknown hazards and should be used with caution. The information and recommendations in this material safety data sheet are offered for the users' consideration and examination. It is the responsibility of the user to determine the final suitability of this information and to comply with all applicable international, federal, state, and local laws and regulations.