ABB BALDOR RELIANCE

Customer information packet

EM2539T-8

40HP, 1770RPM, 3PH, 60HZ, 324T, 4064M, OPSB, F1

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 2:18:47 PM

Specifications

Enclosure	OPSB
Frame	324T
Frame Material	Steel
Frequency	60.00 Hz
Motor Letter Type	Three Phase
Output @ Frequency	40.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	200.0 V @ 60 HZ
Agency Approvals	NEMA PREMIUM NEMA PREMIUM (OLD LOGO) CURUSEEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	109.000 A @ 200.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	94.1 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	109.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	H

Part Detail

Revision	P
Type	AC
Mech. spec.	40J002
Base	
Status	PRD/A
Elec. spec.	40WGX238
Layout	40LYJ002
Eff. date	04-25-2025
CD Diagram	CD0695
Poles	04
Leads	6#4
Proprietary	False
Created date	05-14-2012

Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	6 @ 4 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	4064M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	27.19 IN
Power Factor	84
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	2.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Part Winding
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3554L											
CAT.NO.	EM2539T-8			**P/N**						**ENCL**	OPSB
SPEC.	40J002X238G1	**CC**	010A		**FRAME**	324T		**SER.NO.**			
HP	40			**CLASS**	F		**HZ**	60			
RPM	1770			**PH**	3		**DES**	A			
VOLTS	200				**CODE**	H		**ODE BRG**	6309	**DE BRG**	6312
AMPS	109										
RATING	40C AMB-CONT				**NEMA-NOM-EFF**	94.1		**GREASE**	POLYREX EM		
PF	84	**SER.F.**	1.15		**VPWM INVERTER READY**						
HTR-VOLTS		**HTR-AMPS**			**MAX. SPACE HEATER TEMP.**						

Accessories

Part number	Description	Multiplier
42-1300	C FACE KIT	A8
42EP1601A01	SP'L D-FLANGE MTD. PU. E.P. MDL.42 W/BFL	P1

AC Induction Motor Performance Data
Record # 38390
Typical performance - not guaranteed values

Winding: 40WGX238-R001	**Type:** 4064M	**Enclosure:** OPSB

Nameplate Data				**200 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			40	**Full Load Torque**	119 LB-FT
Volts			200	**Start Configuration**	direct on line
Full Load Amps			109	**Breakdown Torque**	415 LB-FT
R.P.M.			1770	**Pull-up Torque**	181 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	238 LB-FT
NEMA Design Code	A	**KVA Code**	H	**Starting Current**	734 A
Service Factor (S.F.)			1.15	**No-load Current**	45.2 A
NEMA Nom. Eff.	94.1	**Power Factor**	84	**Line-line Res. @ 25ºC**	0.03 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	41°C
S.F. Amps				**Temp. Rise @ S.F. Load**	49°C
				Locked-rotor Power Factor	32
				Rotor inertia	5.09 LB-FT2

Load Characteristics 200 V, 60 Hz, 40 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	44	68	78	84	86	86	85
Efficiency	92.9	94.6	94.9	94.4	93.6	93	94
Speed	1792	1785	1777	1770	1761	1752	1765
Line amperes	52.1	67.5	87.3	109	134	162	124


ABB Motors and Mechanical Inc.


WINDING # 40WGX238

40 HP 3 PH 60 HZ 1770 RPM 200 V 4064M

TORQUES(LB-FT): PO=415 PU=181 LR=238 LRA=734


Typical performance - not guaranteed values.





40LYJ002
(4034 - 4056) = 26.19
(4058 - 4066) = 27.19
4.78
5.57
5.25
.50 KEY
3.88 LONG
Ø2.125
2.124
6 HOLES
Ø.66
10.50
.88
12.00
5.25
13.75
13.38
12.27
6.70
1 LIFTING LUG
(EA END)
DIAGONALLY
SPACED
14.62
8.00 +.00 -.06
4.25
.31
6.23
6.23
LEAD HOLE
Ø2.50
9.71
7.13
14.25
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: FIX LIFTING LUG GRAPHICS
REV: F
VERSION: 04
REVISED: 10:44:13 01/15/2026
TDR: 000001270293
MODEL NO. 40LYJ002
REF: -
BY: USJOCUR5
B
BALDOR
HORZ OPSB 324-6T W/10CB3001 KOBX
40LYJ002

CD0695


TYPICAL WYE–CONNECTED MOTOR




START CONNECTION



RUN CONNECTION



TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. MOTOR MAY BE WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0695

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: C	BY: JLP	REVISED: 01/21/99 3:19	TDR: 0171435
CD0695		FILE: AAA00005151	MDL: –
		MTL: –	3PH, SV, 6 LEADS, PART WINDING START