



HIGHER PERFORMANCE, FASTER INSTALLATION DUAL SELECTABLE STRIP

The new Performance Class Dual Selectable Strip series from LEDVANCE is a flexible, high-performance line of strip fixtures that can be used in new construction and retrofit installations. The Strip series features a toolless, snap off lens/light engine module that makes installation fast and efficient. The fixtures also come from the factory pre-wired for single circuit through wiring – no additional wiring is needed for row mounting, which saves time, material and installation costs. This series also features the availability of a choice of optional field installable PIR or microwave motion/daylight sensors, making it quick and easy to install the sensors during installation or at any time thereafter.

PERFORMANCE CLASS



For more information, visit www.ledvanceUS.com/luminaires



LEDVANCE LLC
 181 Ballardvale Street, Suite 203
 Wilmington, MA 01887 USA
 Phone 1-800-LIGHTBULB
 (1-800-544-4828)

ORDERING GUIDE

STRIP	3A	SXXX	UNH	D	8	SC7	XX	WH	X
PRODUCT NAME	GENERATION	WATTAGE	VOLTAGE	DIMMING	CRI	COLOR TEMPERATURE	SIZE	COLOR	OPTIONS
STRIP = STRIP	3A = Generation 3A	S030 = 15/20/25/30W S055 = 22/35/45/55W S100 = 45/65/85/100W	UNH = 120-347V	D = 0-10V Dimming	80 = >80 CRI	SC7 = 3500/4000/5000K	24 = 2ft 48 = 4ft 96 = 8ft	WH = White	E = Emergency Back-up Battery

CONTRACTOR BENEFITS

- The Dual Selectable Strip product line was designed from the start with the contractor in mind
- Each product is configurable to four wattages and three CCTs, so three SKUs take the place of 36
- Installation accessories are included in the package, so there is no need to order separate brackets and covers – the fixtures are ready to install right out of the box
- Pre-wired polarized plugs are included at the end of every fixture for continuous row mounting; no need to order different SKUs that include the wiring
- Every fixture is factory-ready for fast, efficient installation

BENEFITS AND FEATURES

- CCT and wattage selectable
- Selection switches are easily accessible on the outside of the fixture
- Available in 2ft, 4ft, and 8ft lengths
- Light engine and lens module feature toolless removal and secure snap-fit for fast, efficient installation
- End-to-end joiner bracket for continuous row mounting, V-hook mounting bracket, and split junction box cover included
- Factory installed polarized wiring system, ready for single circuit row mounted through wiring. No additional wiring needed; save time, material and money
- All fixtures are pre-wired for optional field installable internal microwave or external PIR motion/daylight sensors
- Compatible with field installable LEDVANCE LINK™ components
- Optional 8W emergency battery back-up (made to order)
- DLC 5.1 Listed
- Diffuse acrylic lens provides smooth, even illumination
- White powder coated metal body
- CRI >80



SCAN TO FOLLOW US
ON SOCIAL MEDIA

LEDVANCE is a registered trademark. All other trademarks are those of their respective owners. Specifications subject to change without notice.

© 2023 LEDVANCE LLC

Scan the QR tag to view
or download additional
product information

