

## Master MH-80-OFR Kerosene/Diesel Radiant Heater—80,000 BTU



- Heat up well-ventilated construction sites, workshops, farms, or garages
- Made of rugged steel for years of use
- Radiant heat, heats like the sun
- Runs on efficient, clean-burning Kerosene and CSA certified to run on #1 & 2 Diesel Fuel, JP8/Jet A Fuel and #1 & 2 Fuel Oil
- 1-year limited warranty

### Product Description

Master's 80,000 BTU Kerosene Radiant Heater is a pro's dream for quiet, efficient heat. It warms up to 2,000 square feet of your space with its radiant heat plate. This multi-fuel heater is part of Master's line of innovative Radiant Heaters that combine forced-air heat with radiant heat, which warm objects directly like the sun does. The result is a heater that works quickly and effectively to bring warmth to a space. It's also a lot quieter than comparable conventional kerosene heaters. Master – built for power.



## Features and Benefits

- Operates up to 6 hours on a full tank of fuel
- Steel construction
- Heats up to 2,000 square feet
- Ceramic burner housing
- Easy-lift handle
- Radiant heat plate
- Power on/off switch
- Compatible with 7 fuels
- 1-year limited warranty

## Key Specs

|                                   |                                                                          |                                     |              |
|-----------------------------------|--------------------------------------------------------------------------|-------------------------------------|--------------|
| <b>Model Number</b>               | MH-80-OFR                                                                | <b>Max. Operating Hours</b>         | 6            |
| <b>Brand</b>                      | Master                                                                   | <b>Heating Area (sq. ft.)</b>       | 2,000        |
| <b>Warranty</b>                   | 1-year limited warranty                                                  | <b>Volts</b>                        | 120          |
| <b>Net Weight (lb.)</b>           | 37                                                                       | <b>Max. BTU</b>                     | 80,000       |
| <b>Fuel Type</b>                  | K-1 Kerosene, JP8/<br>Jet A Fuel, #1 & 2<br>Fuel Oil, # 1 & #2<br>Diesel | <b>Dimensions (L x W x H) (in.)</b> | 21 x 22 x 14 |
| <b>Fuel Consumption (gal./hr)</b> | 0.63                                                                     |                                     |              |
| <b>Fuel Tank Capacity (gal.)</b>  | 4                                                                        |                                     |              |

