



<b>EAN:</b>	4013288108036	<b>Size:</b>	81x26x26 mm
<b>Part number:</b>	05007670001	<b>Weight:</b>	35 g
<b>Article number:</b>	334 SK	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82054000

- Screwdriver for slotted screws
- Smooth hard zones for high speed turning, soft grip zones for high torque transfer
- Take it easy tool finder: colour coding according to profile and size
- Hexagonal blade

High quality Kraftform Plus screwdriver with hexagonal blade. Hard gripping zones for high working speeds whereas soft zones ensure high torque transfer for fast and low-fatigue working. Take it easy tool finder with colour coding according to profiles and size stamp - for simple and rapid accessing of the required tool. The hexagonal non-roll feature prevents any rolling away at the workplace.



**Web link**

<https://www.wera.de/en/05007670001>

Wera - 334 SK

05007670001 - 4013288108036

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)

**Lasertip prevents slipping out**



Kraftform Plus screwdrivers - ergonomics you can grasp. They relieve the entire hand-arm system even when used intensively. Along with other technical and product advantages such as the Lasertip for a secure fit in the screw head, Kraftform screwdrivers are the ideal choice whenever manual screwdriving jobs are concerned.



A precisely-focused laser creates a sharp-edged surface structure. Wera Lasertip "bites" itself into the screw head and prevents any slips out of the recess. It is available for screwdrivers for slotted, Phillips and Pozidriv screws.

**Lasertip**



A precisely-focused laser creates a sharp-edged surface structure. Wera Lasertip "bites" itself into the screw head and prevents any slips out of the recess. It is available for screwdrivers for slotted, Phillips and Pozidriv screws.

**Reduced contact pressure**




Wera Lasertip reduces the contact pressure required and enhances force transfer - meaning less screwdriving effort is required. Screwdriving becomes safer and easier.

**Hexagonal blade and bolster**



Hexagonal blade and bolster for higher torque transfer.

**Take it easy Tool Finder**



Screwdrivers with Take it easy tool finder: colour coding according to profile and size stamp.

**Kraftform**



The basic idea for the prototype of the Kraftform handle - that the hand should dictate the design - has, right through to today, proved to be correct. In cooperation with the internationally recognised Fraunhofer IAO Institute, Wera developed a screwdriver handle designed to match the shape of the human hand as long ago as the 1960s. After a long development phase, the Wera Kraftform handle was launched to the market in 1968. It has been optimised through the years with new technologies, but has kept its proven shape. After all, the human hand has not changed either.

**Prevents hand injuries**




The outstanding design of the Kraftform handle that fits perfectly into the hand prevents hand injuries such as blisters and calluses.

Web link  
<https://www.wera.de/en/05007670001>

Wera - 334 SK  
 05007670001 - 4013288108036

Wera Werkzeuge GmbH  
 Korzter Straße 21-25  
 D-42349 Wuppertal  
 Tel: +49 (0)2 02 / 40 45-0  
 E-Mail: info@wera.de

Further versions in this product family:



	mm	mm	mm	mm	mm	mm	inch	inch
<b>05007670001<sup>1),2)</sup></b>	<b>0.6</b>	<b>3.5</b>	<b>4</b>	<b>-</b>	<b>75</b>	<b>81</b>	<b>9/64"</b>	<b>3"</b>
05007671001 <sup>2)</sup>	0.8	4.0	4	-	90	81	5/32"	3 1/2"
05007672001	0.8	4.5	5	8	90	98	0.178"	3 1/2"
05007673001	1.0	5.5	6	10	100	98	7/32"	4"
05007674001	1.2	6.5	6	10	125	105	1/4"	5"
05007675001	1.2	7.0	6	10	125	105	9/32"	5"
05007676001	1.6	9.0	8	13	150	112	11/32"	6"
05007677001	1.6	10.0	8	13	175	112	3/8"	7"

1) Without Lasertip  
2) No hexagon bolster

Web link  
<https://www.wera.de/en/05007670001>

Wera - 334 SK  
05007670001 - 4013288108036

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: info@wera.de