SECTION 1. PRODUCT AND COMPANY IDENTIFICATION

Material name : ZEP HARDWOOD & LAMINATE FLOOR CLEANER QT 12CT

Material number : ZUHLF32

Manufacturer or supplier's details

Company : Zep Inc.

Address : 350 Joe Frank Harris Parkway, SE
Emerson, GA 30137

Telephone : Compliance Services - 877-428-9937

Emergency telephone numbers

For SDS Information	:	Compliance Services - 877-428-9937
For a Medical Emergency	:	877-541-2016 Toll Free - All Calls Recorded
For a Transportation Emergency	:	CHEMTREC: 800-424-9300 - All Calls Recorded. In the District of Columbia 202-483-7616

Recommended use of the chemical and restrictions on use

Recommended use : FLOOR CARE

Note: This product is labeled as a consumer product in accordance with the United States Consumer Product Safety Commission regulations. The warnings presented below in this Safety Data Sheet (SDS) comply with the 2012 OSHA Hazard Communication Standard (GHS - Globally Harmonized System of Classification and Labeling). The requirements for the labeling and warnings of consumer products may differ from those required for GHS based hazard communication.

SECTION 2. HAZARDS IDENTIFICATION

Emergency Overview

Appearance	liquid
Colour	colourless
Odour	pleasant

GHS Classification

Not a hazardous substance or mixture.

GHS label elements

Not a hazardous substance or mixture.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture

Hazardous components

Chemical name	CAS-No.	Concentration [%]
2-(2-butoxyethoxy)ethanol	112-34-5	>= 1 - < 3

The exact percentages of disclosed substances are withheld as trade secrets.

SECTION 4. FIRST AID MEASURES

General advice	:	Do not leave the victim unattended. Show this safety data sheet to the doctor in attendance. Move out of dangerous area.
If inhaled	:	If unconscious, place in recovery position and seek medical advice. If symptoms persist, call a physician.
In case of skin contact	:	If on clothes, remove clothes. If skin irritation persists, call a physician. Wash off immediately with plenty of water for at least 15 minutes.
In case of eye contact	:	Remove contact lenses. Protect unharmed eye. If eye irritation persists, consult a specialist.
If swallowed	:	Keep respiratory tract clear. Never give anything by mouth to an unconscious person. If symptoms persist, call a physician. DO NOT induce vomiting unless directed to do so by a physician or poison control center.
Most important symptoms and effects, both acute and delayed	:	Effects may be delayed, symptoms may include minor eye or skin irritation. Overexposure may cause mild eye or skin irritation.
Notes to physician	:	Treat symptomatically. Symptoms may be delayed.

SECTION 5. FIREFIGHTING MEASURES

Suitable extinguishing media	:	Water spray jet Alcohol-resistant foam Carbon dioxide (CO2) Dry chemical
Unsuitable extinguishing media	:	High volume water jet
Specific hazards during firefighting	:	Do not allow run-off from fire fighting to enter drains or water courses.
Hazardous combustion products	:	Carbon dioxide (CO2) Carbon monoxide Smoke

Specific extinguishing methods	:	Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Further information	:	Standard procedure for chemical fires. Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Special protective equipment for firefighters	:	Wear self-contained breathing apparatus for firefighting if necessary.

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures	:	Ensure adequate ventilation. Use personal protective equipment. Evacuate personnel to safe areas.
Environmental precautions	:	If the product contaminates rivers and lakes or drains, inform respective authorities. Prevent further leakage or spillage if safe to do so. Prevent product from entering drains.
Methods and materials for containment and cleaning up	:	Wipe up with absorbent material (e.g. cloth, fleece). Keep in suitable, closed containers for disposal.

SECTION 7. HANDLING AND STORAGE

Advice on safe handling	:	For personal protection see section 8. Smoking, eating and drinking should be prohibited in the application area.
Conditions for safe storage	:	Electrical installations / working materials must comply with the technological safety standards. Keep in a dry, cool and well-ventilated place.
Materials to avoid	:	No materials to be especially mentioned.

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Components with workplace control parameters

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
2-(2-butoxyethoxy)ethanol	112-34-5	TWA (Inhalable fraction and vapor)	10 ppm	ACGIH

Engineering measures : effective ventilation in all processing areas

Personal protective equipment

Respiratory protection	:	No personal respiratory protective equipment normally required.
Hand protection		
Material	:	Protective gloves
Remarks	:	The suitability for a specific workplace should be discussed with the producers of the protective gloves.
Eye protection	:	Safety glasses Eye wash bottle with pure water
Skin and body protection	:	Impervious clothing
Hygiene measures	:	General industrial hygiene practice.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	:	liquid
Colour	:	colourless
Odour	:	pleasant
Odour Threshold	:	No data available
pH	:	8.5 - 9.0
Melting point/freezing point	:	No data available
Boiling point	:	100 °C
Flash point	:	does not flash
Evaporation rate	:	1
Upper explosion limit	:	Not applicable
Lower explosion limit	:	Not applicable
Vapour pressure	:	not determined
Density	:	0.99 g/cm3
Solubility(ies)		
Water solubility	:	soluble
Partition coefficient: n-octanol/water	:	No data available
Auto-ignition temperature	:	not determined
Thermal decomposition	:	No data available
Viscosity		
Viscosity, kinematic	:	No data available

SECTION 10. STABILITY AND REACTIVITY

Reactivity	:	Stable
Chemical stability	:	Stable under normal conditions.
Possibility of hazardous reactions	:	Stable under recommended storage conditions. No hazards to be specially mentioned.
Conditions to avoid	:	No data available
Incompatible materials	:	None.
Hazardous decomposition products	:	Carbon oxides

SECTION 11. TOXICOLOGICAL INFORMATION

Potential Health Effects

Aggravated Medical Condition	:	None known.
Symptoms of Overexposure	:	Effects may be delayed, symptoms may include minor eye or skin irritation. Overexposure may cause mild eye or skin irritation. Treat symptomatically. Symptoms may be delayed.

Carcinogenicity:

IARC	No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
ACGIH	No component of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.
OSHA	No component of this product present at levels greater than or equal to 0.1% is on OSHA's list of regulated carcinogens.
NTP	No component of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

Acute toxicity

No data available

Skin corrosion/irritation

No data available

Serious eye damage/eye irritation

No data available

Respiratory or skin sensitisation

No data available

Germ cell mutagenicity

No data available

Carcinogenicity

No data available

Reproductive toxicity

No data available

STOT - single exposure

No data available

STOT - repeated exposure

No data available

Aspiration toxicity

No data available

Further information

Product:

Remarks: No data available

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity

No data available

Persistence and degradability

No data available

Bioaccumulative potential

Product:

Partition coefficient: n-octanol/water : Remarks: No data available

Components:

2-(2-butoxyethoxy)ethanol :

Partition coefficient: n-octanol/water : Pow: 1

Mobility in soil

No data available

Other adverse effects

No data available

Product:

Regulation	40 CFR Protection of Environment; Part 82 Protection of Stratospheric Ozone - CAA Section 602 Class I Substances
Remarks	This product neither contains, nor was manufactured with a Class I or Class II ODS as defined by the U.S. Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A + B).

Additional ecological information : No data available

SECTION 13. DISPOSAL CONSIDERATIONS

Disposal methods

Waste from residues : Dispose of in accordance with local regulations.
Do not contaminate ponds, waterways or ditches with chemical or used container.
The product should not be allowed to enter drains, water courses or the soil.

Contaminated packaging : Empty remaining contents.
Do not re-use empty containers.
Dispose of as unused product.

SECTION 14. TRANSPORT INFORMATION

Transportation Regulation: 49 CFR (USA):
NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: IMDG (Vessel):
NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: IATA (Cargo Air):
NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: IATA (Passenger Air):
NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: TDG (Canada):
NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

The product as delivered to the customer conforms to packaging requirements for shipment by road under US Department of Transportation (DOT) regulations. Additional transportation classifications

noted above are for reference only, and not a certification or warranty of the suitability of the packaging for shipment under these alternative transport regulations.

SECTION 15. REGULATORY INFORMATION

TSCA list : No substances are subject to a Significant New Use Rule.

No substances are subject to TSCA 12(b) export notification requirements.

EPCRA - Emergency Planning and Community Right-to-Know Act

CERCLA Reportable Quantity

Components	CAS-No.	Component RQ (lbs)	Calculated product RQ (lbs)
copper dinitrate	3251-23-8	100	*

*: Calculated RQ exceeds reasonably attainable upper limit.

SARA 304 Extremely Hazardous Substances Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

SARA 311/312 Hazards : No SARA Hazards

SARA 302 : No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

SARA 313 : The following components are subject to reporting levels established by SARA Title III, Section 313:
2-(2-butoxyethoxy)ethanol 112-34-5 1.5012 %

California Prop. 65

This product does not contain any chemicals known to State of California to cause cancer, birth defects, or any other reproductive harm.

The components of this product are reported in the following inventories:

TSCA On TSCA Inventory
DSL This product contains one or more components that are listed on the Canadian NDSL. All other components are on the Canadian DSL.

For information on the country notification status for other regions please contact the manufacturer's regulatory group.

Inventory Acronym and Validity Area Legend:

TSCA (USA), DSL (Canada), NDSL (Canada)

SECTION 16. OTHER INFORMATION

Further information

NFPA:

HEALTH	0
FLAMMABILITY	0
INSTABILITY	0
SPECIAL HAZARD.	

0 = not significant, 1 =Slight,
2 = Moderate, 3 = High
4 = Extreme

HMIS III:

HEALTH	0
FLAMMABILITY	0
PHYSICAL HAZARD	0

0 = not significant, 1 =Slight,
2 = Moderate, 3 = High
4 = Extreme, * = Chronic

OSHA - GHS Label Information:

Not a hazardous substance or mixture.

Version:	4.1
Revision Date:	10/01/2023
Print Date:	10/27/2026

We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information in this document applies to this specific material as supplied. It may not be valid for this material if it

is used in combination with any other materials. Users should make their own investigations to determine the suitability and applicability of the information for their particular purposes. This SDS has been prepared by the Compliance Services organization supporting this manufacturer, supplier or distributor.