

Special Tec B FE SAE 0W-30

Description

Modern fully synthetic motor oil for superior performance and long engine life. Developed specifically for use in numerous gasoline vehicles without particulate filter (GPF) from 2002 and later. The low viscosity ensures excellent cold start behavior, improves engine efficiency and reduces fuel consumption. Use with extended oil change intervals as per manufacturer.

Properties

- ideal with turbochargers and catalytic converters
- outstanding engine cleanliness
- excellent resistance to aging
- minimizes friction
- ensures maximum engine performance

Specifications / Approvals

API SP • ACEA A5 • ACEA B5 • BMW Longlife-01 FE • MB-Approval 229.6 • Volvo VCC 95200377

LIQUI MOLY recommends this product for vehicles or assemblies for which the following specifications or original spare part numbers are required:

Renault RN 0700

Technical data

SAE Viscosity	0W-30 SAE J300
Density at 59 °F	0,845 g/cm ³ DIN 51757
Viscosity at 104 °F	51,0 mm ² /s ASTM D7042
Viscosity at 212°F	9,8 mm ² /s ASTM D7042
Viscosity at -40 °F (MRV)	< 60000 mPas ASTM D4684
Viscosity at -31 °F (CCS)	≤ 6200 mPas ASTM D5293
Viscosity index	180 DIN ISO 2909
HTHS at 302 °F	≥ 3,0 mPas ASTM D5481
Pour point	-49 °F DIN ISO 3016
Flash point	428 °F DIN ISO 2592
Evaporation loss (Noack)	10,0 % ASTM D5800 B
Total base number	12,0 mg KOH/g DIN ISO 3771



Technical data

Sulfate ash	1,0 g/100g DIN 51575
Color number (ASTM)	3,5 DIN ISO 2049

Areas of application

For gasoline engines where a motor oil according to current specifications is required or recommended. Tested safe with catalytic converters and turbochargers.

Application

Observe the manufacturers instructions!

Available pack sizes

1 l Canister plastic	22260 CAEN-CAFR-USEN
5 l Canister plastic	22261 CAEN-CAFR-USEN
20 l Canister plastic	22269 CAEN-CAFR-USEN
205 l Black plate barrel	22262 CAEN-CAFR-USEN
1.000 l Container	22268 CAEN-CAFR-USEN

Our information is based on thorough research and may be considered reliable, although not legally binding.