ABB BALDOR RELIANCE

Customer information packet

ECR9106T

10HP, 1175RPM, 3PH, 60HZ, 256T, 0962M, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 6:01:32 PM

Specifications

Enclosure	TEFC
Frame	256T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	10.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CCSA US
	CSA EEV
	NEMA PREMIUM
	NEMA_PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	14.000 A @ 460.0 V
	28.000 A @ 230.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK

Part Detail

Revision	AE
Type	AC
Mech. spec.	09L575
Base	
Status	PRD/A
Elec. spec.	09WGT161
Layout	09LYL575
Eff. date	06-24-2024
CD Diagram	CD0005
Poles	06
Leads	9#12 Y
Proprietary	False
Created date	01-14-2015

Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	14.0 a
Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	1800 rpm
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 12 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0962M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	24.77 IN
Power Factor	74
Product Family	Super-E Chemical Processing
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.25
Shaft Diameter	1.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1175 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None

Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3293													
CAT.NO.	ECR9106T		**P/N**				**ENCLOSURE**	TEFC					
SPEC.	09L575T161G1	**CC**	010A	**FRAME**	256T		**S/N**						
HP	10	**CLASS**	F	**HZ**	60	**DES**	A						
RPM	1175	**RPM MAX**	1800	**PH**	3	**KVA-CODE**	J						
VOLT	230/460			**I.P.**	55								
AMP	28/14		**SER.F.**	1.25	**PF**	74	**ODE BRG**	6309	**DE BRG**	6311			
RATING	40C AMB-CONT		**NEMA-NOM-EFF**	91	**GREASE**	POLYREX EM							
HTR-VOLTS	**HTR-AMPS**		**HTR-WATTS**		**INV.TYPE**								
	SFA 33/16.5												
			C HP FR	60	**C HP TO**	90							
			CT HZ FROM	6	**CT HZ TO**	60							
			MOTOR WEIGHT	355	**VT HZ FROM**	6	**VT HZ TO**	60					

AC Induction Motor Performance Data
Record # 51635
Typical performance - not guaranteed values

Winding: 09WGT161-R001	**Type:** 0962M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			10	**Full Load Torque**	45 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			28/14	**Breakdown Torque**	165 LB-FT
R.P.M.			1175	**Pull-up Torque**	80.7 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	128 LB-FT
NEMA Design Code	A	**KVA Code**	J	**Starting Current**	100 A
Service Factor (S.F.)			1.25	**No-load Current**	7.56 A
NEMA Nom. Eff.	91	**Power Factor**	74	**Line-line Res. @ 25ºC**	0.811 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	44°C
S.F. Amps			33/16.5	**Temp. Rise @ S.F. Load**	57°C
				Locked-rotor Power Factor	40.3
				Rotor inertia	4.98 lb-ft²

Load Characteristics 460 V, 60 Hz, 10 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	34	55	67	74	78	80	78
Efficiency	84.8	89.9	91.2	91	90.3	89.4	90.3
Speed	1194	1189	1184	1179	1173	1166	1173
Line amperes	8.1	9.61	11.7	14	16.8	19.7	16.8


ABB Motors and Mechanical Inc.


WINDING # 09WGT161

10 HP 3 PH 60 HZ 1175 RPM 460 V 0962M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=165 PU=80.7 LR=128 LRA=100




09LYL575
(920 - 964) = 24.77
11.53
NAMEPLATE
4.27
4.00
.38 KEY
2.88 LONG
Ø 1.625
1.624
SLINGER
(EA. END)
DRAIN FITTING
(EA. END)
.25-20 TAP
GND LOC
8 HOLES
Ø.53
8.25
8.25
.75
10.00
4.24
11.50
12.94
10.30
6.63
2.70
12.88
6.25
6.19
LEAD
HOLE
1.25 NPT
5.00
5.00
8.27
5.75
11.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CHG 09SF1107A04 TO 09SF1107A02
REV: D
VERSION: 04
REVISED: 09:25:56 03/18/2021
TDR: 000001163004
MODEL NO. 09LYL575
REF: -
BY: USODDIL
B
BALDOR - RELIANCE®
HORZ TEFC 254-6T ECP W/311 PU BRG (CRUSHER DUTY)
09LYL575

CD0005






NOTES:


1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.


CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS

CD0180







NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1