
SIEMENS

Data sheet US2:P1224B3100CU



SIEMENS LOW VOLTAGE PL SERIES LOAD CENTER. FACTORY INSTALLED MAIN BREAKER WITH 12 1-INCH SPACES ALLOWING MAX 24 CIRCUITS. 3-PHASE 4-WIRE SYSTEM RATED 120/240V OR 120/208V (100A) 22KA INTERRUPT. SPECIAL FEATURES: COPPER BUS, INTERCHANGEABLE MAIN, GRAY TRIM, NEMA TYPE1 ENCLOSURE FOR INDOOR USE.

General technical data	
configuration of the busbars	100 A
fastening method	Combination
phase number	3
suitability for operation	Residential
Electricity	
ampacity	100 A
ampacity minimum	100 A
voltage between phase and Ground (GND) rated value	120 V
voltage between phase and phase rated value	240 V
Switching capacity	
switching capacity current acc. to EN 60898 rated value	22000 A
Model	
product brand name	Siemens
product sub brand name	Load Centers
Mechanical Design	
number of modular width units for installation width	12

last modified: 6/18/2021

Subject to change without notice
© Copyright Siemens